



SPECIFICATIONS

KAM1411

COOLING CAPACITY	BTU/hr @ 95F at 60% RH	13,700 (1.1-Ton)
COMPRESSOR DATA	Compressor Type	Hermetic Rotary
	Operating Temperatures	60-110 F 50%RH
	Refrigerant	410A
FAN DATA Evaporator	Fan Type (Centrifugal)	Direct Drive
	Air Flow (CFM)	30'-550 / 60'-495 / 90'-425
	Supply Air Device	1-6" diameter outlet
Condenser	Fan Type (Centrifugal)	Direct Drive
	Air Flow (CFM)	650
ELECTRICAL DATA	Power Supply (Volts)	115/Single Phase
	Current Consumption (Amps)	12.8
	Power Consumption (Watts)	1.1
	Maximum Circuit Breaker (Amps)	15
	Minimum Circuit Ampacity(Amps)	17.824
	Min./Max. Voltage	105-125
	Power Cord Gauge/Length	12/50'
	Plug Configuration	NEMA 5-15
DIMENSIONAL DATA	Width x Depth x Height (Inches)	22" x 22" x 48"
	Weight (Lbs.)	205
	Shipping Weight (Lbs.)	280
	Ceiling Kit Weight (Lbs.)	38
	Shipping Weight w/ Ceiling Kit	283
SAFETY DEVICE DATA	Compressor Overload	Internal
	Fan Motor Overload	Automatic Internal
	High Pressure Switch	Manual
	Compressor Short Cycle	Yes
	Automatic Restart	Yes
	Control	2 Position Switch Off-On
	Condensate Tank Overflow	Yes

1-800-KWIKOOL

www.kwikool.com