




POWER & EFFICIENCY

INPUT POWER OPTIONS	AC 1PH 200-240V 50/60Hz AC 3PH 200-240V 50/60Hz	
CURRENT AT MAX SPEED (Amp)	2.7 - 2.4 A	1.4 - 1.2 A
POWER (hp)	5/8 HP	
MAXIMUM SPEED (RPM)	156 RPM	
MAX AFFECTED AREA	40 ft Dia 1,600 sqft	

DIMENSIONS & WEIGHT

FAN DIAMETER	8 ft
FAN WEIGHT	87lbs (40 kg)



Pictured with 2 ft downrod

MOUNTING & SAFETY

MOUNTING OPTIONS	I-beam Glulam
DOWNROD (A)	Downrods available in 1 ft increments: 2 ft min., 10 ft max. Downrod length must be specified at time of order.
SAFETY FEATURES	Fan Retention System Airfoil Retention System Fire relay

IN THE BOX

INCLUDED	Fan I-beam mount with pre-wired downrod Control panel Install manual Wall Control Mounting hardware kit Communication Kit Guy wire kit
OPTIONAL	Additional cable lengths Network Controller Glulam brackets

WARRANTY & CERTIFICATIONS

CERTIFICATIONS	ETL/Intertek-certified to ANSI/UL 507 and CSA C22.2 No. 113 in North America
WARRANTY ¹	10-year, Non-Prorated Warranty

¹See complete warranty for details.