

# GH-26120ZH WITH NEWALL DP700 DRO AND TAPER ATTACHMENT

321894

The JET ZH-Series 4-1/8" spindle bore lathes feature a clutch operated headstock, universal gearbox, and a rapid traverse on the apron that makes the ZH-Series perfect for high-output production applications. Features you've come to expect in a JET Lathe that is backed by the industry-leading JET Two Year Warranty



## FEATURES

- 4-1/8" Spindle Bore
- Clutch operated headstock with all headstock gears hardened and ground
- Universal gearbox design allows easy selection of inch and metric threading
- Meehanite Castings are used for added durability.
- Bed ways are induction hardened and ground for durability.
- Traveling splash guard
- Heavy-duty tailstock and quill
- Rapid power traverse to cross slide and carriage
- Standard Equipment:
  - Drive Plate
  - 12" 3-Jaw scroll chuck with top reversing jaws
  - 16" 4-Jaw Chuck
  - Face Plate
  - 2 Steady Rests
  - Follow Rest
  - 4-Way Toolpost
- Micro-carriage bed stop
- Coolant System
- Halogen work lamp



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# GH-26120ZH WITH NEWALL DP700 DRO AND TAPER ATTACHMENT

321894

## SPECIFICATIONS

Size	26 x 120
Digital Readout	Newall DP700
Accessory 1	Taper Attachment
Swing Over Bed (In.)	26
Swing Over Cross Slide (In.)	16-1/2
Swing Through Gap (In.)	34
Length of Gap (In.)	8
Distance Between Centers (In.)	120
Spindle Bore (In.)	4-1/8
Spindle Mount	D1-8
Spindle Taper with Sleeve	MT-5
Number of Spindle Speeds	12
Range of Spindle Speeds (RPM)	36 - 1,600
Number of Longitudinal and Cross Feed Rates	65
Range of Longitudinal Feeds (IPR)	.0023 - .0937
Range of Cross Feeds (IPR)	.0040 - .0404
Number of Inch Threads	48



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# GH-26120ZH WITH NEWALL DP700 DRO AND TAPER ATTACHMENT

321894

## FULL SERIES

STOCK NO	MODEL NO	SIZE	DIGITAL READOUT	ACCESSORY 1	ACCESSORY 2	ACCESSORIES
321890	GH-26120ZH	26 x 120				
321860	GH-2680ZH	26 x 80				
321893	GH-26120ZH	26 x 120				Taper Attachment
321892	GH-26120ZH	26 x 120	ACU-RITE 200S			
321895	GH-26120ZH	26 x 120	ACU-RITE 200S			Taper Attachment
321896	GH-26120ZH	26 x 120	ACU-RITE 300S			
321891	GH-26120ZH	26 x 120	Newall DP700			
321894	GH-26120ZH	26 x 120	Newall DP700			Taper Attachment
321864	GH-2680ZH	26 x 80				Taper Attachment
321863	GH-2680ZH	26 x 80	ACU-RITE 200S			
321865	GH-2680ZH	26 x 80	ACU-RITE 200S			Taper Attachment
321861	GH-2680ZH	26 x 80	Newall DP700			
321862	GH-2680ZH	26 x 80	Newall DP700			Taper Attachment

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE