

MILESYN SB 15W40 CJ-4

HEAVY DUTY MOTOR OIL

MILESYN SB 15W40 CJ-4 is a superior lubricant formulated to meet or exceed the warranty requirements of most manufacturers of diesel and gasoline engines. Field tests have shown our CJ-4 oils retain TBN levels for longer periods due to the advanced additive chemistry. Designed for the modern high performance, low emission diesel engines using ERG and Diesel particulate filters, this lubricant offers superior engine protection for heavy-duty diesel engines requiring the latest API CJ-4/SN specification.

Features and Benefits

- Exceptional overall engine protection
- Excellent cold temperature properties
- Outstanding soot control
- Extreme protection against oil thickening.
- Protects against rust, wear, and bearing corrosion.
- Excellent protection against sludge and varnish formation
- Resistant to viscosity and thermal breakdown at high temperatures

Recommended For Applications

API CJ-4/SN, CI-4+,
ACEA E9-08, E7-04
Caterpillar ECF-3, ECF-2, ECF-1a
Cummins CES 20081, 20077 & 20076
Detroit Diesel 7SE270, PG PGOS, 932K218, 93K214
Mack EO-O Premium Plus, EO-M PP, EO-N PP
Mercedes-Benz 228.31
Volvo VDS-4, VDS-3, VDS-2
MTU MTL 5044 Type 2.1
International/Navistar
Renault VI RLD-3

Applications

MILESYN SB 15W40 CJ-4 meets the performance requirements of most diesel engine manufacturers such as Caterpillar, Cummins, Detroit Diesel, Ford, Mack, Navistar, and Volvo. It can be used with complete success in over-the-road diesel trucks, off-highway diesel equipment, farm tractors, and passenger cars and light trucks with diesel engines, turbo-charged or non-turbo-charged and well as gasoline engines.

Typical Properties	
Property	SB 15W40
Viscosity, cSt @ 40°C	114
Viscosity, cSt @ 100°C	15.30
Viscosity Index	141
Viscosity, CCS cP @ -20°C	6100
Flash Point, °C	227
Pour Point, °C	-39
Sulfated Ash, wt%	0.968
Total Base Number	8.4
Specific Gravity	0.889