

J-A3816, 15" 6-SPEED FLOOR MODEL DRILL PRESS 115/230V 1PH

354500

JET's heavy-duty 6-speed Step Pulley Drill Press are manufactured with the weight and rigidity to maintain the tight tolerances required of metalworking applications. The oversized, massive drill heads have widely spaced bearing surfaces for full quill support throughout its travel. JET included a wider range of operation speeds for drilling both small and larger holes with quick and easy speed changes



FEATURES

- Constructed to provide a solid base for drilling
- 6-Spindle Speeds from 375 to 5,000 RPM
- Larger quill provides greater accuracy
- Large production table
- 3" column for maximum head support
- 1/2" drill chuck and arbor included
- Drill chuck guard



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-A3816, 15" 6-SPEED FLOOR MODEL DRILL PRESS 115/230V 1PH

354500

SPECIFICATIONS

Style (Type)	Variable
Drills to Center of Circle (in)	15
Drilling Capacity Cast Iron (In.)	5/8
Drilling Capacity Mild Steel (In.)	1/2
Distance Column to Spindle (In.)	15
Number of Spindle Speeds	6
Range of Spindle Speeds (RPM)	375, 625, 1,125, 1,950, 3,400, 5,000
Column Diameter (In.)	3
Spindle Taper (In. x TPI)	MT-2
Spindle Travel (In.)	6
Spindle Distance to Base (In.)	44-1/2
Spindle Distance to Table (Max.) (In.)	25-3/4
Table Size (L x W) (In.)	15 x 18
Table Travel (In.)	16-3/4
T-Slots Number and Size (In.)	2 & 1/2
T-Slot Centers (In.)	5-5/16
Work Table Weight Capacity (Lbs.)	90



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE