

# VBS-3612, 36" VERTICAL BANDSAW

414470

The line of JET Vertical Bandsaws offers machine and fabrication professionals all the power and precision in a package that meets their individual specifications. An exclusive gear box design permits variety of cutting applications. Features you've come to expect, backed by the industry-leading JET Two Year Warranty



## FEATURES

- Heavy-duty bandsaw, can handle large production pieces on its extra large twin tables
- Three wheel system for cutting wide pieces
- Two-Speed transmission and variable speed allow for a wide range of blade speeds
- Heavy-duty, completely enclosed steel frame
- Multi-tilting worktables
- Easy to read blade tension indicator
- Bi-Metal blade welder, grinder and cutter
- Worklamp
- Chip blower
- Blade and tire cleaning brush
- Rip Fence
- Set of tools
- 1/4" x 14/18VT Bi-Metal blade



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# VBS-3612, 36" VERTICAL BANDSAW

414470

## SPECIFICATIONS

Blade Speeds (SFPM)	50 - 4,925
Height Capacity (Max.) (In.)	12
Throat Capacity (In.)	36
Table Size (L x W) (In.)	23-5/8 x 27-1/2, 17-3/4 x 27-1/2
Table Tilt (Deg.)	10 L, 45 R
Blade Length (In.)	197
Blade Width (Min.-Max.) (In.)	1/8 - 1
Table Height (In.)	40
Motor (HP)	3 HP, 230/460V, 3Ph
Overall Dimensions (L x W x H) (In.)	69 x 32 x 81
Weight (Lbs.)	1,760



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE