

18"

HIGH VELOCITY FAN



standard
YM - YOKE MOUNT

additional mounting options:



PS - Pedestal Stroller



CW - Column Wall



TC - Truck Cooler



RM - Rack Mount



PB - Pedestal Base

Shipping Weights:

94 lbs/ 43 kg

78 lbs/ 35 kg

72 lbs/ 33 kg

64 lbs/ 29 kg

69 lbs/ 31 kg

SIZE	CFM	HP	FAN DIMENSIONS			DISTANCE AIR THROW	SHIPPING WEIGHT
			W	D	I.D.		
18"	3800	1/2	24"	16"	19.125"	80' / 24 m	56 lbs/ 25 kg

Propeller: 17" Diameter, 3 Blade GalvAlum (33 Degree)
Fan Inlet/Outlet: High Impact Polypropylene
Finger Guards: OSHA Standard, Spiral Wound Steel
RPM: 1725
Decibels: 71.2 @ 20'

Enclosure: TEAO Standard
Frame: 56
Ambient Temperature: 40C
Duty Cycle: Continuous
Power Cord (115V Only): 12' Length
Coverage: 2700 Sq.Ft. Max
Warranty: 2 Years

Voltage	Motor Amps	Running Amps
115V/ 208-230V*	6.0/ 3.0-2.9	5.9/ 2.9-2.8
208-230/ 460V	2.11-1.91/ .96	2.0-1.8/ .9
277V	1.85	1.75

*standard

