



SharkBite® Ball Valve

DESCRIPTION

The SharkBite® Ball Valves are high quality forged brass ball valves with SharkBite connections. The SharkBite connections allow the user to connect the ball valves to copper tubing, CPVC, PEX and PE-RT in seconds with relative ease.

FEATURES AND BENEFITS

- Convenient single lever control:
Makes them easy to use and encourages shut-off of water supply.
- Full Port Ball Valve:
Allows water to flow freely through valve.
- Instant push-to-connect connections for increased ease of use:
No soldering, clamps, unions, or glue required.
- Valve assembled to strict quality standards:
Measured thread engagement, measured torque.



22222-0000LF

SPECIFICATION DATA

Performance:



Maximum pressure 200 psi
 Maximum temperature 200°F (water)
 Service Water

Ball Valve Materials:

Body DZR Lead Free Brass
 Seat Ring PTFE
 Ball Brass, chrome plated
 Body End Retainer Brass
 Stem Brass
 O-ring EPDM
 Packing PTFE
 Packing Nut Brass
 Handle Zinc plated steel
 Handle Nut Zinc plated steel

SharkBite Materials:

Body DZR Lead Free Brass
 O-ring EPDM
 Grab Ring Stainless steel
 Tube support liner Polysulfone



Dimensions	A	B
1/2" (22222-0000LF)	3.06"	3.70"
3/4" (22185-0000LF)	3.62"	3.70"
1" (22223-0000LF)	4.40"	4.66"

Dimensions	A	B
1/2" (22182-0000LF)	4.75"	3.70"
1/2" SB X 1/2" FNTP		
3/4" (22186-0000LF)	5"	3.70"
3/4" SB X 3/4" FNTP		
1" (22187-0000LF)	6"	4.66"
1" SB X 1" FNPT		

AVAILABLE CONNECTIONS

SharkBite 1/2" through 1"

CERTIFICATIONS

The SharkBite Ball Valve 1/2", 3/4" and 1" are certified to IGC-157-2013, NSF/ANSI 61, NSF/ASNI 372 and listed by IAPMO.

