

SAFETY DATA SHEET

1. Identification

Product number 1000013157
Product identifier **Tap Magic Multi-Purpose Cleaner/Degreaser**
Company information THE STECO CORPORATION
2330 CANTRELL ROAD
LITTLE ROCK, AR 72202 United States
www.tapmagic.com
Company phone General Assistance 1-501-375-5644
Emergency telephone US 1-800-255-3924
Emergency telephone outside US 1-813-248-0585
Version # 01
Recommended use Cleaner
Recommended restrictions None known.

2. Hazard(s) identification

Physical hazards Gases under pressure Liquefied gas
Health hazards Serious eye damage/eye irritation Category 2A
OSHA defined hazards Not classified.

Label elements



Signal word Warning
Hazard statement Contains gas under pressure; may explode if heated. Causes serious eye irritation.
Precautionary statement
Prevention Wash thoroughly after handling. Wear eye protection/face protection.
Response If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Storage Protect from sunlight. Store in a well-ventilated place.
Disposal Dispose of waste and residues in accordance with local authority requirements.
Hazard(s) not otherwise classified (HNOC) None known.
Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
2-Butoxyethanol		111-76-2	2.5 - 10
Butane		106-97-8	1 - 2.5
EDTA Tetrasodium Salt		64-02-8	1 - 2.5
Isopropyl Alcohol		67-63-0	1 - 2.5
N-Alkyl-N,N-Dimethyl-N-Benzylammonium Chloride		68391-01-5	0.1 - 1
Propane		74-98-6	0.1 - 1
Other components below reportable levels			80 - 90

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	Not likely, due to the form of the product. In the unlikely event of swallowing contact a physician or poison control center. Rinse mouth.
Most important symptoms/effects, acute and delayed	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Do not move cargo or vehicle if cargo has been exposed to heat. Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.
Specific methods	Cool containers exposed to flames with water until well after the fire is out.
General fire hazards	Contents under pressure. Pressurized container may explode when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Refer to attached safety data sheets and/or instructions for use. Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Isolate area until gas has dispersed. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Ground and bond containers when transferring material. Close valve after each use and when empty. Protect cylinders from physical damage; do not drag, roll, slide, or drop. When moving cylinders, even for short distances, use a cart (trolley, hand truck, etc.) designed to transport cylinders. Suck back of water into the container must be prevented. Do not allow backfeed into the container. Purge air from system before introducing gas. Use only properly specified equipment which is suitable for this product, its supply pressure and temperature. Contact your gas supplier if in doubt. Do not re-use empty containers. Do not get in eyes, on skin, or on clothing. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.

Conditions for safe storage, including any incompatibilities

Level 1 Aerosol.

Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Cylinders should be stored upright, with valve protection cap in place, and firmly secured to prevent falling or being knocked over. Stored containers should be periodically checked for general condition and leakage. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
2-Butoxyethanol (CAS 111-76-2)	PEL	240 mg/m3
Isopropyl Alcohol (CAS 67-63-0)	PEL	50 ppm 980 mg/m3
Propane (CAS 74-98-6)	PEL	400 ppm 1800 mg/m3 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
2-Butoxyethanol (CAS 111-76-2)	TWA	20 ppm
Butane (CAS 106-97-8)	STEL	1000 ppm
Isopropyl Alcohol (CAS 67-63-0)	STEL	400 ppm
	TWA	200 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
2-Butoxyethanol (CAS 111-76-2)	TWA	24 mg/m3
Butane (CAS 106-97-8)	TWA	5 ppm 1900 mg/m3 800 ppm
Isopropyl Alcohol (CAS 67-63-0)	STEL	1225 mg/m3
	TWA	500 ppm 980 mg/m3 400 ppm
Propane (CAS 74-98-6)	TWA	1800 mg/m3 1000 ppm

Biological limit values

ACGIH Biological Exposure Indices

Components	Value	Determinant	Specimen	Sampling Time
2-Butoxyethanol (CAS 111-76-2)	200 mg/g	Butoxyacetic acid (BAA), with hydrolysis	Creatinine in urine	*
Isopropyl Alcohol (CAS 67-63-0)	40 mg/l	Acetone	Urine	*

* - For sampling details, please see the source document.

Exposure guidelines

US - California OELs: Skin designation

2-Butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

US - Minnesota Haz Subs: Skin designation applies

2-Butoxyethanol (CAS 111-76-2) Skin designation applies.

US - Tennessee OELs: Skin designation

2-Butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

US NIOSH Pocket Guide to Chemical Hazards: Skin designation

2-Butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

2-Butoxyethanol (CAS 111-76-2) Can be absorbed through the skin.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove supplier.

Other Wear suitable protective clothing.

Respiratory protection If permissible levels are exceeded use NIOSH mechanical filter / organic vapor cartridge or an air-supplied respirator.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Gas.

Form Aerosol. Liquefied gas.

Color Not available.

Odor Not available.

Odor threshold Not available.

pH Not available.

Melting point/freezing point Not available.

Initial boiling point and boiling range 212 °F (100 °C) estimated

Flash point -156.0 °F (-104.4 °C) Propellant estimated

Evaporation rate Not available.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	60 - 75 psig @70F estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	473 °F (245 °C) estimated
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Flame extension	0 in estimated
Oxidizing properties	Not oxidizing.
Specific gravity	0.985 estimated
VOC (Weight %)	7.9 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Heat. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	No adverse effects due to inhalation are expected.
Skin contact	2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans.
Eye contact	Causes serious eye irritation.
Ingestion	Expected to be a low ingestion hazard.
Symptoms related to the physical, chemical and toxicological characteristics	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity

Components	Species	Test Results
2-Butoxyethanol (CAS 111-76-2)		
Acute		
Dermal		
LD50	Guinea pig	7.3 ml/kg, 4 Days 0.23 ml/kg, 24 Hours
	Rabbit	435 mg/kg, 24 Hours 0.68 ml/kg, 24 Hours

Components	Species	Test Results
		0.63 ml/kg
	Rat	> 2000 mg/kg, 24 Hours
Inhalation		
LC50	Rabbit	400 ppm, 7 Hours
	Rat	450 ppm, 4 Hours
Oral		
LD100	Rabbit	695 mg/kg
LD50	Dog	> 695 mg/kg
	Guinea pig	1414 mg/kg
	Mouse	1519 mg/kg
	Rat	1746 mg/kg
Butane (CAS 106-97-8)		
Acute		
Inhalation		
LC50	Mouse	1237 mg/l, 120 Minutes
		52 %, 120 Minutes
	Rat	1355 mg/l
EDTA Tetrasodium Salt (CAS 64-02-8)		
Acute		
Oral		
LD50	Rat	1658 mg/kg
Isopropyl Alcohol (CAS 67-63-0)		
Acute		
Dermal		
LD50	Rabbit	16.4 ml/kg, 24 Hours
Inhalation		
LC50	Rat	> 10000 ppm, 6 Hours
Oral		
LD50	Rat	5.84 g/kg
Propane (CAS 74-98-6)		
Acute		
Inhalation		
LC50	Mouse	1237 mg/l, 120 Minutes
		52 %, 120 Minutes
	Rat	1355 mg/l
		658 mg/l/4h

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation Causes serious eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

2-Butoxyethanol (CAS 111-76-2)

3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure Not applicable.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not likely, due to the form of the product.

Chronic effects May be harmful if absorbed through skin.

2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components		Species	Test Results
2-Butoxyethanol (CAS 111-76-2)			
Aquatic			
Fish	LC50	Inland silverside (Menidia beryllina)	1250 mg/l, 96 hours
EDTA Tetrasodium Salt (CAS 64-02-8)			
Aquatic			
Algae	IC50	Algae	1.01 mg/L, 72 Hours
Fish	LC50	Bluegill (Lepomis macrochirus)	472 - 500 mg/l, 96 hours
Isopropyl Alcohol (CAS 67-63-0)			
Aquatic			
Algae	IC50	Algae	1000.0001 mg/L, 72 Hours
Crustacea	EC50	Daphnia	13299 mg/L, 48 Hours
Fish	LC50	Bluegill (Lepomis macrochirus)	> 1400 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

2-Butoxyethanol	0.83
Butane	2.89
Isopropyl Alcohol	0.05
Propane	2.36

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste disposal company.

Waste from residues / unused products Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.

14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, flammable, (each not exceeding 1 L capacity)
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.
Special provisions	N82
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

This product meets the exception requirements of section 173.306 as a limited quantity and may be shipped as a limited quantity. Until 12/31/2020, the "Consumer Commodity - ORM-D" marking may still be used in place of the new limited quantity diamond mark for packages of UN 1950 Aerosols. Limited quantities require the limited quantity diamond mark on cartons after 12/31/20 and may be used now in place of the "Consumer Commodity ORM-D" marking and both may be displayed concurrently.

IATA

UN number	UN1950
UN proper shipping name	Aerosols, flammable
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Environmental hazards	No.
ERG Code	10L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.

Other information

Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.
Packaging Exceptions	LTD QTY

IMDG

UN number	UN1950
UN proper shipping name	AEROSOLS
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Environmental hazards	
Marine pollutant	No.
EmS	F-D, S-U
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.

Packaging Exceptions	LTD QTY
-----------------------------	---------

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

DOT



IATA; IMDG



General information

Avoid transport on vehicles where the load space is not separated from the driver's compartment. Ensure vehicle driver is aware of the potential hazards of the load and knows what to do in the event of an accident or an emergency. Before transporting product containers: Ensure that containers are firmly secured. Ensure cylinder valve is closed and not leaking. Ensure valve outlet cap nut or plug (where provided) is correctly fitted. Ensure valve protection device (where provided) is correctly fitted. Ensure adequate ventilation. Ensure compliance with applicable regulations.

15. Regulatory information

US federal regulations

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - Yes
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.
2-Butoxyethanol	111-76-2	2.5 - 10

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Butane (CAS 106-97-8)
Propane (CAS 74-98-6)

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

2-Butoxyethanol (CAS 111-76-2)

Butane (CAS 106-97-8)

Isopropyl Alcohol (CAS 67-63-0)

US. Massachusetts RTK - Substance List

2-Butoxyethanol (CAS 111-76-2)

Butane (CAS 106-97-8)

Isopropyl Alcohol (CAS 67-63-0)

Propane (CAS 74-98-6)

US. New Jersey Worker and Community Right-to-Know Act

2-Butoxyethanol (CAS 111-76-2)

Butane (CAS 106-97-8)

Isopropyl Alcohol (CAS 67-63-0)

Propane (CAS 74-98-6)

US. Pennsylvania Worker and Community Right-to-Know Law

2-Butoxyethanol (CAS 111-76-2)

Butane (CAS 106-97-8)

Isopropyl Alcohol (CAS 67-63-0)

Propane (CAS 74-98-6)

US. Rhode Island RTK

Butane (CAS 106-97-8)

Isopropyl Alcohol (CAS 67-63-0)

Propane (CAS 74-98-6)

US. California Proposition 65

WARNING: This product contains a chemical known to the State of California to cause cancer.

US - California Proposition 65 - CRT: Listed date/Carcinogenic substance

Dimethylnitrosoamine (CAS 62-75-9)

Listed: October 1, 1987

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	Yes
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 10-07-2016

Version # 01

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Revision information

Product and Company Identification: Alternate Trade Names