

Model Number:

T10035

Long Description:

Torin Big Red T10035 3.5-Gallon Benchtop Bio-Aqueous Parts Washer: Portable Mechanic Garage Parts Cleaner, Electric Pump 110 Volt, Red

Short Description:

Torin Big Red T10035 3.5-Gallon Benchtop Bio-Aqueous Parts Washer

Core Bullets

- Designed to work with water-based cleaning solutions
- Use with non-flammable water-based degreaser or cleaning agent
- Electric pump operates at 264 Gallons/Hour - 4 Gallons/Minute
- Steel work basin is 18.5 inches wide x 14.17 inches deep and 9.84 inches high.
- Lid includes fusible Link for fire safety

Long Description:

The Torin Big Red Benchtop Bio-Aqueous Parts Washer with 3.5-gallon fluid reservoir, is the perfect solution for small parts cleaning in the shop or garage. The super handy bench top unit fits almost anywhere, and is great for most cleaning jobs, wheel bearings, gears and carburetors. The pump recycles at 1/2 gallons per minute. Steel work basin is 18 inches wide x 13.5 inches deep and 9 inches high. Lid includes fusible Link for fire safety. A rugged high-grade steel frame is teamed with a lead-free paint finish that covers the entire surface to ensure long-lasting wear and help prevent rust. The paint is oil, grease, and dirt-resistant for easy cleanup no matter how often you put this jack to work.

The TORIN BIG RED Mobile Parts Washer is completely portable so that you can bring the washer to the parts. Features Lid includes fusible Link for fire safety, high side walls to prevent cleaner from leaking or spilling out during transport. Built-in 110/120-volt pump can handle 4 GPM. Includes a built-in screen and a 4-gallon solution capacity.

Bio-Aqueous parts washers give cleaning power that is safe and biodegradable. **Bio-aqueous parts washer cleaning chemistry is safe for workers, safe for the environment and unmatched in aqueous cleaning performance.** This unit is approved for use with biodegradable cleaners. Do not use with high volatile, flammable or combustible solvents. Durable steel cabinet construction and is UL/CSA approved. This unit is 100% factory tested for reliability to meet safety standards.

Features + Benefits

- Designed to work with water-based cleaning solutions
- Use with non-flammable water-based degreaser or cleaning agent
- Electric pump operates at 264 Gallons/Hour - 4 Gallons/Minute

- Steel work basin is 18 inches wide x 13.5 inches deep and 9 inches high.
- Lid includes fusible Link for fire safety
- Comes with a component shelf
- Tanks are made of powder coated 20-gauge Steel for durability and rust resistance
- Lead-free paint is applied after a thorough chemical wash to ensure a long-lasting finish and to help prevent rust
- Paint is oil, grease, and dirt-resistant for easy cleanup
- No VOC permit required (most locations)
- Non-toxic
- Non-flammable
- Biodegradable
- Effectively cleans a variety of soils, oils and greases
- Safe on all metal and most plastic surfaces
- Rust and corrosion inhibiting ingredients
- Built in ISO certified facilities and engineered using the same systems as Aerospace Technologies and the Automotive OEM sector
- This unit is 100% factory tested for reliability and safety to meet safety standards

What's included:

(1) Jack

(1) Handle

(1) Manual

(1) Additional what's included items

Key Specs

Capacity (gallon)	3.5
Min. Solution Capacity (gallon)	2
Max. Solution Capacity (gallon)	4
Pump Output (gallon min./hr)	4 / 264
Power Supply (VAC)	115
Operation	Electric
Handle Included	Yes
Manufacturer's Warranty	1 Year Limited Warranty
Product Dimension W (in.)	18.5
Product Dimension D (in.)	14.17
Product Dimension H (in.)	9.84
GW (lbs.)	16.53

Safety Warning:

- **WARNING:** This product contains one or more chemicals known to the state of California to cause cancer and birth defects or other reproductive harm, including DEHP, a phthalate chemical. Wash hands thoroughly after handling.

Notice:

- **Illustrations or images provided are a convenient reference, the manufacturer reserves the rights to make design changes and or improvements to product lines, color, and manuals without notice.**

Safety Messages:

WARNING!

1. Read, study and follow all instructions before assembling or operating this device.
2. Failure to heed these instructions may result in personal injury and/or property damage.
3. DO NOT EXCEED MAXIMUM CAPACITY.
4. This product is designed for use on hard, level surfaces capable of sustaining the load.
5. Alterations shall not be made to this product because of the dangers associated to the misuse of this product.
6. If product is not operating properly, or parts are loose, missing, or broken, stop use of product immediately.

Failure to heed these warnings may result in personal injury and/or prop