

# NPP-4840-FP-E6OD-FDA

## 48x40 (Standard) Plastic Industrial Pallet



### Technical Data

Dimensions	48x40x6.1 inches (1219x1016x155 mm)
Weight	34.0 lbs
<b>Load Capacities</b>	
Static	8800 lbs
Dynamic	4400 lbs
Racking	2200 lbs
Entry	4-way
Pallets per Stack	18
Truckload Qty	540

Available in Truckload or LTL quantities. Minimum quantity required. We reserve the right to change any stated information without prior notice. Not responsible for typographical errors.

### Materials and Colors

**Condition**  
New

**Material** HDPP (Recycled)      **Color** Black (custom colors available)

### Deck Specs

**Top Deck**  
Ventilated

**Bottom Deck**  
6-Runner

**Available Options:**  
RFID Transponders  
Individual Markings  
Anti-Slip Bottom Grommets  
ESD Prevention for Anti-Static  
FDA Version with Freezer Additives  
Rod Inserts for Increased Performance.


### Handling Data

<b>Nestable</b> No	<b>Reusability</b> Multi-Trip	<b>ISPM-15 Exempt</b> Yes
<b>Stackable</b> Yes	<b>Destination</b> Captive	<b>Food Grade</b> FDA Approved
<b>Rackable</b> Yes	<b>Airfreight</b> Yes	<b>Pharmaceutical</b> Yes

### Features

Ideal for closed loops or distribution chains across industry sectors including Food, Retail, Medical and Pharmaceutical.

- High performance at low cost
- Top Safety Rim
- Open deck flow-thru design
- Allows for safe double stacking
- Low-cost Plastic Pallet
- Impervious to acids, fats, solvents and odors
- Resists water absorption & bacteria growth
- Inert to infestation, mold and mildew
- Consistently dimensionally accurate
- Exempt from ISPM 15 shipping regulations



### DECK & BOTTOM SUPPORT OPTIONS

Open or Closed Deck

3 Runner or 6 Runner



**Your Sales Rep**  
Mike Cunneen  
mcunneen@nelsoncompany.com  
M 804.307.1474

**Nelson™**

The Nelson Company

[www.NelsonCompany.com](http://www.NelsonCompany.com)

[www.NelsonTechCenter.com](http://www.NelsonTechCenter.com)