

NPP-4840-FP-E60D

48x40 (Standard) Plastic Industrial Pallet



Technical Data

Dimensions	48x40x6.1 inches (1219x1016x155 mm)
Weight	34.0 lbs
Load Capacities	
Static	8800 lbs
Dynamic	4400 lbs
Racking	2200 lbs
Entry	4-way
Pallets per Stack	18
Truckload Qty	540

Available in Truckload or LTL quantities. Minimum quantity required. We reserve the right to change any stated information without prior notice. Not responsible for typographical errors.

Handling Data

Nestable No	Reusability Multi-Trip	ISPM-15 Exempt Yes
Stackable Yes	Destination Captive	Food Grade Yes, non-FDA
Rackable Yes	Airfreight Yes	Pharmaceutical Yes



DECK & BOTTOM SUPPORT OPTIONS

Open or Closed Deck

3-Runner or 6-Runner



Materials and Colors

Condition
New

Material HDPP (Recycled) **Color** Black (custom colors available)

Deck Specs

Top Deck
Ventilated

Bottom Deck
6-Runner

Available Options:
RFID Transponders
Individual Markings
Anti-Slip Bottom Grommets and Top Safety Rim
ESD Prevention for Anti-Static
FDA Version with Freezer Additives
Rod Inserts for Increased Performance.

Features

Ideal for closed loops or distribution chains across industry sectors including Food, Retail, Medical and Pharmaceutical.

- High performance at low cost
- Open deck flow-thru design
- Allows for safe double stacking
- Low-cost Plastic Pallet
- Easy-to-clean hygienic design
- Suitable for packaged food items
(not approved for direct food contact)
- Impervious to acids, fats, solvents and odors
- Resists water absorption & bacteria growth
- Inert to infestation, mold and mildew
- Consistently dimensionally accurate
- Exempt from ISPM 15 shipping regulations

Nelson™

The Nelson Company

(410) 477-3000 x110

plastic@NelsonCompany.com

www.NelsonCompany.com

www.NelsonTechCenter.com