

PS500

Compact Light Weight Floor Scale

CE



Shown with optional floor stand

- **Accuracy**– 0.2% of full capacity
- **Capacity**– 250 kg / 500 lb
- **Construction**– Low profile stainless steel platform with mild steel understructure and stainless steel/ABS indicator and a rubber slip mat
- **Functions**– lb, kg and lb/oz weighing modes, weight hold feature, stable weight indication and auto power off to extend battery life
- **Protocol**– Standard NCI interfaces to most common shipping software, including UPS™ Worldship Online and FedEx®. Not legal for trade
- **Display**– Five 16 mm / 0.625" digits LCD
- **Power**– Battery or AC power (included)
- **Operator Keys**– On/Off/Zero, Tare, Units (lb/kg), Hold/Print
- **Options**– Floor and table top stands for the weight indicator
- **Animal Weighing Software**

VALUE IN
WEIGHING

PS500 Compact Light Weight Floor Scale

Specifications

Capacity:

250 kg x 0.1 kg / 500 lb x 0.2 lb / 500 lb x 5 oz

Dimension:

Platform: 559 mm (L) x 559 mm (W) x 51 mm (H)
22" L x 22" W x 2" H

906 mm (L) x 559 mm (W) x 51 mm (H)
36" L x 22" W x 2" H

1067 mm (L) x 559 mm (W) x 51 mm (H)
42" L x 22" W x 2" H

Indicator: 164 mm (L) x 81 mm (H) x 29 mm (W)
6.5" L x 3.2" H x 1.2" W

Indicator Features:

Display: Five 16 mm / 0.625" digits LCD

RS-232:10' interface cable (DB-9) (included)

Keyboard: Hold/Print, Units, Tare, On/Off/Zero

Units: lb, kg, lb/oz

Power: Four AAA batteries or 6 VDC, 500mA
adapter (both included)

Optional UK Power Adapter: 816965002887

Optional EU Power Adapter: 816965002870

Battery Life: 20 hours

Operating Temperature:

5° C to 35° C / 41° F to 95° F

Packaging Dimension:

Scale: 660 mm (L) x 609 mm (W) x 101 mm (H)
26" L x 24" W x 4" H

965 mm (L) x 609 mm (W) x 101 mm (H)
39" L x 24" W x 4" H

1117 mm (L) x 609 mm (W) x 101 mm (H)
44" L x 24" W x 4" H

Shipping Weight:

16 kg / 35 lb - 607 mm / 22"

26 kg / 57 lb - 914 mm / 36"

29 kg / 63 lb - 1067 mm / 42"

Options (not included):

Floor Stand: 816965002061

350 mm (L) x 350 mm (W) x 25 mm (H)

13.8" L x 13.8" W x 1" H

overall height 940 mm / 37"

weight 4.5 kg / 10 lb

Certifications: Full FCC compliance, UL/CUL power adapter

Product Code:

816965001903: 22" x 22"

816965001897: 22" x 36"

816965001453: 22" x 42"



Shown with optional floor stand



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031
Toll free: 800-637-0529, Tel: 507-238-8702
Fax: 507-238-8271
e-mail: sales@brecknellscales.com
www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick
West Midlands B66 2LP UK
Tel: +44 (0) 845 246 6717
Fax: +44 (0) 845 246 6718
Email: sales@brecknellscales.co.uk
www.brecknellscales.co.uk

