



## SAFETY DATA SHEET

### SECTION I: PRODUCT & COMPANY IDENTIFICATION

**PRODUCT NAME:** GRAN-SORB

**Distribution Location:**

Chemtex, Inc.

1 Front Street

Cumberland RI 02864

**Customer Service Telephone Number:** 1-401-305-3030

**Emergency phone number:** 1-877-431-0200

**Date Prepared:** 01/28/2015

### SECTION II: HAZARDOUS IDENTIFICATION



NATIONAL FIRE PROTECTION ASSOCIATION (NFPA) RATING:

HEALTH:	0
FLAMMABILITY:	1
REACTIVITY:	0

\*Not considered a hazardous material at temperatures below melting point. Not considered a controlled substance or a carcinogen

### SECTION III: COMPOSITION/INFORMATION ON INGREDIENTS

<b><u>CAS Registry #</u></b>	<b><u>Component</u></b>
9004-34-6	Paper Fiber
1332-58-7	Kaolin
471-34-1	Calcium Carbonate
13463-67-7	Titanium Dioxide

(NOTE: See Section 8 of this MSDS for Exposure Guidelines)

#### **SECTION IV: FIRST AID MEASURES**

EYE CONTACT: Use eyewash, consult physician if accompanied by pain or irritation.  
SKIN CONTACT: Wash irritated area with mild soap and water  
INHALATION: N/A  
INGESTION: N/A

#### **SECTION V: FIRE FIGHTING MEASURES**

Flash Point: not available  
Flammable Limits: lower- N/A upper-N/A  
Auto-ignition Temperature: 220 °C  
Extinguishing Media: Water spray, ABC dry chemical, foam, sand, or carbon dioxide. Use water fog or spray to cool exposed equipment and containers.  
Special Fire Fighting Procedures: Use water to wet down material and to reduce the likelihood of ignition or dispersion of dust into the air. For large fires or fires in confined areas, full emergency equipment with self-contained breathing apparatus and full protective clothing should be used. Thermal decomposition of this product may produce carbon monoxide and carbon dioxide gases.

#### **SECTION VI: ACCIDENTAL RELEASE MEASURES**

Avoid breathing dust. Unused material can be shoveled, swept, or vacuumed and recycled for use. Avoid generating airborne dust.

If used material is released or spilled, see Section 13.

#### **SECTION VII: HANDLING AND STORAGE**

Store in dry area to avoid unwanted hydration. When used, transport in accordance with local, state and federal regulations.

#### **SECTION VIII: EXPOSURE CONTROLS/ PERSONAL PROTECTION**

VENTILATION: Use local exhaust to control possible air borne material.  
PROTECTIVE GLOVES: Recommended for prolong exposure.  
EYE PROTECTION: Safety glasses with side shields are recommended as a good practice for industrial safety.  
OTHER PROTECTIVE EQUIPMENT (SPECIFY): None Required

#### **SECTION IX: PHYSICAL AND CHEMICAL PROPERTIES**

APPEARANCE AND ODOR: Typically gray with musty odor  
BOILING POINT (C): N/A  
MELTING POINT (C): N/A  
SOLUBILITY IN WATER: N/A  
EVAPORATION RATE: N/A  
VAPOR PRESSURE (mm Hg): N/A  
VAPOR DENSITY (Air = 1): N/A  
EXPLOSIVE PROPERTIES: N/A

**SECTION X: STABILITY AND REACTIVITY**

GENERAL: Stable  
CONDITIONS OF REACTIVITY: N/A  
INCOMPATIBLE MATERIALS: N/A  
CONDITION TO AVOID: N/A  
HAZARDOUS DECOMPOSITION: N/A  
HAZARDOUS POLYMERIZATION: Will not occur

**SECTION XI: TOXICOLOGICAL INFORMATION**

This product is not listed by NTP or IARC. See Section 15.

**SECTION XII: ECOLOGICAL INFORMATION**

No data available

**SECTION XIII: DISPOSAL CONSIDERATIONS**

This product in itself is considered to be non-hazardous as defined by RCRA (40 CFR 261). Once used, this product will take on the characteristics of the chemical sorbed and should be disposed of accordingly. Disposal of this product (used or unused) must be in compliance with all local, state, and federal regulations.

**SECTION XIV: TRANSPORT INFORMATION**

This product is not a DOT Hazardous Material and is not regulated for all shipping purposes.

**SECTION XV: REGULATORY INFORMATION**

CERCLA (Comprehensive Environmental Response Compensation and Liability Act):	Not reportable quantity
OSHA Hazard Communications Standard, 29 CFR 1910.1200:	No listed ingredient
SARA Title III (Superfund Amendments and Reauthorization Act):	No listed ingredient
TSCA (Toxic Substances Control Act):	All ingredients are listed

**SECTION XVI: OTHER INFORMATION**

NFPA Hazard Rating:	none – extreme	Health:	0	Reactivity:	0
	0 - 4	Fire:	1		

For more information:  
Phone (877) 431-0200 - Fax (401) 305-3030  
[www.chemtexinc.com](http://www.chemtexinc.com)