



SAFETY DATA SHEET

Issue Date 09-Jan-2017

Revision Date 09-Jan-2017

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Formula 429 Floor Cleaner & Bacterial Grease Eliminator

Other means of identification

Product Code NL429

Synonyms None

Details of the supplier of the safety data sheet

Company Name Nyco Products Company
5332 Dansher Road
Countryside, IL 60525
(708) 579-8100
nycoproducts.com

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Serious eye damage/eye irritation	Category 2A

Label elements

Emergency Overview

Warning

Hazard statements

Causes serious eye irritation



Appearance Slightly hazy Green

Physical state Liquid

Odor Pleasant

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

Immediately call a POISON CENTER or doctor/physician

Specific Treatment (See Section 4 on the SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

If eye irritation persists: Get medical advice/attention

Hazards not otherwise classified (HNOC)

Other Information

- Harmful to aquatic life

Unknown Acute Toxicity

2% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Alcohol Ethoxylate	68439-46-3	1-5	*
Viable Bacterial Cultures	Proprietary	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Skin Contact

Wash off immediately with plenty of water. Wash skin with soap and water.

Eye contact

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Inhalation

Remove to fresh air.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms

Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians

Contains Viable Bacterial Cultures classified as Risk Group 1.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No Information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-(2-methoxypropoxy)propano 34590-94-8	STEL: 150 ppm TWA: 100 ppm S*	TWA: 100 ppm TWA: 600 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 600 mg/m ³ (vacated) STEL: 150 ppm (vacated) STEL: 900 mg/m ³ (vacated) S*	IDLH: 600 ppm TWA: 100 ppm TWA: 600 mg/m ³ STEL: 150 ppm STEL: 900 mg/m ³
Sodium Hydroxide 1310-73-2	Ceiling: 2 mg/m ³	TWA: 2 mg/m ³ (vacated) Ceiling: 2 mg/m ³	IDLH: 10 mg/m ³ Ceiling: 2 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be

required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene

Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Slightly hazy Green
Color	Green
Odor	Pleasant
Odor threshold	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	9.0-10.0	
Specific Gravity	1.0	
Viscosity	<25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range		
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.34
VOC Content (%)	3

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Extremes of temperature and direct sunlight.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

- Inhalation** Avoid breathing vapors or mists. May cause irritation of respiratory tract.
- Eye contact** Avoid contact with eyes. Direct contact may cause serious eye irritation.
- Skin Contact** Avoid contact with skin. Prolonged contact with skin may result in the absorption of potentially harmful amounts leading to possible liver and kidney damage.
- Ingestion** Do not taste or swallow. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Alcohol Ethoxylate 68439-46-3	= 1378 mg/kg (Rat) = 1400 mg/kg (Rat)	> 2 g/kg (Rabbit)	-

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

- Sensitization** No Information available.
- Germ cell mutagenicity** No Information available.
- Carcinogenicity** No Information available.
IARC (International Agency for Research on Cancer)
Group 2A - Probably Carcinogenic to Humans
OSHA (Occupational Safety and Health Administration of the US Department of Labor)
X - Present
- Reproductive toxicity** No Information available.
- STOT - single exposure** No Information available.
- STOT - repeated exposure** No Information available.
- Target organ effects** Central nervous system, EYES, Respiratory system.
- Aspiration hazard** No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 2% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

- ATEmix (oral)** 16,709.00
- ATEmix (dermal)** 60,080.00

12. ECOLOGICAL INFORMATION

Ecotoxicity

2.3% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-(2-methoxypropoxy)propano 34590-94-8	-	10000: 96 h Pimephales promelas mg/L LC50 static	1919: 48 h Daphnia magna mg/L LC50
Tetrasodium EDTA 64-02-8	1.01: 72 h Desmodosmus subspicatus mg/L EC50	41: 96 h Lepomis macrochirus mg/L LC50 static 59.8: 96 h Pimephales promelas mg/L LC50 static	610: 24 h Daphnia magna mg/L EC50
Sodium Hydroxide 1310-73-2	-	45.4: 96 h Oncorhynchus mykiss mg/L LC50 static	-
Trisodium nitrilotriacetate 5064-31-3	560 - 1000: 96 h Chlorella vulgaris mg/L EC50	93 - 170: 96 h Pimephales promelas mg/L LC50 flow-through 560 - 1000: 96 h Oryzias latipes mg/L LC50 semi-static 470: 96 h Pimephales promelas mg/L LC50 static 560 - 1000: 96 h Poecilia reticulata mg/L LC50 114: 96 h Pimephales promelas mg/L LC50 252: 96 h	560 - 1000: 48 h Daphnia magna mg/L LC50

		Lepomis macrochirus mg/L LC50 72 - 133: 96 h Oncorhynchus mykiss mg/L LC50 static 175 - 225: 96 h Lepomis macrochirus mg/L LC50 static 560 - 1000: 96 h Poecilia reticulata mg/L LC50 semi-static 560 - 1000: 96 h Oryzias latipes mg/L LC50	
--	--	--	--

Persistence and degradability

No Information available.

Bioaccumulation

No Information available.

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

Not regulated

TDG

Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA

Complies

DSL/NDSL

Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-(2-methoxypropoxy)propano - 34590-94-8	1.0

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No

Sudden release of pressure hazard No
 Reactive Hazard No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-(2-methoxypropoxy)propano 34590-94-8	X	X	X
Sodium Hydroxide 1310-73-2	X	X	X
Trisodium nitrilotriacetate 5064-31-3	-	X	-

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 2	Flammability 0	Instability 0	Physical and Chemical Properties Yes Personal protection B
HMIS	Health hazards 2	Flammability 0	Physical hazards 0	

Issue Date 09-Jan-2017
 Revision Date 09-Jan-2017

Revision Note
 No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet