



# SAFETY DATA SHEET

Issue Date 08-Jul-2016

Revision Date 13-Feb-2015

Version 1

## 1. PRODUCT AND COMPANY IDENTIFICATION

### Product identifier

**Product Name** Liquid Laundry Detergent

### Other means of identification

**Product Code** NL929

**Synonyms** None

### Details of the supplier of the safety data sheet

**Company Name** Nyco Products Company  
5332 Dansher Road  
Countryside, IL 60525  
(708) 579-8100  
nycoproducts.com

### Emergency telephone number

**Emergency Telephone** Chemtrec 1-800-424-9300

## 2. HAZARDS IDENTIFICATION

### Classification

#### **OSHA Regulatory Status**

This product has been classified in accordance with the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified

### Label elements

#### **Emergency Overview**

**Appearance** Clear Blue

**Physical state** Liquid

**Odor** Pleasant

#### **Precautionary Statements - Response**

Immediately call a POISON CENTER or doctor/physician  
Specific Treatment (See Section 4 on the SDS)

### Hazards not otherwise classified (HNOC)

#### Other Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Surfactant Blend	Proprietary	3-7	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

#### 4. FIRST AID MEASURES

##### First aid measures

<b>Skin Contact</b>	Wash off immediately with plenty of water. Wash skin with soap and water.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
<b>Inhalation</b>	Remove to fresh air.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water.

##### Most important symptoms and effects, both acute and delayed

<b>Symptoms</b>	Any additional important symptoms and effects are described in Section 11: Toxicology Information.
-----------------	--

##### Indication of any immediate medical attention and special treatment needed

<b>Note to physicians</b>	Treat symptomatically.
---------------------------	------------------------

#### 5. FIRE-FIGHTING MEASURES

##### Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

##### Specific hazards arising from the chemical

No Information available.

##### Explosion data

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

##### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

#### 6. ACCIDENTAL RELEASE MEASURES

##### Personal precautions, protective equipment and emergency procedures

<b>Personal precautions</b>	Ensure adequate ventilation, especially in confined areas.
-----------------------------	--

##### Environmental precautions

<b>Environmental precautions</b>	See Section 12 for additional ecological information.
----------------------------------	---

##### Methods and material for containment and cleaning up

<b>Methods for containment</b>	Prevent further leakage or spillage if safe to do so.
--------------------------------	---

<b>Methods for cleaning up</b>	Pick up and transfer to properly labeled containers.
--------------------------------	--

#### 7. HANDLING AND STORAGE

##### Precautions for safe handling

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible materials** None known based on information supplied.

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

**Control parameters**

**Exposure Guidelines** This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

**Appropriate engineering controls**

**Engineering Controls** Showers, Eyewash stations & Ventilation systems.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection** Wear safety glasses if handling large volume.

**Skin and body protection** Wear protective gloves and protective clothing if needed. Rubber gloves if prolonged contact is involved.

**Respiratory protection** No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**General Hygiene** Handle in accordance with good industrial hygiene and safety practice.

**9. PHYSICAL AND CHEMICAL PROPERTIES**

**Information on basic physical and chemical properties**

**Physical state** Liquid  
**Appearance** Clear Blue  
**Color** Blue  
**Odor** Pleasant  
**Odor threshold** No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	7.0 - 8.0	
Specific Gravity	1.01	
Viscosity	> 50 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range	100 °C / 212 ° F Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

**Other Information**

**Density Lbs/Gal** 8.41

VOC Content (%) Not Applicable

## 10. STABILITY AND REACTIVITY

### Reactivity

No data available

### Chemical stability

Stable under recommended storage conditions.

### Possibility of Hazardous Reactions

None under normal processing.

### Conditions to avoid

Extremes of temperature and direct sunlight.

### Incompatible materials

None known based on information supplied.

### Hazardous Decomposition Products

None known based on information supplied.

## 11. TOXICOLOGICAL INFORMATION

### Information on likely routes of exposure

<b>Product Information</b>	Maybe harmful by inhalation, ingestion, in contact with eyes and skin,
<b>Inhalation</b>	Inhalation of vapors in high concentration may cause irritation of respiratory system.
<b>Eye contact</b>	Avoid contact with eyes. Contact with eyes may cause irritation.
<b>Skin Contact</b>	Prolonged or repeated contact may dry skin and cause irritation. Repeated or prolonged skin contact may cause allergic reactions with susceptible persons.
<b>Ingestion</b>	May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Surfactant Blend	> 2000 mg/kg ( Rat )	> 2000 mg/kg ( Rat )	-

### Information on toxicological effects

**Symptoms** No Information available.

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

<b>Sensitization</b>	No Information available.
<b>Germ cell mutagenicity</b>	No Information available.
<b>Carcinogenicity</b>	The table below indicates whether each agency has listed any ingredient as a carcinogen.
	<i>IARC (International Agency for Research on Cancer)</i>
	<i>Group 3 -Not classifiable as a human carcinogen</i>
<b>Reproductive toxicity</b>	No Information available.
<b>STOT - single exposure</b>	No Information available.
<b>STOT - repeated exposure</b>	No Information available.
<b>Aspiration hazard</b>	No Information available.

### Numerical measures of toxicity - Product Information

**Unknown Acute Toxicity** 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

<b>ATEmix (oral)</b>	27,778.00
<b>ATEmix (dermal)</b>	39,216.00

**12. ECOLOGICAL INFORMATION**

**Ecotoxicity**

7.83125% of the mixture consists of component(s) of unknown hazards to the aquatic environment

**Persistence and degradability**

No Information available.

**Bioaccumulation**

No Information available.

**Other adverse effects**

No Information available

**13. DISPOSAL CONSIDERATIONS**

**Waste treatment methods**

**Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging**

Do not reuse container.

**14. TRANSPORT INFORMATION**

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT**

Not regulated

**TDG**

Not regulated

**15. REGULATORY INFORMATION**

**International Inventories**

**TSCA**

Complies

**DSL/NDSL**

Complies

**Legend:**

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**US Federal Regulations**

**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

<b>Acute health hazard</b>	No
<b>Chronic Health Hazard</b>	No
<b>Fire hazard</b>	No
<b>Sudden release of pressure hazard</b>	No
<b>Reactive Hazard</b>	No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations**

**California Proposition 65**

This product does not contain any Proposition 65 chemicals

**U.S. State Right-to-Know Regulations**

**U.S. EPA Label Information**

EPA Pesticide Registration Number Not Applicable

**16. OTHER INFORMATION**

<b><u>NFPA</u></b>	Health hazards 0	Flammability 0	Instability 0	<b>Physical and Chemical Properties</b> Yes
<b><u>HMIS</u></b>	Health hazards 0	Flammability 0	Physical hazards 0	<b>Personal protection</b> A

Issue Date 08-Jul-2016  
 Revision Date 13-Feb-2015

Revision Note  
 No Information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**