



# SAFETY DATA SHEET

Issue Date 19-Oct-2015

Revision Date 06-Oct-2015

Version 1

## 1. PRODUCT AND COMPANY IDENTIFICATION

### Product identifier

**Product Name** OM1 Multi-Surface Cleaner

### Other means of identification

**Product Code** OM104

**Synonyms** None

### Details of the supplier of the safety data sheet

**Company Name** Nycoproducts Company  
5332 Dansher Road  
Countryside, IL 60525  
(708) 579-8100  
nycoproducts.com

### Emergency telephone number

**Emergency Telephone** Chemtrec 1-800-424-9300

## 2. HAZARDS IDENTIFICATION

### Classification

#### **OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 3
Serious eye damage/eye irritation	Category 2A

### Label elements

#### Emergency Overview

## Warning

#### **Hazard statements**

Causes mild skin irritation  
Causes serious eye irritation



**Appearance** Clear Green

**Physical state** Liquid

**Odor** Spicy sandalwood

#### **Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling

Wear protective gloves/protective clothing/eye protection/face protection

#### Precautionary Statements - Response

Immediately call a POISON CENTER or doctor/physician

Specific Treatment (See Section 4 on the SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

If eye irritation persists: Get medical advice/attention

If skin irritation occurs: Get medical advice/attention

#### Hazards not otherwise classified (HNOC)

##### Other Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Surfactant Blend	Proprietary	1-5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

### 4. FIRST AID MEASURES

#### First aid measures

<b>Skin Contact</b>	Wash off immediately with plenty of water. Wash skin with soap and water.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
<b>Inhalation</b>	Remove to fresh air.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water.

#### Most important symptoms and effects, both acute and delayed

**Symptoms** Any additional important symptoms and effects are described in Section 11: Toxicology Information.

#### Indication of any immediate medical attention and special treatment needed

**Note to physicians** Treat symptomatically.

### 5. FIRE-FIGHTING MEASURES

#### Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

#### Specific hazards arising from the chemical

No Information available.

#### Explosion data

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

#### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

### Personal precautions, protective equipment and emergency procedures

**Personal precautions**                      Ensure adequate ventilation, especially in confined areas.

### Environmental precautions

**Environmental precautions**            See Section 12 for additional ecological information.

### Methods and material for containment and cleaning up

**Methods for containment**                Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up**                Pick up and transfer to properly labeled containers.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Advice on safe handling**                Handle in accordance with good industrial hygiene and safety practice.

### Conditions for safe storage, including any incompatibilities

**Storage Conditions**                    Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible materials**                None known based on information supplied.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

**Exposure Guidelines**                    This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

### Appropriate engineering controls

**Engineering Controls**                    Showers, Eyewash stations & Ventilation systems.

### Individual protection measures, such as personal protective equipment

**Eye/face protection**                    Wear safety glasses with side shields (or goggles).

**Skin and body protection**            Wear protective gloves and protective clothing.

**Respiratory protection**                Ensure adequate ventilation, especially in confined areas. In case of insufficient ventilation, wear suitable respiratory equipment.

**General Hygiene**                         Handle in accordance with good industrial hygiene and safety practice.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Information on basic physical and chemical properties

<b>Physical state</b>	Liquid
<b>Appearance</b>	Clear Green
<b>Color</b>	Green
<b>Odor</b>	Spicy sandalwood
<b>Odor threshold</b>	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	6.0 - 8.0	
Specific Gravity	1.008	
Viscosity	No Information available Not Applicable	
Melting point/freezing point	No Information available	
Flash point	Above 200°F	
Boiling point / boiling range	212 °F	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

**Other Information**

Density Lbs/Gal	8.40
VOC Content (%)	Not Applicable

**10. STABILITY AND REACTIVITY****Reactivity**

No data available

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Conditions to avoid**

Extremes of temperature and direct sunlight.

**Incompatible materials**

None known based on information supplied.

**Hazardous Decomposition Products**

None known based on information supplied.

**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure****Product Information**

<b>Inhalation</b>	Not an expected route of exposure. No known effect based on information supplied.
<b>Eye contact</b>	Avoid contact with eyes. Direct contact may cause serious eye irritation.
<b>Skin Contact</b>	Avoid contact with skin. Causes mild skin irritation. Repeated or prolonged skin contact may cause allergic reactions with susceptible persons.
<b>Ingestion</b>	Do not taste or swallow. May cause stomach distress, nausea, or vomiting.

<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Inhalation LC50</u>
Surfactant Blend	> 5000 mg/kg ( Rat )	> 2000 mg/kg ( Rabbit )	-

**Information on toxicological effects**

**Symptoms** No Information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Sensitization** No Information available.  
**Germ cell mutagenicity** No Information available.  
**Carcinogenicity** No Information available.  
**Reproductive toxicity** No Information available.  
**STOT - single exposure** No Information available.  
**STOT - repeated exposure** No Information available.  
**Aspiration hazard** No Information available.

**Numerical measures of toxicity - Product Information**

**Unknown Acute Toxicity** 0% of the mixture consists of ingredient(s) of unknown toxicity

## 12. ECOLOGICAL INFORMATION

**Ecotoxicity**

0.952% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Butyl 3-hydroxybutanoate 53605-94-0	-	100: 96 h Rainbow Trout mg/L LC50	100: 48 h Daphnia magna mg/L LC50
Surfactant Blend	-	>100: 96 h Brachydanio Rerio mg/L LC50	>100: 48 h Daphnia Magna mg/L EC50

**Persistence and degradability**

No Information available.

**Bioaccumulation**

No Information available.

**Other adverse effects**

No Information available

## 13. DISPOSAL CONSIDERATIONS

**Waste treatment methods**

**Disposal of wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging** Do not reuse container.

## 14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT** Not regulated

**TDG** Not regulated

## 15. REGULATORY INFORMATION

### International Inventories

TSCA Complies  
DSL/NDSL Complies

### Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

### US Federal Regulations

#### **SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

#### **SARA 311/312 Hazard Categories**

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

#### **CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

#### **CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

### US State Regulations

#### **California Proposition 65**

This product does not contain any Proposition 65 chemicals

### U.S. State Right-to-Know Regulations

#### **U.S. EPA Label Information**

EPA Pesticide Registration Number Not Applicable

## 16. OTHER INFORMATION

<b>NFPA</b>	Health hazards 0	Flammability 0	Instability 0	<b>Physical and Chemical Properties</b> Yes
<b>HMIS</b>	Health hazards 0	Flammability 0	Physical hazards 0	<b>Personal protection</b> B

Issue Date 19-Oct-2015

Revision Date 06-Oct-2015

#### **Revision Note**

No Information available

#### **Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**