EZH2O® Bottle Filling Station Retro-fit Model for EZ/LZ Coolers Model EZWSRK

RATED FOR INDOOR USE ONLY

PRODUCT SPECIFICATION

Retrofit bottle filling station for 115V/60Hz EZ style pushbar-activated models. Bottle filling unit shall include an electronic sensor for touchless activation with auto 20-second shut-off timer. Shall include Green Ticker™ displaying count of plastic bottles saved from waste. Bottle filler shall provide 1.1-1.5 gpm flow rate with laminar flow to minimize splashing. Shall include integrated silver ion anti-microbial protection in key areas. Unit shall meet ADA guidelines. Unit shall be lead-free design which is certified to NSF/ANSI 61 and 372 and meets Federal and State low-lead requirements. Unit shall be certified to UL399 and CAN/CSA 22.2 No. 120.

STANDARD FEATURES

- · Sanitary, touchless activation with auto 20-second shut-off
- · Integrated Silver Ion Anti-microbial Protection in key areas
- Quick Fill Rate: 1.1 gpm when connected to refrigerated EZ models;
 1.5 gpm for non-refrigerated connections
- · Laminar Flow provides minimal splash
- · Real Drain System eliminates standing water
- · Visual User Interface display includes:
 - Innovative Green Ticker[™] counts bottles saved from waste

Model EZWSRK

CONSTRUCTION

- · Stainless Steel bottle filler wrapper with ABS plastic alcove
- Retrofits to most 115/60Hz EZ style pushbar-activated models Not designed for retrofit to EZO / LZO sensor-activated coolers

CAPACITIES CHART

Model	Voltage / Hertz	Chilling Capacity	F.L. Amps	Rated Watts	Approx. Ship Wt.
EZWSRK	115V / 60Hz	Based on Existing Cooler Rating	1.0	15	18

The above ratings apply only to the EZWSRK unit. Ratings for the cooler not included.

OPTIONAL ACCESSORY:

 36292C Receptacle Adaptor Plug (115V with three plug-in receptacles).

Warranty: Electrical components and water system are warranted for 12 months from date of installation or 18 months from factory shipment, whichever date falls first.

CERTIFICATIONS / STANDARDS

- · ADA Compliant
- · UL399 and CAN/CSA 22.2 No. 120 Certified
- · ANSI/NSF 61 and 372 Certified
- GreenSpec® Listed









This specification describes an Elkay product with design, quality and functional benefits to the user. When making a comparison of other producer's offerings, be certain these features are not overlooked.

EZH20[®] Bottle Filling Station Retro-fit Model for EZ/LZ Coolers Model EZWSRK



RATED FOR INDOOR USE ONLY

IMPORTANT!

EZH2O Retro-fit is designed to fit on an existing EZ style cooler which is properly installed per the EZ Spec Sheet rough-in information.


ELECTRICAL

EZH2O equipped with electrical cord and three-prong molded rubber plug for use with 15-amp minimum receptacle. Rated at 115V/60Hz, single phase.

INSTALLATION NOTES:

- Unit will mount on bracket attached to wall as indicated by six holes shown.
- · Water and electrical will route through hole punched into basin.
- Cooler must be pressurized. Bi-level and glass filler prepped units are already pressurized.

SINGLE COOLER RETRO-FIT



REDUCE HEIGHT BY 3 INCHES FOR INSTALLATION OF CHILDRENS ADA COOLER

LEGEND:

- A = Recommended Water Supply location. Shut-off Valve (not furnished) to accept 3/8" O.D. unplated copper tube. Up to 3" (76mm) maximum out from wall.
- B = Recommended Waste Outlet location. To accommodate 1-1/4" nominal drain. Drain stub 2" (51mm) out from wall.
- C = 1-1/4" Trap (not furnished).
- D = Electrical Supply (3) Wire Recessed Box Duplex Outlet.
- E = Insure proper ventilation by maintaining 6" (152mm) minimum clearance from cabinet louvers to wall.
- F = 7/16" (11mm) Bolt Holes for fastening to wall.
- **New Installations Must Use Ground Fault Circuit Interrupter (GFCI).

Job Name:	
Model:	Qty.
Contact:	
Approval Signature:	
Notes:	

EZH2O® Bottle Filling Station Retro-fit Model for EZ/LZ Coolers Model EZWSRK



IMPORTANT!

EZH2O Retro-fit is designed to fit on an existing EZ style cooler which is properly installed per the EZ Spec Sheet rough-in information.

ELECTRICAL


EZH2O equipped with electrical cord and three-prong molded rubber plug for use with 15-amp minimum receptacle. Rated at 115V/60Hz, single phase.

RATED FOR INDOOR USE ONLY

INSTALLATION NOTES:

- · Unit will mount on bracket attached to wall as indicated by six holes shown.
- · Water and electrical will route through hole punched into basin.
- Cooler must be pressurized. Bi-level and glass filler prepped units are already pressurized.

BI-LEVEL COOLER RETRO-FIT



REDUCE HEIGHT BY 3 INCHES FOR INSTALLATION OF CHILDRENS ADA COOLER

LEGEND:

- A = Recommended Water Supply location. Shut-off Valve (not furnished) to accept 3/8" O.D. unplated copper tube. Up to 3" (76mm) maximum out from wall.
- B = Recommended Waste Outlet location. To accommodate 1-1/2" nominal drain. Drain stub 2" (51mm) out from wall.
- C = 1-1/2" Trap (not furnished).
- D = Electrical Supply (3) Wire Recessed Box Duplex Outlet.
- E = Insure proper ventilation by maintaining 6" (152mm) minimum clearance from cabinet louvers to wall.
- F = 7/16" (11mm) Bolt Holes for fastening to wall.
- **New Installations Must Use Ground Fault Circuit Interrupter (GFCI).

Job Name:	
Model:	Qty
Contact:	
Approval Signature:	
Notes:	

EZH20[®] Bottle Filling Station Retro-fit Model for EZ/LZ Coolers Model EZWSRK



RATED FOR INDOOR USE ONLY

IMPORTANT!

EZH2O Retro-fit is designed to fit on an existing EZ style cooler which is properly installed per the EZ Spec Sheet rough-in information.


ELECTRICAL

EZH2O equipped with electrical cord and three-prong molded rubber plug for use with 15-amp minimum receptacle. Rated at 115V/60Hz, single phase.

INSTALLATION NOTES:

- · Unit will mount on bracket attached to wall as indicated by six holes shown.
- · Water and electrical will route through hole punched into basin.
- Cooler must be pressurized. Bi-level and glass filler prepped units are already pressurized.

BI-LEVEL REVERSE COOLER RETRO-FIT



REDUCE HEIGHT BY 3 INCHES FOR INSTALLATION OF CHILDRENS ADA COOLER

LEGEND:

- A = Recommended Water Supply location. Shut-off Valve (not furnished) to accept 3/8" O.D. unplated copper tube. Up to 3" (76mm) maximum out from wall.
- B = Recommended Waste Outlet location. To accommodate 1-1/2" nominal drain. Drain stub 2" (51mm) out from wall.
- C = 1-1/2" Trap (not furnished).
- D = Electrical Supply (3) Wire Recessed Box Duplex Outlet.
- E = Insure proper ventilation by maintaining 6" (152mm) minimum clearance from cabinet louvers to wall.
- F = 7/16" (11mm) Bolt Holes for fastening to wall.
- **New Installations Must Use Ground Fault Circuit Interrupter (GFCI).

Job Name:	
Model:	Qty.
Contact:	
Approval Signature:	
Notes:	