

## SERIES 9 HAND GRINDER MODEL 8574-210

This unit was designed for heavy duty grinding operations – such as grinding weld seams, snagging casting, spark testing, porting and polishing engines. This higher torque Dumore grinder is manufactured with a ¼ HP fan cooled motor that idles at 15,500 RPM. Three heavy duty precision grease-lubricated ball bearings provide rigid spindle support. The threaded spindle allows the use of 1/4” shank mounted wheels in the collet chuck included with the unit, or 3/8” bore standard grinding wheels.



- 1/4 HP Universal Motor
- 15,500 RPM
- 1/4” Chuck
- 115V AC/DC
- Net weight 7 lbs 10 oz
- Uses 1-1/4” Standard Wheel
- Includes 2” High Speed Wheel
- 2-1/2” Wheel Guard
- 2 Wheel Collars

**Contact your local Dumore distributor and...**

**Do More with DUMORE**

Don't get a cheap knockoff, get this long lasting American made product that is one of industry's most efficient die grinders for decades. Built by the hard working men and women here in Mauston, Wisconsin.



**DUMORE CORPORATION**

1030 Veterans Street  
Mauston, WI 53948

Phone: 888-467-8288  
Fax: 800-338-6673  
E-mail: [sales@dumorecorp.com](mailto:sales@dumorecorp.com)