



# SAFETY DATA SHEET

Revision Date 03-Apr-2015

Version 3

## 1. IDENTIFICATION

### Product identifier

**Product Name** Spray Nine Glass & Stainless Steel Cleaner 19 oz.

### Other means of identification

**Product Code** 23319

**Synonyms** None

### Recommended use of the chemical and restrictions on use

**Recommended Use** Glass cleaner - Aerosol

**Uses advised against** No information available

### Details of the supplier of the safety data sheet

#### Manufacturer Address

ITW Permatex  
10 Columbus Blvd.  
Hartford, CT 06106 USA

#### Distributor

ITW Permatex Canada  
35 Brownridge Road, Unit 1  
Halton Hills, ON Canada L7G 0C6  
Telephone: (800) 924-6994

**Company Phone Number** 1-87-Permatex  
(877) 376-2839

**24 Hour Emergency Phone Number** Chem-Tel: 800-255-3924  
International Emergency:  
00+1+ 813-248-0585  
Contract Number: MIS0003453

**E-mail address** mail@permatex.com

## 2. HAZARDS IDENTIFICATION

### Classification

#### **OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Gases under pressure

Liquefied gas

### Label elements

#### **Emergency Overview**

#### **Warning**

Contains gas under pressure; may explode if heated



**Appearance** White **Physical state** Liquid **Odor** Citrus

**Precautionary Statements - Prevention**

Pressurized container: Do not pierce or burn, even after use

**Precautionary Statements - Response**

IF exposed or concerned: Get medical advice/attention

**Precautionary Statements - Storage**

Protect from sunlight. Store in a well-ventilated place

**Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

Not applicable

**Other Information**

The classification as a carcinogen or mutagen need not apply if it can be shown that the substance contains less than 0.1 % w/w 1,3-butadiene (EINECS No. 203-450-8). If the substance is not classified as a carcinogen or mutagen, at least the S-phrases (2)-9-16 (Table 3.2) should apply. This note applies only to certain complex oil-derived substances in Part 3

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

**substance(s)**

Chemical Name	CAS No	Weight-%	Trade Secret
PETROLEUM GASES, LIQUEFIED, SWEETENED	68476-86-8	1 - 5	*
2-BUTOXYETHANOL	111-76-2	1 - 5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

**4. FIRST AID MEASURES**

**Description of first aid measures**

- General advice** Get medical advice/attention if you feel unwell.
- Eye contact** IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
- Skin contact** IF ON SKIN: Wash skin with soap and water. If skin irritation persists, call a physician. Wash contaminated clothing before reuse.
- Inhalation** IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. If symptoms persist, call a physician.
- Ingestion** IF SWALLOWED. Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Call a physician.

**Self-protection of the first aider** Use personal protective equipment as required.

**Most important symptoms and effects, both acute and delayed**

**Symptoms** See section 2 for more information.

**Indication of any immediate medical attention and special treatment needed**

**Note to physicians** Treat symptomatically.

**5. FIRE-FIGHTING MEASURES**

**Suitable extinguishing media**

Carbon dioxide (CO2), Dry chemical, Foam

**Unsuitable extinguishing media**

Do not use a solid water stream as it may scatter and spread fire.

**Specific hazards arising from the chemical**

Heating causes rise in pressure with risk of bursting. Keep product and empty container away from heat and sources of ignition.

**Explosion data**

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**6. ACCIDENTAL RELEASE MEASURES**

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Ensure adequate ventilation, especially in confined areas. Avoid contact with eyes and skin. Use personal protective equipment as required. Do not puncture or incinerate cans.

**Environmental precautions**

**Environmental precautions** Do not flush into surface water or sanitary sewer system. See Section 12 for additional ecological information.

**Methods and material for containment and cleaning up**

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Ensure adequate ventilation. Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.

**Prevention of secondary hazards** Clean contaminated objects and areas thoroughly observing environmental regulations.

**7. HANDLING AND STORAGE**

**Precautions for safe handling**

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice. Avoid breathing vapors or mists. Avoid contact with skin, eyes or clothing. Wash thoroughly after handling. Wash contaminated clothing before reuse. Use personal protective equipment as required. Contents under pressure. Do not puncture or incinerate cans.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F. Keep from freezing.

**Incompatible materials** Strong oxidizing agents, Acids

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

Control parameters

**Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-BUTOXYETHANOL 111-76-2	TWA: 20 ppm	TWA: 50 ppm TWA: 240 mg/m <sup>3</sup> (vacated) TWA: 25 ppm (vacated) TWA: 120 mg/m <sup>3</sup> (vacated) S* S*	IDLH: 700 ppm TWA: 5 ppm TWA: 24 mg/m <sup>3</sup>

NIOSH IDLH *Immediately Dangerous to Life or Health*

**Other Information** Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

**Engineering Controls** Showers  
Eyewash stations  
Ventilation systems

Individual protection measures, such as personal protective equipment

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin and body protection** Wear protective gloves and protective clothing.

**Respiratory protection** None under normal use conditions. In case of insufficient ventilation, wear suitable respiratory equipment.

**General Hygiene Considerations** Handle in accordance with good industrial hygiene and safety practice. Regular cleaning of equipment, work area and clothing is recommended.

**9. PHYSICAL AND CHEMICAL PROPERTIES**

Information on basic physical and chemical properties

**Physical state** Liquid  
**Appearance** White  
**Odor** Citrus  
**Odor threshold** No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	10.47-11.0	
Melting point / freezing point	No information available	
Boiling point / boiling range	> 100 °C / 212 °F	
Flash point	> 93 °C / > 200 °F	
Evaporation rate	< 1	Aerosol Contents under pressure
Flammability (solid, gas)	No information available	Butyl acetate = 1
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	No information available	

<b>Vapor density</b>	>1	Air = 1
<b>Relative density</b>	0.993-0.998	
<b>Water solubility</b>	Soluble in water	
<b>Solubility in other solvents</b>	No information available	
<b>Partition coefficient</b>	No information available	
<b>Autoignition temperature</b>	No information available	
<b>Decomposition temperature</b>	No information available	
<b>Kinematic viscosity</b>	No information available	
<b>Dynamic viscosity</b>	No information available	
<b>Explosive properties</b>	No information available	
<b>Oxidizing properties</b>	No information available	

**Other Information**

<b>Softening point</b>	No information available
<b>Molecular weight</b>	No information available
<b>VOC Content (%)</b>	7.8%
<b>Density</b>	No information available
<b>Bulk density</b>	No information available

**10. STABILITY AND REACTIVITY**

**Reactivity**

No data available

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Conditions to avoid**

Heat, flames and sparks. Keep from freezing.

**Incompatible materials**

Strong oxidizing agents, Acids

**Hazardous Decomposition Products**

Carbon oxides

**11. TOXICOLOGICAL INFORMATION**

**Information on likely routes of exposure**

<b>Inhalation</b>	May cause irritation of respiratory tract.
<b>Eye contact</b>	Contact with eyes may cause irritation. May cause redness and tearing of the eyes.
<b>Skin contact</b>	May cause skin irritation and/or dermatitis.
<b>Ingestion</b>	Ingestion may cause irritation to mucous membranes.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-BUTOXYETHANOL 111-76-2	= 470 mg/kg ( Rat )	= 99 mg/kg ( Rabbit )	= 450 ppm ( Rat ) 4 h

**Information on toxicological effects**

**Symptoms** No information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Sensitization** No information available.  
**Germ cell mutagenicity** No information available.  
**Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
2-BUTOXYETHANOL 111-76-2	A3	Group 3	-	-

*ACGIH (American Conference of Governmental Industrial Hygienists)*

A3 - Animal Carcinogen

*IARC (International Agency for Research on Cancer)*

Not classifiable as a human carcinogen

**Chronic toxicity** May cause adverse effects on the bone marrow and blood-forming system. May cause adverse liver effects.

**Target Organ Effects** Blood, Central nervous system, Eyes, Hematopoietic System, kidney, Liver, Respiratory system, Skin.

The following values are calculated based on chapter 3.1 of the GHS document .

**ATEmix (oral)** 15667 mg/kg  
**ATEmix (dermal)** 36667 mg/kg  
**ATEmix (inhalation-dust/mist)** 50 mg/l  
**ATEmix (inhalation-vapor)** 15000 mg/l

## 12. ECOLOGICAL INFORMATION

### Ecotoxicity

4% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-BUTOXYETHANOL 111-76-2	-	1490: 96 h Lepomis macrochirus mg/L LC50 static 2950: 96 h Lepomis macrochirus mg/L LC50	1000: 48 h Daphnia magna mg/L EC50 1698 - 1940: 24 h Daphnia magna mg/L EC50

### Persistence and degradability

No information available.

### Bioaccumulation

No information available.

### Mobility

No information available.

Chemical Name	Partition coefficient
PETROLEUM GASES, LIQUEFIED, SWEETENED 68476-86-8	<=2.8
2-BUTOXYETHANOL 111-76-2	0.81

### Other adverse effects

No information available

## 13. DISPOSAL CONSIDERATIONS

### Waste treatment methods

**Disposal of wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging** Do not reuse container.

**US EPA Waste Number** Not applicable

**14. TRANSPORT INFORMATION**

**DOT**

UN/ID no 1950  
 Proper shipping name: Aerosols, Limited Quantity (LQ)  
 Hazard Class 2.2  
 Emergency Response Guide Number 126

**IATA**

UN/ID no ID 8000  
 Proper shipping name: Consumer commodity  
 Hazard Class 9  
 ERG Code 9L

**IMDG**

UN/ID no 1950  
 Proper shipping name: Aerosols, Limited Quantity (LQ)  
 Hazard Class 2.2  
 EmS-No F-D, S-U

**15. REGULATORY INFORMATION**

**International Inventories**

TSCA Complies  
 DSL/NDSL Complies  
 EINECS/ELINCS Complies  
 ENCS Not Listed  
 IECSC Complies  
 KECL Complies  
 PICCS Complies  
 AICS Complies

**Legend:**

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory  
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List  
 EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances  
 ENCS - Japan Existing and New Chemical Substances  
 IECSC - China Inventory of Existing Chemical Substances  
 KECL - Korean Existing and Evaluated Chemical Substances  
 PICCS - Philippines Inventory of Chemicals and Chemical Substances  
 AICS - Australian Inventory of Chemical Substances

**US Federal Regulations**

**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-BUTOXYETHANOL - 111-76-2	1.0

**SARA 311/312 Hazard Categories**

Acute health hazard Yes  
 Chronic Health Hazard No  
 Fire hazard No  
 Sudden release of pressure hazard No  
 Reactive Hazard No

**CWA (Clean Water Act)**

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

**US State Regulations**

**California Proposition 65**

This product does not contain any Proposition 65 chemicals

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania
WATER 7732-18-5	-	-	X
2-BUTOXYETHANOL 111-76-2	X	X	X
AMMONIA SOLUTION 1336-21-6	X	X	X

**U.S. EPA Label Information**

EPA Pesticide Registration Number Not applicable

<b>NFPA</b>	Health hazards 1	Flammability 1	Instability 0	-
<b>HMIS</b>	Health hazards 1	Flammability 1	Physical hazards 0	Personal protection B

NFPA (National Fire Protection Association)  
HMIS (Hazardous Material Information System)

Revision Date 03-Apr-2015

**Disclaimer**

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**