

DZ5 40/395

Dual Zone Refrigerated Snack & Beverage Merchandiser

Brought to
you by




SELECTIVEND, INC.

A Leader in Vending Machine Manufacturing Since 1931

Built in the USA, the DZ5 40/395 snack & beverage vending machine is a proven performer for dispensing a wide variety of snacks, confections and drinks. Equipped with the latest in electronic controls, premium coin changer and bill acceptor as well as our money back vend sensing technology this vendor is a great choice for serving your locations.



- **ENERGY STAR Compliant**
- **Americans With Disabilities Act Compliant (ADA)**
- 40 selections of snack & beverages (20 Snack & 20 drink)
- Adjustable flex trays accommodate popular product packages
- Adjustable temperatures zones for snack & beverage with 20 degree variance
- Programmable health safety by selection, range or row for the entire machine
- 100% financing available
- Delivers plug-in ready - Just set prices and operate
- Premium electronic coin changer accepts \$.05 to \$1.00 coins and tokens
- Automatic bill acceptor/stacker accepts \$1 & \$5 bills
- Credit/Debit & mobile payment system option
- Pull-out, tilting food trays for easy loading and assured product rotation
- Sturdy beverage trays on roller bearing slides hold up to 60 drinks per tray
- Individual electronic pricing of product from \$0 through \$655.35 – no price labels needed
- Free-vend capable
- Multi-vend mode (buy multiple items with one credit)
- Cash/sales accountability by selection
- Guaranteed delivery sensor system ensures product or money back
- Class leading energy saving features including LED Lighting and programmable power saving options
- Attractive styling bezels with back lighted changable point of sale window
- All-steel construction
- Industry leading warranty & support



Std. Configuration




Features

- Adjustable temperatures zones for snack & beverage with 20 degree variance
- Attractive styling bezel with point of sale window
- Standard peripheral opening for additional payment or POS systems
- Back lighted keypad with Braille identification
- Americans With Disabilities Act (ADA) Ready
- MDB support for all industry standard devices including cash, coin, debit and credit systems
- DEX data output support
- Full featured controller with sales and accounting:
 - Price setting by selection, row or machine
 - Free vend and Combo vend modes
 - Flexible space to selection setting
 - Time of day discounting
 - Time of day shutdown modes for energy savings and secured vend times
 - Programmable coupon and token values
 - Coin and bill rejection rate counts
 - Accountability display by selection, row or machine
 - Talker device support for sight impaired (Talker not included)
- Self cleaning condenser coil with reverse on startup fan
- Motor pairing capable
- Proven operating environment
 - High: 100°F (38°C) @ 90% RH

Energy Efficient

- Uses only 4.2 Kwh/day @ 75°F (24°C), 45% RH based on refrigerating 34.6 cu.ft. of space
- Low-E triple pane Argon filled door glass
- LED lighting
- Thickest foaming on the market with Eco-friendly zero ODP Ecomate® foaming process
- Balanced airflow design
- Energy saving programmable shutdown modes
- Eco-friendly refrigeration system




Configure to meet your merchandising needs.

Movable barrier tray allows you to adjust temperature zones




Credit/Debit & mobile reader options.



iVend® Guaranteed Delivery System

Keeps customers satisfied and reduces service calls for misloaded product.



LED Lighting

Enhances product presentation promoting more sales. No bulb servicing for 5 years. Energy efficient and eco-friendly.



Premium Currency Acceptors

Includes standard electronic coin acceptor and \$1 & \$5 bill acceptor.



Versatile Steel Beverage Trays

Hold up to 36 canned or bottle beverages.

DZ5 40/395 (5W Dual Zone)

Selections	40 Standard Items					
Capacity	235 Food Items; 120 Beverage					
Selection Pricing	Individual from \$0 to \$655.35					
Payment Systems	Premium Electronic Coin Acceptor; \$1 & \$5 Bill Acceptor					
Electrical Requirements	115 VAC/60Hz, 9.5 AMPS (230 VAC/50Hz, 4.8 AMPS); With heated glass active 115 VAC/60Hz, 10.5 AMPS (230 VAC/50Hz, 5.2 AMPS)					
Refrigeration	Environmentally Friendly Super 1/3 HP, R134a Closed System					
Dimensions	Height	72" (183 cm)	Width	41" (104 cm)	Depth	38" (97 cm)
Net Weight	*838 lbs. (380.1 kg) *Varies with configuration & options.					
Standard Features	Styling Package, LED Lighting, iVend® Sensor System, Can & Bottle Trays, Heated Glass, Motor Pairing Capability					
Options	Credit/Debit Card Reader					

In order to bring you the best products possible, we continue to improve product design and performance and as such specifications are subject to change without notice. The manufacturer makes no warranties or representations of compliance with any local, state, national or international requirements for the operation of the equipment in any application for which it is capable of being used beyond approvals listed on the product. Any purchaser is required to make an independent analysis of the fitness and legality of the product's usage before it is deployed and must continue to monitor the potential changing nature of compliance requirements. The manufacturer expressly disclaims responsibility for compliance with any laws and affirmatively requires any buyer to make an independent analysis of the fitness and legal basis of any use or application of the subject unit.



SELECTIVEND, INC.

Selectivend, Inc.
8040 University Blvd.
P.O. Box 1395
Des Moines, Iowa 50305
1-800-282-1944
Fax: 515-274-5180
www.selectivend.com