


TECHNICAL SPECIFICATION




Tower


FRONT VIEW



SIDE VIEW



PLAN VIEW



Machine dimensions

Height: 40 in. (1018 mm), Amp width: 7.5 in. (190 mm),

Amp depth: 4.3 in. (110 mm), Base diameter: 7.7 in. (196 mm)

Electrical

Input voltage/frequency: 120V / 50/60Hz

Standby power consumption: <0.5W

Max input power: 56W

Min input power: 6W

Construction

Polycarbonate

ABS

Filter

Removes 99.97% of allergens and pollutants as small as 0.3 microns from the air

360° borosilicate glass microfiber HEPA filter

Activated carbon filter

Rubber vacuum seals

Filter life: One year based on 12 hr. use a day; or 6 months based on 24 hr. use a day

Height: 7.7 in. (196 mm)

Diameter: 7.7 in. (196 mm)

Unboxed weight: 0.77 lb. (0.35 kg)

Operation

For indoor use only

Operation environment:

Engineered to operate between 0-104°F (0-40°C), 0-100% humidity

10 speed settings

70° oscillation

Auto mode:

Automatically monitors air quality and adjusts airflow accordingly

Quiet mode: Purifies and cools you using the quiet setting

Standby mode

Sleep time increments: 15 min., 30 min., 45 min., 1-9 hrs.

Hidden LED display

CADR rate: 70 cfm¹

Sound level at min flow rate: Quieter than 45 dB(A)

Sound level at max flow rate: 63 dB(A)

Remote control battery: CR2032L coin cell

Remote control functions: On/Off, airflow, oscillation, sleep timer, auto mode, night mode

Dyson Link app

Automatically monitors, reacts and purifies²

Live air quality metrics straight to your smart phone²

Requires iOS 8.0 or later or Android 4.0 or later

Logistics

Single unit order code:

White/Silver: 305158-01

Iron/Blue: 305159-01

Unit barcode:

White/Silver: 885609009172

Iron/Blue: 885609008189

Net weight: 8.2 lb. (3.72 kg)

Packaged weight: 12.7 lb. (5.76 kg)

Packaged dimensions:

(H) 44.5 in. (1131 mm) × (W) 8.6 in. (219 mm) × (D) 8.6 in. (219 mm)

Cable length: 6.6 ft. (2 m)

Standard warranty

2 year warranty – parts and labor



Product range

White/Silver

Remote



Certified **asthma & allergy friendly**[™] by Allergy Standards Limited. ASTHMA & ALLERGY FRIENDLY and ASTHMA & ALLERGY FRIENDLY LOGO are certification marks and trademarks of ALLERGY STANDARDS LIMITED. The ASTHMA AND ALLERGY FOUNDATION OF AMERICA is a Registered Trademark of AAFA.

¹ Clean Air Delivery Rate for smoke tested to AHAM AC1.

² Standard data and messaging rates may apply. Requires Wifi and app-enabled device.