

STAINLESS STEEL INDUSTRIAL FLOOR FANS

shop-air®

A Shop-Vac® Company

Stay cool and well ventilated with Shop-Air® Industrial Floor Fans. Choose from belt driven to direct drive, ranging from 24 in. up to 48 in. diameters and as high as 3/4 Peak Horsepower motors. Featuring high velocity air movement, these fans are perfect for moving large volumes of air quickly, keeping your factories and workplaces cool.

All of our fans include:

- Durable stainless steel corrosion resistant housings built to last a long time.
- Non-skid front legs to keep your fan in position while operating.
- C UL US listed.
- Durable wheels for easy mobility.
- 3 and 4 blade designs provide even airflow and low noise levels.
- Non-corroding aluminum fan blades for longer life.
- 10 ft. 3 prong heavy duty power cords with cord wraps.



24
inch
diameter

ITEM #	FAN DIA.	BODY WIDTH	HP	MOTOR TYPE	DIRECT DRIVE	BELT DRIVE	CFM		BLADES
							HIGH	LOW	
1180000	24 in. Dia.	13 in. Stainless	1/3	OPEN	YES	NO	6,500	5,000	4

30
inch
diameter

ITEM #	FAN DIA.	BODY WIDTH	HP	MOTOR TYPE	DIRECT DRIVE	BELT DRIVE	CFM		BLADES
							HIGH	LOW	
1180100	30 in. Dia.	13 in. Stainless	1/2	OPEN	YES	NO	9,600	7,500	4

36
inch
diameter

ITEM #	FAN DIA.	BODY WIDTH	HP	MOTOR TYPE	DIRECT DRIVE	BELT DRIVE	CFM		BLADES
							HIGH	LOW	
1180200	36 in. Dia.	13 in. Stainless	1/2	OPEN	YES	NO	11,000	10,000	3
1181000	36 in. Dia.	13 in. Stainless	1/2	OPEN	NO	YES	12,200	11,000	4

42
inch
diameter

ITEM #	FAN DIA.	BODY WIDTH	HP	MOTOR TYPE	DIRECT DRIVE	BELT DRIVE	CFM		BLADES
							HIGH	LOW	
1181100	42 in. Dia.	17.12 in. Stainless	3/4	OPEN	NO	YES	16,500	14,500	4

48
inch
diameter

ITEM #	FAN DIA.	BODY WIDTH	HP	MOTOR TYPE	DIRECT DRIVE	BELT DRIVE	CFM		BLADES
							HIGH	LOW	
1181200	48 in. Dia.	17.12 in. Stainless	3/4	OPEN	NO	YES	22,000	20,000	4

CFM/Specifications subject to change without notice - Shop-Vac lab testing.

