1 - PRODUCT IDENTIFICATION

PRODUCT NAME: Good Hood

PRODUCT TYPE: Alkaline liquid cleaning compound

PRODUCT NUMBER:......G1371XXX (Last 3 characters vary with the packaging)

COMPANY: Simoniz USA, Inc.

201 Boston Turnpike Bolton, CT 06043 1-800-227-5536

www.simoniz.com

EMERGENCY PHONE:(800) 255-3924 (CHEM-TEL)

2 - HAZARDS IDENTIFICATION

CLASSIFICATION OF SUBSTANCE/MIXTURE: Skin Corrosion (1A) Serious Eye Damage
(1) Sprcific Target Organ Toxicity – Single Exposure (1)

SYMBOLS:.....



SIGNAL WORD: DANGER!

HAZARD STATEMENT: Causes severe skin burns and eye damage. Causes serious

eve damage. Causes damage to organs.

PRECAUTIONARY STATEMENTS:

PREVENTION: Wash hands thoroughly after handling. Do not eat, drink or

smoke when using this Do not breathe

dust/fume/gas/mist/vapours/spray. Wear protective

gloves/protective clothing/eye protection/face protection.

RESPONSE:......IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell. Rinse mouth. IF exposed or concerned: Get medical advice/attention. IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Remove/Take off

immediately all contaminated clothing. Rinse skin with

water/shower. Wash contaminated clothing before reuse. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or doctor/physician. Specific treatment (see First AID Section on this label). IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses if present and easy

to do – continue rinsing.

STORAGE:..... Store locked up.

DISPOSAL: Dispose of container and contents in accordance with local regulations.

3 - COMPOSITION / INFORMATION ON INGREDIENTS

INGREDIENT	C.A.S. NUMBER	CONCENTRAION (%)
Water	7732-18-5	70-92
Potassium Hydroxide	1310-58-3	5-15
2-Butoxy Ethanol	111-76-2	1-5
Alkyl Glucoside Surfactant	68515-73-1	1-5
Sodium Gluconate	527-07-1	1-5

4 - FIRST-AID MEASURES

BREATHING (INHALATION): .. If victim shows signs of discomfort or irritation, remove to fresh air. If symptoms persist, get immediate medical attention. SWALLOWING (INGESTION):. DO NOT INDUCE VOMITING! Drink a large quantity of water or milk. Do not attempt to give liquids to an unconscious person. Get immediate medical attention!

EYES: Inhalation, skin absorption, or ingestion.

SKIN (DERMAL): Flush from skin and clothing with large amounts of fresh water. If

irritation persists, consult physician. Wash contaminated clothing

before wearing.

5 – FIRE-FIGHTING MEASURES

FLASHPOINT: This product is non-flammable.

EXTINGUISHING MEDIA: This product is non-flammable. Use extinguishing media suitable

for materials already burning.

SPECIAL FIRE FIGHTING PROCEDURES:Firefighters working in areas where this

product is present should be equipped with an approved, fully

enclosed SCBA.

UNUSUAL FIRE AND EXPLOSION HAZARDS:.....None known.

6 - ACCIDENTAL RELEASE MEASURES

SPILL PROCEDURES:...... Dike to prevent spillage into streams or sewer systems. Consult

local, state and federal authorities.

WASTE DISPOSAL: As recommended by local, state and federal authorities.

7 - HANDLING and STORAGE

STORAGE:......Store in a cool, well ventilated area. Avoid overheating or

freezing.

HANDLING: Under normal use according to label instructions, special

protection should not be necessary. Wear eye protection if product is likely to splash.Do not place this product in an unmarked container! Keep away from children! Spilled material

is slippery.

8 - EXPOSURE CONTROLS / PERSONAL PROTECTION

RESPIRATORY PROTECTION:.....Not usually needed in well-ventilated areas. If

needed, use a NIOSH approved respirator.

PROTECTIVE CLOTHING:...... Nitrile or PVC gloves, and chemical splash goggles.

ADDITIONAL MEASURES:..... Under normal use according to label instructions, special

protection should not be necessary. Wear eye protection if product is likely to splash.Do not place this product in an unmarked container! Keep away from children! Spilled material

is slippery.

INGREDIENT C.A.S. NUMBER PEL

Water	7732-18-5	No limits established
Potassium Hydroxide	1310-58-3	2 mg/m3 ceiling
2-Butoxy Ethanol	111-76-2	20 ppm TLV, 25 ppm PEL
Alkyl Glucoside Surfactant	68515-73-1	No limits established
Sodium Gluconate	527-07-1	No limits established

9 - PHYSICAL / CHEMICAL PROPERITES

APPEARANCE & ODOR:...... Slightly viscous light golden liquid. Slight solvent odor.

ODOR THRESHOLD: N/A pH: 13.5-14

MELTING POINT: 210 degrees F.

FREEZING POINT: N/A

BOILING POINT: 210 degrees F.

BOILING POINT RANGE: N/A

FLASHPOINT: This product is non-flammable.

VAPOR DENSITY (AIR=1): Greater than 1. SPECIFIC GRAVITY: Greater than 1. SOLUBILITY IN WATER: Completely soluble.

PARTITION COEFFICIENT: N/A

AUTO-IGNITION TEMPERATURE:N/A

DECOMPOSITION TEMPERATURE:N/A VISCOSITY: Significant body 10 - STABILITY and REACTIVITY STABILITY: Stable under normal conditions. **HAZARDOUS DECOMP.:.....** This product not known to polymerize. 11 - TOXICOLOGICAL INFORMATION **ROUTE(S) OF ENTRY:.....** Inhalation, skin absorption, or ingestion. **LISTED CARCINOGEN:.....** None over 0.1%. **MEDICAL CONDITION AGGRAVATED:** May aggravate pre-existing dermatitis. INHALATION: Not likely to be inhaled in hazardous amounts. Avoid exposure to mists or vapors. Maintain adequate ventilation in the work area. INGESTION: This material can cause burns and serious damage to any exposed body parts. EYES: Undiluted product will cause burns or eye irritation, or possibly blindness. SKIN (DERMAL): This product may cause burns or irritation if not removed from the skin. Chronic overexposure may cause injury to blood, liver & kidneys. **ACUTE TOXICITY* (ORAL):.....>2000 mg/kg** ACUTE TOXICITY* (DERMAL):....>2000 mg/kg ACUTE TOXCITY* (INHALATION):>20,000 ppm V (Gas), >20 mg/l (Vapor), >5 mg/l (Dust) *Determined using the additivity formula for mixtures (GHS Purple Book, 3.1.3.6) 12 - ECOLOGICAL INFORMATION **ENVIRONMENTAL FATE AND DISTRIBUTION: N/A** 13 - DISPOSAL CONSIDERATIONS WASTE DISPOSAL: As recommended by local, state and federal authorities. 14 - TRANSPORTATION INFORMATION PROPER SHIPPING NAME: Compounds, Cleaning, Liquid (contains potassium hydroxide) **HAZARD CLASS:** 8 UN/NA NUMBER: NA 1760 PACKAGING GROUP:.....III

15 - REGULATIONS

Contents of this MSDS comply with the OSHA Hazard Communication Standard 29CFR 1910.1200

16 – OTHER INFORMATION

NFPA HEALTH:NFPA FLAMMABILITY:NFPA REACTIVITY:NFPA OTHER:	0 0
	The information contained in this SDS is based on the data available to us from sources we believe to be reliable. No warranty or guaranty expressed or implied is made regarding the accuracy of this data or the results obtained from the reliance on this data. The manufacturer assumes no responsibility for injury from the use of this product. Be safe- read this product safety information and pass it on to all persons who may be exposed to this product. Federal law requires it. This product and/or all of its components are either included on or exempt from the TSCA