

# RFBW64



68" x 23.63" x 25" (H x W x D)

Fully assembled warming cabinet & all-refrigerator stacked combination

## Highlights:

Glass door warming cabinet keeps full blanket inventory in easy view

Factory installed locks in each section offer security you can count on

Digital controls for both units ensure easy temperature management

Frost-free operation ensures minimum user maintenance in the refrigerator compartment

## Product Features:

|   |  |
|---|--|
| Energy efficient design                                 | Warming cabinet is partially powered by the lower refrigerator, offering huge energy savings for your facility by having a single plug appliance serve two functions |
| Fully assembled   | Unit ships completely assembled for easy installation  |
| Slim 24" footprint                                      | Ideally sized for use in space-challenged facilities   |
| Stainless steel interior (warming cabinet)              | Offers lasting durability and improved sanitary conditions   |
| Stainless steel trimmed double pane tempered glass door | Heat-safe door offers a full view of interior blanket inventory  |
| Adjustable cantilevered shelves (warming cabinet)       | Top unit offers a variety of interior configurations with flexible cantilevered shelving in chrome cabinet)  |
| Foamed-in-place cabinet                                 | Ensures the interior is efficiently insulated  |
| Factory installed locks                                 | Both units include a front keyed lock for added security   |
| Digital thermostats                                     | Electronic controls for both sections to ensure easy temperature management. Warming cabinet features an external LED temperature readout                            |

## RFBW64 Specifications:

| Overview                         |                    |
|----------------------------------|--------------------|
| Height                           | 68.0"              |
| Width                            | 23.63"             |
| Depth                            | 25.0"              |
| Depth with Handle                | 25.88"             |
| Depth with door at 90°           | 46.13"             |
| Capacity                         | 8.6 cu.ft.         |
| Defrost Type                     | Frost-Free         |
| Door                             | Glass/SS           |
| Cabinet                          | Black              |
| US Electrical Safety             | ETL                |
| Canadian Electrical Safety       | ETL-C              |
| Amps                             | 1.5                |
| Voltage/Frequency                | 115 V AC/60 Hz     |
| Weight                           | 300.0 lbs.         |
| Shipping Weight                  | 350.0 lbs.         |
| Parts & Labor Warranty           | 1 Year             |
| Compressor Warranty              | 5 Years            |
| Warming & Cooling Cabinet        |                    |
| Top Unit                         | Warming Cabinet    |
| Door Swing (Top Unit)            | RHD                |
| Reversible (Top Unit)            | Factory Reversible |
| Adjustable Shelves (Top Unit)    | Yes                |
| Shelf Type (Top Unit)            | Chrome             |
| Shelf Quantity (Top Unit)        | 2                  |
| Thermostat Type (Top Unit)       | Digital Unit       |
| Capacity (Top Unit)              | 4.0 cu.ft.         |
| Refrigeration Unit               | All-Refrigerator   |
| Door Swing (Bottom Unit)         | RHD                |
| Reversible (Bottom Unit)         | Factory Reversible |
| Adjustable Shelves (Bottom Unit) | Yes                |
| Shelf Type (Bottom Unit)         | Glass              |
| Shelf Quantity (Bottom Unit)     | 3                  |

|                               |                       |
|-------------------------------|-----------------------|
| Interior Light (Bottom Unit)  | Yes                   |
| Thermostat Type (Bottom Unit) | Digital               |
| Interior Height (Bottom Unit) | 24.0"                 |
| Interior Width (Bottom Unit)  | 19.25"                |
| Interior Depth (Bottom Unit)  | 16.0"                 |
| Capacity (Bottom Unit)        | 4.6cu.ft.             |
| Refrigerant Type              | R134a                 |
| Fan Type                      | Interior and Exterior |

