

## Multi-Treatment Cart Specialty Package #6201

### Specifications



#### Construction:

- All steel

#### Features include:

- Two Adjustable 3 inch Exchange Trays
- Removable Plastic Top
- Stainless Steel Combination Top Rail/Push Handle
- Tall Cabinet (30 inches / 76.2 cm) with key locking system for drawers and doors (keyed the same)
- Vinyl-padded full wrap-around steel bumper
- Five-inch (12.7 cm) premium rubber single-wheel caster set, full swivel – one with brake, one directional
- Storage Compartment: 21-inch high opening, with adjustable internal shelf
- Ball-Bearing Drawer Slides
- Double-walled drawer faces with no rough edges
- Side mounted drop shelf, without lip
- Cart is delivered fully assembled
- Certified "Latex Free"
- Five Year Warranty
- Compatible with most accessories
- Hard-baked powder coat finish

#### Twelve available color choices:

- Beige (-BG), Burgundy (-BU), Light Blue (-LB), Navy (-NY), Light Gray (-GY), Mauve (-MV), Red (-RD), Teal (-TL), Yellow (-YL), Hammer Tone Blue (-HTB), Hammer Tone Gray (-HTGY) and Hammer Tone Green (-HTGN)

#### Drawer configuration:

- 1 x 3-inch (7.6 cm)
- 1 x 6-inch (15.2 cm)

#### Assembled Cart Dimensions:

- 44.5" H x 32" W x 22" D (113cm H x 81.3cm W x 55.9cm D)
- Cart Net Weight: 128 pounds (58.1 kg)
- Approx. shipping Weight: 163 pounds (74.1 kg)