

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-500

Excellent dexterity and breathability in a very versatile glove

MD

Medium Duty



Cut-Protection

Performance and safety combined with excellent dexterity and breathability in a very versatile glove

- Ansell's HyFlex 11-500 industrial glove is well suited for a broad range of assembly applications
- It is designed for dry or slightly oily applications where workers need light cut protection, and in some cases, isolation from heat or flying molten metal debris
- Offering optimal comfort and a sure grip, the HyFlex 11-500 glove is the versatile choice for optimal productivity and safety



Industries

- Aerospace
- Appliance Manufacturing
- Automotive
- Electricians
- General Carpentry
- General Industry
- Glass
- HVAC/Sheet Metal Users/Window Glazers
- Metal Fabrication
- Metalworking
- Paper
- Plastics
- Plumbers

Applications

- Brown goods
- Assembly of white goods
- Plastics injection and moulding
- Cycles
- Assembling and inspecting engine parts and small components
- Light assembly of oil-coated pieces

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-500

Excellent dexterity and breathability in a very versatile glove

Performance Profile

- Provides “second skin” closeness, reducing risk of snags and cuts.
- Ability to handle sharp parts with confidence, increasing productivity and safety.
- Enhances grip in light oil conditions with good abrasion resistance.
- Silicone-free and natural rubber latex-free for worker and product protection.


Key Features

- Stretch DuPont™ Kevlar® liner provides excellent cut resistance and comfortable fit.
- Product provides: ISO Cut Level B.
- Excellent protection from nuisance nicks and abrasion.
- Extended cuff offers extra cut protection around the wrist.
- Foam nitrile coating channels away oil from the surface of the gloves, providing a sure grip in light oil applications.
- Soil-hiding black palm coating.

Technologies

DuPont™
KEVLAR®

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
HyFlex 11-500	Type: Palm coated Coating material:Nitrile Liner material: Nylon Lycra® Kevlar Cuff style: Knitwrist	15	6-11	199-266 mm 7.83-10.47 inches	Black and yellow	12 pairs/bag, 12 bags/carton

Europe, Middle East & Africa

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
+32 2 528 74 00
+32 2 528 74 01

North America

Ansell Healthcare Products, LLC
111 Wood Avenue South
Suite 210
Iselin, NJ 08830, USA
+1 800 800 0444
+1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
+61 1800 337 041
+61 1800 803 578

Asia Pacific

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
63000 Cyberjaya
Selangor, Malaysia
T: +60 3 83106688
F: +60 3 8318 6699

Latin America & Caribbean

Ansell Brazil Ltda.
Rua das Figueiras 474 - 4º Andar
Bairro Jardim
SP 09080-300 Santo André
Brazil
CNPJ: 03.496.778/0001-21
+55 11 3356 3100

Russia

Анселл РУС
123610 Россия, Москва
Краснопресненская
Наб. 12, п.3, оф. 1304А
Тел. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates, except as noted. DuPont™ and Kevlar® are trademarks of DuPont used under license. © 2016 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

