Permatex

SAFETY DATA SHEET

Revision Date 15-May-2015 Version 1

1. IDENTIFICATION

Product identifier

Product Name DEVCON HOME SUPER GLUE 2 GR.

Other means of identification

Product Code 29045 Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use This product is a cyanoacrylate-based adhesive

Uses advised against No information available

Details of the supplier of the safety data sheet

<u>Manufacturer Address</u> <u>Distributor</u>

ITW Permatex Canada
10 Columbus Blvd. 35 Brownridge Road, Unit 1
Hartford, CT 06106 USA Halton Hills, ON Canada L7G 0C6

Telephone: (800) 924-6994

Company Phone Number 1-87-Permatex

(877) 376-2839

24 Hour Emergency Phone Number Chem-Tel: 800-255-3924

International Emergency: 00+1+ 813-248-0585

Contract Number: MIS0003453

E-mail address mail@permatex.com

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

| Skin corrosion/irritation | Category 2 |
|--|------------|
| Serious eye damage/eye irritation | Category 2 |
| Specific target organ toxicity (single exposure) | Category 3 |
| Flammable liquids | Category 4 |

Label elements

Emergency Overview

Warning

Causes skin irritation
Causes serious eye irritation
May cause respiratory irritation

Combustible liquid



Appearance Clear Physical state Liquid Odor Irritating

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling Wear protective gloves/protective clothing/eye protection/face protection Avoid breathing dust/fume/gas/mist/vapors/spray Use only outdoors or in a well-ventilated area Keep away from heat/sparks/open flames/hot surfaces. — No smoking Keep cool

Precautionary Statements - Response

Specific treatment (see supplemental first aid instructions on this label)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

If eye irritation persists: Get medical advice/attention IF ON SKIN: Wash with plenty of soap and water

If skin irritation occurs: Get medical advice/attention

Take off contaminated clothing and wash before reuse

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell In case of fire: Use CO2, dry chemical, or foam for extinction

Precautionary Statements - Storage

Store in a well-ventilated place. Keep container tightly closed Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other Information

Not applicable.

Unknown acute toxicity 3% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

substance(s)

| Chemical Name | CAS No | Weight-% | Trade Secret |
|-----------------------|-----------|----------|--------------|
| ETHYL-2-CYANOACRYLATE | 7085-85-0 | 60 - 100 | * |

^{*}The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

Description of first aid measures

General advice Get medical advice/attention if you feel unwell.

Eye contact IF IN EYES:. Immediately flush with plenty of water. After initial flushing, remove any

contact lenses and continue flushing for at least 15 minutes. If eyelids are bonded closed, release eyelashes with warm water by covering with a wet pad. If symptoms persist, call a

physician.

Skin contact IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin

with water/shower. Wash with soap and water. Allow warm water to penetrate the bond and gently attempt to move bonded areas without pulling the skin away from bonded area. If

symptoms persist, call a physician.

Inhalation IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for

breathing. If symptoms persist, call a physician.

Ingestion IF SWALLOWED:. Do NOT induce vomiting. Never give anything by mouth to an

unconscious person. Call a physician.

Self-protection of the first aiderUse personal protective equipment as required.

Most important symptoms and effects, both acute and delayed

Symptoms See section 2 for more information.

Indication of any immediate medical attention and special treatment needed

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Carbon dioxide (CO2), Dry chemical, Foam

Unsuitable extinguishing media

None.

Specific hazards arising from the chemical

Combustible material.

Explosion data

Sensitivity to Mechanical Impact None.
Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment as required. Remove all sources of ignition. Ensure

adequate ventilation, especially in confined areas. Avoid contact with skin, eyes or clothing.

Environmental precautions

Environmental precautions See Section 12 for additional ecological information. Do not flush into surface water or

sanitary sewer system. Prevent further leakage or spillage if safe to do so. Prevent product

from entering drains.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Ensure adequate ventilation. Soak up with inert absorbent material. Sweep up and shovel

into suitable containers for disposal.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Avoid breathing

vapors or mists. Avoid contact with skin, eyes or clothing. Wash thoroughly after handling. Wash contaminated clothing before reuse. Use personal protective equipment as required.

Keep away from heat/sparks/open flames/hot surfaces. — No smoking.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric

motors and static electricity).

Incompatible materials Strong oxidizing agents, Water, Alcohols, Amines, Alkalis, Polymerization can occur

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

| Chemical Name | ACGIH TLV | OSHA PEL | NIOSH IDLH |
|-----------------------|--------------|----------|------------|
| ETHYL-2-CYANOACRYLATE | TWA: 0.2 ppm | - | - |
| 7085-85-0 | | | |

Appropriate engineering controls

Engineering Controls Showers

Eyewash stations Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing.

Respiratory protectionUse NIOSH-approved air-purifying respirator with organic vapor cartridge or canister, as

appropriate.

General Hygiene Considerations When using do not eat, drink or smoke. Regular cleaning of equipment, work area and

clothing is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear
Odor Irritating

Odor threshold No information available

Property Values Remarks • Method

pH No information available
Melting point / freezing point
Boiling point / boiling range No information available
> 150 °C / 302 °F

Flash point / Boiling range > 150 °C / 302

Polymerization

Evaporation rate No information available

Flammability (solid, gas) Flammability Limit in Air

Upper flammability limit:No information availableLower flammability limit:No information available

Vapor pressure <0.2 mmHg

Vapor density >1 Air = 1

No information available

Relative density 1.06

Water solubility Not applicable Solubility in other solvents No information available **Partition coefficient** No information available **Autoignition temperature** No information available **Decomposition temperature** No information available Kinematic viscosity No information available Dynamic viscosity No information available **Explosive properties** No information available **Oxidizing properties** No information available

Other Information

Softening pointNo information availableMolecular weightNo information available

VOC Content (%) <20 g/l

Density No information available Bulk density No information available

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Heat, flames and sparks.

Incompatible materials

Strong oxidizing agents, Water, Alcohols, Amines, Alkalis, Polymerization can occur

Hazardous Decomposition Products

Carbon oxides

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Inhalation May cause irritation of respiratory tract. May cause drowsiness or dizziness.

Eye contact Contact with eyes may cause irritation. May cause redness and tearing of the eyes.

Skin contact Will bond to skin.

Ingestion Ingestion may cause irritation to mucous membranes.

| Chemical Name | Oral LD50 | Dermal LD50 | Inhalation LC50 |
|------------------------------------|-----------------|-------------|-----------------|
| ETHYL-2-CYANOACRYLATE 7085-85-0 | > 5 mL/kg (Rat) | - | - |

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

SensitizationNo information available.Germ cell mutagenicityNo information available.CarcinogenicityNo information available.

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral) 5144 mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity

100% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Mobility

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and

regulations.

Contaminated packaging Do not reuse container.

US EPA Waste Number Not applicable

14. TRANSPORT INFORMATION

DOT

Proper shipping name: Not regulated

IATA

Proper shipping name: Not regulated

IMDG

Proper shipping name: Not regulated

15. REGULATORY INFORMATION

International Inventories

29045 - DEVCON HOME SUPER GLUE 2 GR.

TSCA Complies Complies DSL/NDSL Complies **EINECS/ELINCS** Complies **ENCS IECSC** Complies Complies **KECL** Complies **PICCS AICS** Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

ENCS - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

AICS - Australian Inventory of Chemical Substances

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

| Acute health hazard | Yes |
|-----------------------------------|-----|
| Chronic Health Hazard | No |
| Fire hazard | Yes |
| Sudden release of pressure hazard | No |
| Reactive Hazard | No |

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

| Chemical Name | New Jersey | Massachusetts | Pennsylvania |
|-----------------------|------------|---------------|--------------|
| ETHYL-2-CYANOACRYLATE | X | - | - |
| 7085-85-0 | | | |

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

NFPAHealth hazards 2Flammability 2Instability 0-HMISHealth hazards 2Flammability 2Physical hazards 0Personal protection B

NFPA (National Fire Protection Association)
HMIS (Hazardous Material Information System)

Revision Date

15-May-2015

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet