



SAFETY DATA SHEET

Revision Date 30-Jul-2015

Version 6

1. IDENTIFICATION

Product identifier

Product Name DEVCON HOME SILICONE ADHESIVE 50 GR.

Other means of identification

Product Code 12045

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Sealant

Uses advised against No information available

Details of the supplier of the safety data sheet

Manufacturer Address

ITW Permatex
10 Columbus Blvd.
Hartford, CT 06106 USA

Distributor

ITW Permatex Canada
35 Brownridge Road, Unit 1
Halton Hills, ON Canada L7G 0C6
Telephone: (800) 924-6994

Company Phone Number 1-87-Permatex
(877) 376-2839

24 Hour Emergency Phone Number Chem-Tel: 800-255-3924
International Emergency:
00+1+ 813-248-0585
Contract Number: MIS0003453

E-mail address mail@permatex.com

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

NOTE: This product is a consumer product and is labeled in accordance with the US Consumer Product Safety Commission regulations which take precedence over OSHA Hazard Communication labeling. The actual container label will not include the label elements below. The labeling below applies to industrial/professional products.

Label elements

Emergency Overview

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Clear

Physical state Paste

Odor Acetic acid

Precautionary Statements - Storage

Protect from moisture

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other Information

- The classification as a carcinogen need not apply if the full refining history is known and it can be shown that the substance from which it is produced is not a carcinogen. This note applies only to certain complex oil derived substances in Annex I
- Acetic acid produced during curing can irritate eyes, nose and throat

Unknown acute toxicity

2.7 % of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS**substance(s)**

Chemical Name	CAS No	Weight-%	Trade Secret
POLY (DIMETHYLSILOXANE), HYDROXY TERMINATED	70131-67-8	40 - 70	*
DISTILLATES (PETROLEUM), HYDROTREATED MIDDLE	64742-46-7	10 - 30	*
AMORPHOUS SILICA	7631-86-9	7 - 13	*
METHYLTRIACETOXYSILANE	4253-34-3	1 - 5	*
ETHYLTRIACETOXYSILANE	17689-77-9	1 - 5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES**Description of first aid measures****General advice**

Get medical advice/attention if you feel unwell.

Eye contact

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Skin contact

IF ON SKIN: Wash skin with soap and water. If skin irritation persists, call a physician. Wash contaminated clothing before reuse.

Inhalation

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. If symptoms persist, call a physician.

Ingestion

IF SWALLOWED: Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Call a physician.

Self-protection of the first aider

Use personal protective equipment as required.

Most important symptoms and effects, both acute and delayed**Symptoms**

See section 2 for more information.

Indication of any immediate medical attention and special treatment needed**Note to physicians**

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Carbon dioxide (CO2), Dry chemical, Foam

Unsuitable extinguishing media

None.

Specific hazards arising from the chemical

None in particular.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with eyes and skin. Wash thoroughly after handling.

Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. See Section 12 for additional ecological Information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Ensure adequate ventilation. Flood with water to complete polymerization and scrape off floor. Sweep up and shovel into suitable containers for disposal. Slippery, can cause falls if walked on.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin and eyes.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a cool, well-ventilated place. Protect from moisture.

Incompatible materials Strong oxidizing agents, Acids, Water

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
AMORPHOUS SILICA 7631-86-9	-	(vacated) TWA: 6 mg/m ³ <1% Crystalline silica TWA: 20 mppcf : (80)/(% SiO ₂) mg/m ³ TWA	IDLH: 3000 mg/m ³ TWA: 6 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Eyewash stations

Individual protection measures, such as personal protective equipment

- Eye/face protection** Wear safety glasses with side shields (or goggles).
- Skin and body protection** Wear protective gloves and protective clothing.
- Respiratory protection** Use NIOSH-approved air-purifying respirator with organic vapor cartridge or canister, as appropriate.

General Hygiene Considerations When using do not eat, drink or smoke. Regular cleaning of equipment, work area and clothing is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Paste
Appearance Clear
Odor Acetic acid
Odor threshold No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No information available	
Melting point / freezing point	No information available	
Boiling point / boiling range	Not Applicable	
Flash point	> 93 °C / > 200 °F	Polymerization
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	No information available	
Vapor density	>1	Air = 1
Relative density	0.96	
Water solubility	Not applicable	Polymerization
Solubility in other solvents	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Kinematic viscosity	No information available	
Dynamic viscosity	No information available	
Explosive properties	No information available	
Oxidizing properties	No information available	

Other Information

Softening point No information available
Molecular weight No information available
VOC Content (%) 23 g/L
Density No information available
Bulk density No information available

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Excessive heat.

Incompatible materials

Strong oxidizing agents, Acids, Water

Hazardous Decomposition Products

Carbon oxides

Nitrogen oxides (NOx)

Acetic acid

Formaldehyde

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Inhalation	May cause irritation of respiratory tract.
Eye contact	Contact with eyes may cause irritation. May cause redness and tearing of the eyes.
Skin contact	May cause skin irritation and/or dermatitis.
Ingestion	Ingestion may cause irritation to mucous membranes.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
POLY (DIMETHYLSILOXANE), HYDROXY TERMINATED 70131-67-8	-	> 16 mL/kg (Rabbit)	> 8750 mg/m ³ (Rat) 7 h
DISTILLATES (PETROLEUM), HYDROTREATED MIDDLE 64742-46-7	= 7400 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	= 4.6 mg/L (Rat) 4 h
AMORPHOUS SILICA 7631-86-9	> 5000 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	> 2.2 mg/L (Rat) 1 h
METHYLTRIACTOXYLSILANE 4253-34-3	= 2060 mg/kg (Rat)	-	-

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Germ cell mutagenicity No information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
AMORPHOUS SILICA 7631-86-9	-	Group 3	-	-

IARC (International Agency for Research on Cancer)

Not classifiable as a human carcinogen

Target Organ Effects Eyes, Respiratory system, Skin, Teeth.

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral) 15169 mg/kg

ATEmix (dermal) 4633 mg/kg
 ATEmix (inhalation-dust/mist) 5.5 mg/l

12. ECOLOGICAL INFORMATION

Ecotoxicity

67 % of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
DISTILLATES (PETROLEUM), HYDROTREATED MIDDLE 64742-46-7	-	35: 96 h Pimephales promelas mg/L LC50 flow-through 10000: 96 h Pimephales promelas mg/L LC50 static	-
AMORPHOUS SILICA 7631-86-9	440: 72 h Pseudokirchneriella subcapitata mg/L EC50	5000: 96 h Brachydanio rerio mg/L LC50 static	7600: 48 h Ceriodaphnia dubia mg/L EC50

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Mobility

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

US EPA Waste Number Not applicable

14. TRANSPORT INFORMATION

DOT

Proper shipping name: Not regulated

IATA

Proper shipping name: Not regulated

IMDG

Proper shipping name: Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
 DSL/NDSL Complies
 EINECS/ELINCS Not Listed.

ENCS Not Listed.
IECSC Complies
KECL Complies
PICCS Complies
AICS Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AICS - Australian Inventory of Chemical Substances

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard Yes
Chronic Health Hazard No
Fire hazard No
Sudden release of pressure hazard No
Reactive Hazard No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
AMORPHOUS SILICA 7631-86-9	X	X	X
ACETIC ACID 64-19-7	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

NFPA Health hazards 1 Flammability 1 Instability 0 -
HMIS Health hazards 1 Flammability 1 Physical hazards 0 Personal protection B

NFPA (National Fire Protection Association)
 HMIS (Hazardous Material Information System)

Revision Date 30-Jul-2015

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet