

#### Section 1: IDENTIFICATION

#### 1.1 PRODUCT IDENTIFIER

Product Name: DUPONT™ AIRTITE SILICONIZED ACRYLIC CAULK CLEAR

**Product Code:** 07873, 07874, 07876, 07877

1.2 RECOMMENDED USE OF CHEMICAL AND RESTRICTIONS ON USE

**Use:** Caulking (Exterior).

1.3 DETAILS OF THE SUPPLIER OF THE SAFETY DATA SHEET

Name/Address: Tower Sealants

2095 Memorial Park Road Gainesville, Georgia

30504 USA

**Telephone Number:** 1-770-535-8780

1.4 EMERGENCY TELEPHONE NUMBER

**Emergency Telephone Number:** CHEMTREC: 1-800-424-9300

## Section 2: HAZARD(S) IDENTIFICATION

#### 2.1 CLASSIFICATION OF THE CHEMICAL ACCORDING TO OSHA HAZCOM 2012

**Hazard class** 

Skin irritation 2 Eye irritation 2A Skin sensitization 1

Specific target organ toxicity - Repeated exposure 1

### 2.2 LABEL ELEMENTS ACCORDING TO OSHA HAZCOM 2012

## **Hazard Pictogram:**





Signal Word: Danger

Hazard Statement: Causes skin irritation. Causes serious eye irritation. May cause an

allergic skin reaction. Causes damage to organs through prolonged

or repeated exposure.

**Prevention:** Wash hands thoroughly after handling. Wear protective gloves/eye

protection/face protection. Contaminated work clothing must not be allowed out of the workplace. Do not breathe dust/fume/gas/mist/vapors/spray. Do not eat, drink or smoke when using this product.

Response: Get medical advice/attention if you feel unwell. If on skin: Wash with

plenty of water. Take off contaminated clothing and wash it before reuse. If skin irritation or rash occurs: Get medical advice/attention. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye

irritation persists: Get medical advice/attention.

Trade Name: DUPONT™ AIRTITE SILICONIZED ACRYLIC CAULK CLEAR





Storage: Not applicable.

**Disposal:** Dispose of contents and container in accordance with all local,

regional, national and international regulations.

#### 2.3 ADDITIONAL INFORMATION

Hazards not otherwise classified: Not applicable.

2 % of the mixture consists of ingredient(s) of unknown acute toxicity.

## WHMIS Classification(s):

Class D2A - Teratogenicity and Embryotoxicity

Class D2B - Skin/Eye Irritant

## **WHMIS Hazard Symbols:**



WHMIS Signal Word: WARNING

#### Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

#### 3.1 MIXTURES

Ingredient	CAS No	Wt. %
Polymer, Acrylic (non-hazardous)	Trade Secret	30.0 - 70.0
Sodium lauryl sulfate	151-21-3	0.1 - 5
Ethylene glycol	107-21-1	0.1 - 5
Ammonium hydroxide	1336-21-6	0.1 - 1
Stoddard solvent	8052-41-3	0.1 - 1
[3-(2,3-Epoxypropoxy)propyl]trimethoxysilane	2530-83-8	0.1 - 1
1,2-Benzisothiazolone	2634-33-5	0.1 - 1
3-lodo-2-propynyl butylcarbamate	55406-53-6	0.1 - 1
Ethyl acrylate	140-88-5	< 0.1

The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

#### **Section 4: FIRST- AID MEASURES**

## 4.1 DESCRIPTION OF THE FIRST AID MEASURE

Eye: In case of contact, immediately flush eyes with plenty of water for at

least 15 minutes. If easy to do, remove contact lenses, if worn. If

irritation persists, get medical attention.

**Skin:** In case of contact, immediately flush skin with plenty of water.

Remove contaminated clothing and shoes. Wash clothing before

reuse. Call a physician if irritation develops and persists.

**Inhalation:** If breathing is difficult, remove victim to fresh air and keep at rest in a

position comfortable for breathing. Get medical advice/attention if

you feel unwell.







**Ingestion:** If swallowed, do NOT induce vomiting unless directed to do so by

medical personnel. Never give anything by mouth to an unconscious

person. Get medical advice/attention if you feel unwell.

## 4.2 MOST IMPORTANT SYMPTOMS AND EFFECTS, BOTH ACUTE AND DELAYED

Eye: Causes serious eye irritation. Symptoms may include discomfort or

pain, excess blinking and tear production, with marked redness and

swelling of the conjunctiva.

**Skin:** Causes skin irritation. Symptoms may include redness, edema, drying,

defatting and cracking of the skin. May cause an allergic skin reaction.

**Inhalation:** May cause respiratory tract irritation. May cause headache and dizziness.

Ingestion: May be harmful if swallowed. May cause stomach distress, nausea

or vomiting.

#### 4.3 INDICATION OF ANY IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENTS NEEDED

**Note to Physicians:** Symptoms may not appear immediately.

Specific Treatments: In case of accident or if you feel unwell, seek medical advice

immediately (show the label or SDS where possible).

## **Section 5: FIRE-FIGHTING MEASURES**

#### **5.1 FLAMMABILITY**

Flammability: Not flammable by WHMIS/OSHA criteria.

**5.2 EXTINGUISHING MEDIA** 

**Suitable Extinguishing Media:** Powder, water spray, foam, carbon dioxide.

**Unsuitable Extinguishing Media:** None known.

## 5.3 SPECIAL HAZARDS ARISING FROM THE CHEMICAL

**Products of Combustion:** May include, and are not limited to: oxides of carbon.

**Explosion Data:** 

Sensitivity to Mechanical Impact: Not available. Sensitivity to Static Discharge: Not available.

#### 5.4 SPECIAL PROTECTIVE EQUIPMENT AND PRECAUTIONS FOR FIRE FIGHTERS

Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA). Use water spray to keep fire-exposed containers cool. Material may splatter if heated above 93°C / 200°F.

#### Section 6: ACCIDENTAL RELEASE MEASURES

#### 6.1 PERSONAL PRECAUTIONS, PROTECTIVE EQUIPMENT AND EMERGENCY PROCEDURES

Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel. Avoid contact with skin and eyes.

## 6.2 METHODS AND MATERIALS FOR CONTAINMENT AND CLEANING - UP

Methods for Containment: Contain spill, then place in a suitable container. Do not flush to

sewer or allow to enter waterways. Use appropriate Personal

Protective Equipment (PPE).

Trade Name: DUPONT™ AIRTITE SILICONIZED ACRYLIC CAULK CLEAR

Page 3 of 10

NEXREG



Methods for Cleaning-Up: Preferred method would be to scrape up spilled material and place in

secondary container for disposal. Smaller spills can also be wiped up. Residual material can be removed with the assistance of hot

water and soap. Provide ventilation.

## **Section 7: HANDLING AND STORAGE**

#### 7.1 PRECAUTIONS FOR SAFE HANDLING

Handling: Avoid contact with skin and eyes. Do not swallow. Do not breathe

dust/fume/gas/mist/vapors/spray. Handle and open container with care. Use only in well-ventilated areas. When using do not eat, drink

or smoke. (See section 8)

General Hygiene Advice: Launder contaminated clothing before reuse. Wash hands before

eating, drinking, or smoking.

## 7.2 CONDITIONS FOR SAFE STORAGE, INCLUDING ANY INCOMPATIBILITIES

Storage: Keep out of the reach of children. Keep container tightly closed.

Store in a dry, cool and well-ventilated area. Keep from freezing.

(See section 10)

## Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

## **8.1 CONTROL PARAMETERS**

## **Exposure Guidelines**

Occupational Exposure Limits		
Ingredient	OSHA-PEL ACGIH	
-		
Sodium lauryl sulfate	Not available.	Not available.
		100 mg/m <sup>3</sup> Ceiling
Ethylene glycol	Not available.	(aerosol only)
Ammonium hydroxide	Not available.	Not available.
Stoddard solvent	2900 mg/m³; 500 ppm	100 ppm
[3-(2,3-Epoxypropoxy)propyl]trimethoxysilane	Not available.	Not available.
1,2-Benzisothiazolone	Not available.	Not available.
3-lodo-2-propynyl butylcarbamate	Not available.	Not available.
Ethyl acrylate	5 ppm	5 ppm

#### **8.2 EXPOSURE CONTROLS**

**Engineering Controls:** Use ventilation adequate to keep exposures (airborne levels of dust,

fume, vapor, etc.) below recommended exposure limits.


## **8.3 INDIVIDUAL PROTECTIVE MEASURES**

Personal Protective Equipment:

**Eye/Face Protection:** Wear eye protection.

Skin Protection:

Hand Protection: Wear chemical resistant gloves.Body Protection: Wear suitable protective clothing.





Print date: 2014-11-21



**Respiratory Protection:** In case of insufficient ventilation, wear suitable respiratory equipment.

Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the

selected respirator.

General Health and Safety Measures: Do not eat, smoke or drink where material is handled, processed

or stored. Wash hands carefully before eating or smoking.

## **Section 9: PHYSICAL AND CHEMICAL PROPERTIES**

#### 9.1 INFORMATION ON BASIC PHYSICAL AND CHEMICAL PROPERTIES

Appearance: Paste

**Color:** White when wet, clear when dries.

**Odor:** Sweet acrylic, with a mild ammonia odor.

Odor Threshold: Not available.

Physical State: Liquid. pH: 7.5 – 9.0

Melting Point/Freezing Point:< 0 °C (< 32 °F)</td>Initial Boiling Point and Boiling Range:> 93 °C (> 200 °F)Flash Point:Not applicable.Evaporation Rate:Slower than ether.

Flammability: Not flammable.

Lower Flammability/Explosive Limit: Not available.

Upper Flammability/Explosive Limit: Not available.

Vapor Pressure: 25 mm Hg @ 20 °C (68 °F)

Vapor Density: > 1 (Air = 1)Relative Density/Specific Gravity: Not available. Solubility: Dispersible. Partition coefficient: n-octanol/water: Not available. **Auto-ignition Temperature:** Not available. **Decomposition Temperature:** Not available. Not available. Viscosity: **Explosive Properties:** Not available. **Oxidizing Properties:** Not available.

## **Section 10: STABILITY AND REACTIVITY**


#### **10.1 REACTIVITY**

No dangerous reaction known under conditions of normal use.

## **10.2 CHEMICAL STABILITY**

Stable under normal storage conditions.

Trade Name: DUPONT™ AIRTITE SILICONIZED ACRYLIC CAULK CLEAR



Print date: 2014-11-21



#### 10.3 POSSIBILITY OF HAZARDOUS REACTIONS

No dangerous reaction known under conditions of normal use.

#### **10.4 CONDITIONS TO AVOID**

Heat. Incompatible materials.

#### **10.5 INCOMPATIBLE MATERIALS**

Oxidizers.

## **10.6 HAZARDOUS DECOMPOSITION PRODUCTS**

May include, and are not limited to: oxides of carbon.

## **Section 11: TOXICOLOGICAL INFORMATION**

## 11.1 INFORMATION ON TOXICOLOGICAL EFFECTS

**Likely Routes of Exposure:** Skin contact, skin absorption, eye contact, inhalation, and ingestion.

Symptoms related to physical/chemical/toxicological characteristics:

Eye: Causes serious eye irritation. Symptoms may include discomfort or pain,

excess blinking and tear production, with marked redness and swelling of

the conjunctiva.

**Skin:** Causes skin irritation. Symptoms may include redness, edema, drying,

defatting and cracking of the skin. May cause an allergic skin reaction.


**Ingestion:** May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

**Inhalation:** May cause respiratory tract irritation. May cause headache and dizziness.

## **Acute Toxicity:**

Ingredient	LC50	LD50
-		
	Inhalation	Oral 1288 mg/kg, rat
Sodium lauryl sulfate	>3900 mg/m <sup>3</sup> 1h, rat	Dermal 580 mg/kg, rabbit
		Oral 4000 mg/kg, rat
Ethylene glycol	Not available.	Dermal 9530 µL/kg, rabbit
Ammonium hydroxide	Not available.	Oral 350 mg/kg, rat
Stoddard solvent	Not available.	Not available.
	Inhalation	Oral 22600 µL/kg, rat
[3-(2,3-Epoxypropoxy)propyl]trimethoxysilane	> 5.3 mg/L 4h, rat	Dermal 3970 µL/kg, rabbit
1,2-Benzisothiazolone	Not available.	Oral 1020 mg/kg, rat
	Inhalation	Oral 300-500 mg/kg, rat
3-lodo-2-propynyl butylcarbamate	0.78 mg/L 4h, rat	Dermal >2000 mg/kg, rat
	Inhalation	Oral 800 mg/kg, rat
Ethyl acrylate	1414 ppm 4 h, rat	Dermal 500 µL/kg, rabbit

Calculated overall Chemical Acute Toxicity Values			
LC50 (inhalation) LD50 (oral) LD50 (dermal)			
>20 mg/L 4h, rat	> 2000 mg/kg, rat	> 2000 mg/kg, rabbit	





Ingredient	Chemical Listed as Carcinogen or Potential Carcinogen (NTP, IARC, OSHA, ACGIH, CP65)*	
-		
Sodium lauryl sulfate	Not listed.	
Ethylene glycol	G-A4	
Ammonium hydroxide	Not listed.	
Stoddard solvent	Not listed.	
[3-(2,3-Epoxypropoxy)propyl]trimethoxysilane	Not listed.	
1,2-Benzisothiazolone	Not listed.	
3-lodo-2-propynyl butylcarbamate	Not listed.	
Ethyl acrylate	G-A4, I-2B, O, CP65	

<sup>\*</sup> See Section 15 for more information.

#### 11.2 DELAYED. IMMEDIATE. AND CHRONIC EFFECTS OF SHORT- AND LONG-TERM EXPOSURE

**Skin Corrosion/Irritation:** Causes skin irritation.

Serious Eye Damage/Irritation: Causes serious eye irritation.

**Respiratory Sensitization:** Based on available data, the classification criteria are not met.

**Skin Sensitization:** May cause an allergic skin reaction.

STOT-Single Exposure: Based on available data, the classification criteria are not met.

**Chronic Health Effects:** 

Carcinogenicity: Based on available data, the classification criteria are not met.

Germ Cell Mutagenicity: Based on available data, the classification criteria are not met.

**Reproductive Toxicity:** 

**Developmental:** Based on available data, the classification criteria are not met.

**Teratogenicity:** Hazardous by WHMIS criteria. **Embryotoxicity:** Hazardous by WHMIS criteria.

Fertility: Based on available data, the classification criteria are not met.

STOT-Repeated Exposure: Causes damage to organs through prolonged or repeated exposure.

Aspiration Hazard: Based on available data, the classification criteria are not met.

**Toxicologically Synergistic Materials:** Not available.

Other Information: Not available.

## **Section 12: ECOLOGICAL INFORMATION**

## **12.1 ECOTOXICITY**

**Acute/Chronic Toxicity:** May cause long-term adverse effects in the aquatic environment.

12.2 PERSISTENCE AND DEGRADABILITY

Not available.

12.3 BIOACCUMULATIVE POTENTIAL

Bioaccumulation: Not available.





#### **12.4 MOBILITY IN SOIL**

Not available.

## 12.5 OTHER ADVERSE EFFECTS

Not available.

**Section 13: DISPOSAL CONSIDERATIONS** 

13.1 WASTE TREATMENT METHODS

Disposal Method: This material must be disposed of in accordance with all

local, state, provincial, and federal regulations.

Other disposal recommendations: Not available.

**Section 14: TRANSPORT INFORMATION** 

**14.1 UN NUMBER** 

DOT TDG

Not regulated. Not regulated.

14.2 UN PROPER SHIPPING NAME

DOT TDG

Not applicable. Not applicable.

14.3 TRANSPORT HAZARD CLASS (ES)

DOT TDG

Not applicable. Not applicable.

**14.4 PACKING GROUP** 

DOT TDG

Not applicable. Not applicable.

14.5 ENVIRONMENTAL HAZARDS

Not available.

14.6 TRANSPORT IN BULK ACCORDING TO ANNEX II OF MARPOL 73/78 AND THE IBC CODE

Not available.

14.7 SPECIAL PRECAUTIONS FOR USER

Do not handle until all safety precautions have been read and understood.

**Section 15: REGULATORY INFORMATION** 

# 15.1 SAFETY, HEALTH AND ENVIRONMENTAL REGULATIONS/ LEGISLATIONS SPECIFIC FOR THE CHEMICAL

**Canada:** This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the SDS contains all the information required by the Controlled Products Regulations.

**US:** SDS prepared pursuant to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012





SARA Title III				
Ingredient	Section 302 (EHS) TPQ (lbs.)	Section 304 EHS RQ (lbs.)	CERCLA RQ (lbs.)	Section 313
-				
Sodium lauryl sulfate	Not listed.	Not listed.	Not listed.	Not listed.
Ethylene glycol	Not listed.	Not listed.	5,000	313
Ammonium hydroxide	Not listed.	Not listed.	1,000	313
Stoddard solvent	Not listed.	Not listed.	Not listed.	Not listed.
[3-(2,3-Epoxypropoxy)propyl]				
trimethoxysilane	Not listed.	Not listed.	Not listed.	Not listed.
1,2-Benzisothiazolone	Not listed.	Not listed.	Not listed.	Not listed.
3-lodo-2-propynyl butylcarbamate	Not listed.	Not listed.	Not listed.	313
Ethyl acrylate	Not listed.	Not listed.	1,000	313

## **State Regulations**

## **California Proposition 65:**

This product contains a chemical known to the State of California to cause cancer.

## **Global Inventories:**

Ingredient	Canada DSL/NDSL	USA TSCA
	DOE/NDOE	100/1
-		
Sodium lauryl sulfate	DSL	Yes.
Ethylene glycol	DSL	Yes.
Ammonium hydroxide	DSL	Yes.
Stoddard solvent	DSL	Yes.
[3-(2,3-Epoxypropoxy)propyl]trimethoxysilane	DSL	Yes.
1,2-Benzisothiazolone	DSL	Yes.
3-lodo-2-propynyl butylcarbamate	DSL	Yes.
Ethyl acrylate	DSL	Yes.

NFPA National Fire Protection Association:			
Health: 1			
Fire:	0		
Reactivity:	0		

HMIS-Hazardous Materials Identification System		
Health:	1*	
Fire:	0	
Physical Hazard:	0	

**Hazard Rating:** 0 = minimal, 1 = slight, 2 = moderate, 3 = severe, 4 = extreme

## SOURCE AGENCY CARCINOGEN CLASSIFICATIONS:

CP65 California Proposition 65

OSHA (O) Occupational Safety and Health Administration.

ACGIH (G) American Conference of Governmental Industrial Hygienists.


A1 - Confirmed human carcinogen.

A2 - Suspected human carcinogen.

A3 - Animal carcinogen.

A4 - Not classifiable as a human carcinogen.

A5 - Not suspected as a human carcinogen.





International Agency for Research on Cancer.

1 - The agent (mixture) is carcinogenic to humans. IARC (I)

2A - The agent (mixture) is probably carcinogenic to humans; there is limited evidence of carcinogenicity in humans and sufficient evidence of carcinogenicity in experimental animals.

2B - The agent (mixture) is possibly carcinogenic to humans; there is limited evidence of carcinogenicity in humans in the absence of sufficient evidence of carcinogenicity in experimental animals.

3 - The agent (mixture, exposure circumstance) is not classifiable as to its carcinogenicity to humans.

4 - The agent (mixture, exposure circumstance) is probably not carcinogenic to humans.

#### NTP (N) National Toxicology Program.

1 - Known to be carcinogens.

2 - Reasonably anticipated to be carcinogens.

## **Section 16: OTHER INFORMATION**

**Date of Preparation: Nov**ember 21, 2014 **Expiry Date:** November 21, 2017

Version: 1.0

**Revision Date:** November 21, 2014

Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.

Nexreg Compliance Inc. Prepared by:

Phone: (519) 488-5126

www.nexrea.com

Prepared for: **Tower Sealants** 

**End of Safety Data Sheet** 

NEXREG

Print date: 2014-11-21