

PS400

Portable Bench Scales CE



- **0.1% Accuracy**
- **Capacity**– 181 kg / 400 lb
- **Construction**– 22 gauge steel with ribbed base with ABS plastic indicator
- **Display**– Large and visible
- **Power**– Battery or AC power
- **Large Push Buttons**

VALUE IN
WEIGHING

PS400 Portable Bench Scales

Features

PS400 is particularly suited to shipping/warehouse applications and general purpose weighing. These are very affordable scales with high accuracy.

A large, simple to read display can be wall or desk mounted for easy visibility and the large keyboard switches even work for gloved hands. The display cable is a coil style for durability and easy extension to the wall or desk mount.

Specifications

Capacity: 181 kg x 0.2 kg / 400 lb x 0.5 lb

Platform Dimension: 309 mm x 297 mm / 12.2" x 11.7"

Display: 25 mm / 1.0" LCD

Power Supply: Six AA batteries or 9 VDC, 100mA adapter (both included)

Shipping Weight: 5 kg / 11 lb

Certifications: CE

Product Code: 816965000517



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031
Toll free: 800-637-0529, Tel: 507-238-8702
Fax: 507-238-8271
e-mail: sales@brecknellscales.com
www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick
West Midlands B66 2LP UK
Tel: +44 (0) 845 246 6717
Fax: +44 (0) 845 246 6718
Email: sales@brecknellscales.co.uk
www.brecknellscales.co.uk

