

# 2360P100 Adjustable Strap Disposable Respirators



## P100 PROTECTION

99.97% efficient against oil and non-oil based particulates.

## ALL DAY COMFORT

Molded nose bridge with foam face cushion fits easily and comfortably without a metal noseband. Exclusive Ventex® valve lets the hot air out faster so breathing resistance is reduced and workers stay cooler. Adjustable cloth straps allow a comfortable fit with a simple tug on the straps.

## DURA-MESH® SHELL LASTS LONGER

The exclusive Dura-Mesh® shell protects the filter media so it stays cleaner looking longer. The shell also resists collapsing in hot, humid environments so the respirator holds its shape longer. The result is fewer respirators used and lower costs.

## APPLICATIONS

Environments where an OSHA substance specific standard applies (lead, cadmium, arsenic, MDA) as well as pharmaceutical manufacturing, battery manufacturing, conventional and nuclear power generation, welding, cutting and metal pouring.

## FEATURES

- 100% PVC-Free.
- Adjustable cloth straps assure a snug, cool and comfortable fit.
- Ventex® valve lets the hot air out faster so workers breathe easier and stay cooler.
- Soft foam face cushion for added comfort and no pressure points.
- Dura-Mesh® shell resists collapsing in heat and humidity.
- Contour molded nose bridge seals without a metal noseband.
- 99.97% efficient against oil and non-oil based particulates.
- Meets heat and flame resistance in accordance with ANSI/ISEA 110.2003 Section 7.11.1.



## USE AGAINST:

1. Oil or non-oil particulate aerosols.

## DO NOT USE AGAINST:

1. Concentrations of contaminants which are unknown, or are immediately dangerous to life or health.
2. Concentrations of particulates which exceed the maximum use concentration or 10 times the OSHA Permissible Exposure Limit, whichever is lower.
3. Gases, vapors, asbestos, paint spray, sandblasting or particulate materials which generate harmful vapors.
4. Oil-based mists for longer than one 8 hour work shift.

## RESTRICTIONS

1. This respirator does not supply oxygen and must not be used in atmospheres containing less than 19.5% oxygen.
2. Do not remain in contaminated area if any physical distress occurs, for example breathing difficulty, dizziness or nausea.
3. Leave contaminated area and replace respirator if it is damaged, distorted, a proper fit can not be obtained or breathing becomes difficult.
4. Prior to each use, carefully inspect the entire respirator, including filter media and strap/weld attachment area for tears and damage. Staple or strap/weld attachment perforations do not affect respirator performance.
5. Do not alter, modify, or abuse this respirator.
6. Store unused respirators in box/bag in a clean, dry, non-contaminated area.
7. Dispose of respirator according to your employer's policy and local regulations.
8. Where oil mists are present dispose no later than 8 hours after first use. Where non-oil particulates only are present, dispose no later than 30 days after first use.
9. Use respirator before the "use by" expiration date printed on box/bag.
10. If used for welding, wear appropriate eye and face protection.

## TECHNICAL SERVICE HELP LINE

For technical assistance, call Moldex Technical Service Department at +1 (310) 837-6500 ext. 512/550 or +1 (800) 421-0668 ext. 512/550.

### MOLDEX-METRIC, INC.

10111 W. Jefferson Blvd. Culver City, CA 90232  
TEL: +1 (800) 421-0668 or +1 (310) 837-6500 FAX +1 (310) 837-9563  
www.moldex.com e-mail: sales@moldex.com

### CANADIAN CUSTOMER SERVICE

TEL: +1 (310) 837-6500, Ext. 517  
FAX: +1 (310) 837-9563

Moldex, Ideas that wear well, Ventex, Softspun and Dura-Mesh are registered trademarks of Moldex-Metric, Inc. The mesh design is a trademark of Moldex-Metric, Inc.  
U.S. Patents #D285,374, #D389,239, #6,571,797, #6,047,698 and #4,850,347  
Made in the U.S.A. 9701-798 REV E 08/14



Moldex-Metric, Inc.  
CULVER CITY, CALIFORNIA, 90232  
+1 (800) 421-0668



THIS RESPIRATOR IS APPROVED ONLY IN THE FOLLOWING CONFIGURATION:			
TC-	PROTECTION <sup>1</sup>	RESPIRATOR	CAUTIONS AND LIMITATIONS <sup>2</sup>
		2360P100	
84A-3642	P100	X	A B C J M N O P

**1. Protection**  
P100-Particulate Filter (99.97% filter efficiency level) effective against all particulate aerosols.

**2. Cautions and Limitations**  
A- Not for use in atmospheres containing less than 19.5 percent oxygen.  
B- Not for use in atmospheres immediately dangerous to life or health.  
C- Do not exceed maximum use concentrations established by regulatory standards.  
J- Failure to properly use and maintain this product could result in injury or death.  
M- All approved respirators shall be selected, fitted, used, and maintained in accordance with MSHA, OSHA, and other applicable regulations.  
N- Never substitute, modify, add, or omit parts. Use only exact replacement parts in the configurations as specified by the manufacturer.  
O- Refer to User's Instructions, and/or maintenance manuals for information on use and maintenance of these respirators.  
P- NIOSH does not evaluate respirators as surgical masks.

## PACKAGING

**2360P100, Medium/Large**  
5 Respirators per Bag  
4 Bags per Case

## LIMITED WARRANTY IMPORTANT NOTICE TO PURCHASER

This limited warranty is made in lieu of the warranties of merchantability, fitness for particular purposes and all other warranties, express or implied. There are no other warranties which extend beyond the description on the face hereof. The physical standards and specifications of Moldex will be met by products sold. Exclusive Remedies: damages for the breach of this limited warranty are limited to the replacement of such quantity of Moldex products proved to be defectively manufactured. Except as provided above, Moldex shall not be liable or responsible for any loss, damages, or liability, direct, indirect, incidental, special or consequential, arising out of a sale, use or misuse, or the inability to use products by the user.



## WARNING TO USER

1. Follow all instructions and warnings on the use of this respirator and wear during all times of exposure. Failure to do so will reduce respirator effectiveness, wearer protection and may result in sickness or death.
2. Before use, the user must first be trained by the employer in proper respirator use, in accordance with applicable safety and health standards, for the contaminant and exposure level in the assigned work area.
3. The particulates and other contaminants which can be dangerous to your health include those which you cannot see, taste, or smell.
4. This product has not been sold with warnings or use instructions for personnel involved in healthcare or related situations, where there may be the possibility of contact with disease or biological hazards. If you are considering such uses, first call the Moldex Technical Service Dept., +1 (310) 837-6500 or +1 (800) 421-0668 ext. 512/550.

## DISTRIBUTED BY:

