



TECHNICAL SPECIFICATION




FRONT VIEW



SIDE VIEW



PLAN VIEW



Machine dimensions

Height: 24.8 in. (631 mm), Amp width: 6.1 in. (154 mm),

Amp depth: 4.4 in. (112 mm), Base diameter: 8.7 in. (222 mm)

dyson pure hot+cool link

Electrical

Input voltage/frequency: 120V / 60Hz
Standby power consumption: <0.5W
Max input power (heater mode): 1575W
Max input power (fan mode): 44W
Min input power (fan mode): 36W

Construction

Polycarbonate
ABS

Filter

Removes 99.97% of allergens and pollutants as small as 0.3 microns from the air
360° borosilicate glass microfiber HEPA filter
Activated carbon filter
Rubber vacuum seals
Filter life: One year based on 12 hr. use a day; or 6 months based on 24 hr. use a day
Height: 6.2 in. (159 mm)
Diameter: 8.4 in. (214 mm)
Unboxed weight: 0.73 lb.

Operation

For indoor use only
Operation environment:
Engineered to operate between 0-104°F (0-40°C), 0-100% humidity
10 speed settings
70° oscillation
62-80° diffusion angle
40° tilt
Auto mode:
Automatically monitors air quality and adjusts airflow accordingly
Quiet mode: Purifies and cools you using the quiet setting
Standby mode
Sleep time increments: 15 min., 30 min., 45 min., 1-9 hrs.
Hidden LED display
Intelligent thermostat heater mode
CADR rate: 60 cfm¹
Sound level at min flow rate: Quieter than 45 dB(A)
Sound level at max flow rate: 64 dB(A)
Remote control battery: CR2032L coin cell
Remote control functions: On/Off, airflow, temperature, Jet Focus control, oscillation, cooling mode, sleep timer, auto mode, night mode

Dyson Link app

Automatically monitors, reacts and purifies²
Live air quality metrics straight to your smart phone²
Requires iOS 8.0 or later or Android 4.0 or later

Logistics

Single unit order code:
White/Silver: 305571-01
Iron/Blue: 305570-01
Unit barcode:
White/Silver: 885609009827
Iron/Blue: 885609009810
Net weight: 8 lb. 9 oz. (3.9 kg)
Packaged weight: 12 lb. 9 oz. (5.7 kg)
Packaged dimensions:
(H) 27.3 in. (694 mm) x (W) 10.23 in. (260 mm) x (D) 10.27 in. (261 mm)
Cable length: 5.9 ft. (1.8 m)

Standard warranty

2 year warranty – parts and labor



Product range

White/Silver Iron/Blue Remote



Certified **asthma & allergy friendly**[™] by Allergy Standards Limited. ASTHMA & ALLERGY FRIENDLY and ASTHMA & ALLERGY FRIENDLY LOGO are certification marks and trademarks of ALLERGY STANDARDS LIMITED. The ASTHMA AND ALLERGY FOUNDATION OF AMERICA is a Registered Trademark of AAFA.



For further information contact:
www.globalindustrial.com
888.978.7759

¹ Clean Air Delivery Rate for smoke tested to AHAM AC1.

² Standard data and messaging rates may apply. Requires Wifi and app-enabled device.