



N9674
NINJA
 Dipped
 Specification Sheet

PRODUCT DESCRIPTION:

Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. Common features to all styles include individual packaging for point of sale display, treated with Actifresh® to kill bacteria and promote freshness, and available in sizes small through extra large.

FEATURES:

- 15 guage black nylon/Lycra shell.
- Bi-Polymer Palm and Fingertips coated
- Great dexterity and sense of touch
- Comfortable and Cool
- EN388 score 412X

APPLICATIONS:


Abrasive applications, Assembly, Brick handling, Construction, Farming, General maintenance, Landscaping, Plumbing, Recycling, Shipping / receiving

TECHNICAL DATA FOR: N9674L

Material: Nylon
Gauge: 15 Gauge
Shell Color: Black
Dots-Blocks-Coatings: Coated Palm, Coated Palm
Palm: Black, Flat, Bi-Polymer
Cuff: Knitted, Knit Wrist
Treated with Actifresh: Yes




Hemmed: Yes
Hem Color: White
Packaging Hand Tag: Hangtag
Packaging Inner Pack: Polybag 12
CE Abrasion: 4
CE Cut: 1
CE Tear: 2
CE Puncture: X
Country Of Origin: Pakistan



| <u>Item No:</u> | <u>Size:</u> | <u>A:</u> | <u>B:</u> | <u>C:</u> | <u>Case Weight:</u> | <u>UOM Weight:</u> |
|-----------------|--------------|-----------|-----------|-----------|---------------------|--------------------|
| N9674L | Large | 6.78 | 4.88 | 3.39 | 18.313 LB | 1.526 LB |



N9674
NINJA
Dipped
Specification Sheet



| <u>Item No:</u> | <u>Size:</u> | <u>A:</u> | <u>B:</u> | <u>C:</u> | <u>Case Weight:</u> | <u>UOM Weight:</u> |
|-----------------|--------------|-----------|-----------|-----------|---------------------|--------------------|
| N9674M | Medium | 6.66 | 4.56 | 3.35 | 17.310 LB | 1.443 LB |
| N9674S | Small | 6.50 | 4.24 | 3.35 | 15.310 LB | 1.276 LB |
| N9674XL | X - Large | 7.16 | 5.15 | 3.70 | 18.983 LB | 1.582 LB |
| N9674XS | X - Small | n/a | n/a | n/a | 15.610 LB | 1.301 LB |