

PRODUCT SPECIFICATIONS

Hinged, Self-Tracking Rope Grab

#7479

Material Specifications

Ring/body: *Alloy Steel; Min. 3,600 lbs. tensile strength*

Performance Specifications

Tensile Strength: *Min. 3,600 lbs.*

Max. Capacity: *310 lbs.*

Max. Freefall: *6 feet*

Max. Arrest Force: *Less than 1,800 lbs.*

Max. Elongation: *54 inches*

Relevant Standards

OSHA: *CFR1926.502, CFR1910.66*

ANSI: *A10.32-2004*

Warnings

- Read, understand and follow all labels and instructions prior to use.
- Inspect before each use.
- Remove from service if there is evidence of damage or excessive wear.
- Remove from service if there is any signs of activation.
- Never attach a Shock Absorbing Lanyard to the front or side D-rings.



This product must be used in conjunction with a 3' Shock-Absorbing Lanyard and rigged to allow a 6' max. free-fall.

Rope grab meets the requirements of ANSI Z359.1-2007 for strength and dynamic performance