

FRIGIDAIRE®

# PTAC

## 2017 Air Conditioner Collection



# FRIGIDAIRE®

## PTAC COLLECTION



The Frigidaire® 2017 PTAC Collection offers flexibility for any application. Simple, intuitive controls and options, including remote thermostats, allow users to create the ultimate relaxing atmosphere. Efficient, versatile designs that save energy are better for budgets and the environment. That's why Frigidaire® PTAC products offer cost-saving features — including our Energy-Saver function — that maximize energy efficiency while keeping guests comfortable.

# SIGNATURE FEATURES

## Corrosion Guard

All Frigidaire® PTACs come standard with corrosion guard, to increase system and component durability in standard applications and protect system and components in coastal areas where air-sea salt content is higher than standard applications. All coils are treated with a dual hydrophilic coating, and there is an added hydrophilic coating for all connecting plates. Standard materials have been replaced with stainless steel for critical components such as hardware, condenser side panel, compressor hardware and condenser fan hardware. Special corrosion-guard paint is used on the drain pan to ensure the integrity of unit mounts to the chassis.

## Dry Mode

For increased comfort and humidity management, an added “Dry Mode” is standard on all Frigidaire® PTACs. This mode feature will help manage and reduce the humidity content within the living space, making it more comfortable. In DRY mode, the unit will modulate cooling mode at low fan speed until the room temperature is 4° F below the room temperature setting regardless of fan mode selection.

## Effortless Operation

Improved energy efficient units following our successful 2016 PTAC lineup. Simple room controls are easy for guests to operate — ensuring a relaxing, enjoyable visit every time. Features such as Effortless™ Restart and easy-to-use LCD controls create fewer maintenance calls for management.

## Intuitive Control

Frigidaire® PTACs are designed for adaptability for any climate or guest preference. With the convenience of wall or optional remote thermostats, guests can control the temperature and air movement to create their ultimate comfort zone. Quiet fan motors ensure peaceful sleep.

## Low Maintenance

Frigidaire® has a reputation for durability, easy maintenance and reliable parts and service, so you’re sure to get the highest-quality performance. Plus, the Energy-Saver function maximizes energy efficiency while keeping guests comfortable.


## PTAC Models

### Cool/Electric Heat

Deliver comfort and convenience with electric heat-element models designed to efficiently cool and dehumidify, as well as heat. Available in a variety of BTU ratings to handle room sizes from 300 sq. ft. to 830 sq. ft.

### Cool/Heat Pump with Backup Electric Heat

Designed to cool, heat and dehumidify for greater efficiency in cooler climates, these electric heat-element models feature an additional heat pump that extracts heat from the air and transfers it inside, increasing energy efficiency. As the outdoor temperature drops, the PTAC will automatically switch from heat pump to electric heat as necessary. Available in a variety of BTU ratings.



# PTAC SPECIFICATIONS

## Air Conditioners with Electric Heat

All models come with Corrosion Guard.

PERFORMANCE (230/208V)	FFRP072LT2	FFRP072LT3	FFRP092LT2	FFRP092LT3	FFRP122LT3	FFRP152LT3	FFRP152LT4
BTU (Cool)	7,200/7,000	7,200/7,000	9,400/9,200	9,400/9,200	11,800/11,600	14,500/14,200	14,500/14,200
BTU (Electric Heater)	8,300/6,800	11,700/9,600	8,300/6,800	11,700/9,600	11,700/9,600	11,700/9,600	17,000/13,900
Dehumidification (Pints per Hour)	1.7	1.7	2.1	2.1	2.7	3.5	3.5
Cool Area (Approx. Sq.Ft.)	300	300	450	450	620	830	830
Energy Efficiency Ratio	13.0	13.0	12.1	12.1	11.6	10.4	10.4
Air Volume CFM (High/Low)	312/282	312/282	330/294	330/294	341/306	341/306	341/306
Dry Mode	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Noise Level dB (High/Low)	50/48	50/48	52/50	52/50	53/50	54/51	54/51
<b>ELECTRICAL</b>							
Volts / Hertz	230/208V / 60Hz	230/208V / 60Hz	230/208V / 60Hz	230/208V / 60Hz	230/208V / 60Hz	230/208V / 60Hz	230/208V / 60Hz
Amps (Cool)	2.7/2.9	2.7/2.9	3.7/3.9	3.7/3.9	4.9/5.1	6.2/6.7	6.2/6.7
Amps (Electric Heater)	10.7/9.7	15.0/13.6	10.7/9.7	15.0/13.6	15.0/13.6	15.0/13.6	21.8/19.7
Watts (Cool)	550/535	550/535	775/760	775/760	1,015/1,000	1,390/1,365	1,390/1,365
Watts (Electric Heater)	2,450/2,000	3,450/2,820	2,450/2,000	3,450/2,820	3,450/2,820	3,450/2,820	5,000/4,089
Cable Included	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Length of Power Cord	5.5'	5.5'	5.5'	5.5'	5.5'	5.5'	5.5'
Circuit Breaker	15A	20A	15A	20A	20A	20A	30A
Plug Type (NEMA)	LCDD 6-15P	LCDD 6-20P	LCDD 6-15P	LCDD 6-20P	LCDD 6-20P	LCDD 6-20P	LCDD 6-30P
<b>SPECIFICATIONS</b>							
Refrigerant / Charge	R410a / 22.90 oz.	R410 / 22.90 oz.	R410a / 23.60 oz.	R410 / 23.60 oz.	R410a / 35.27 oz.	R410a / 35.27 oz.	R410a / 35.27 oz.
Product Weight	104 Lbs.	104 Lbs.	113 Lbs.	113 Lbs.	116 Lbs.	118 Lbs.	120 Lbs.
Shipping Weight (Approx.)	128 Lbs.	128 Lbs.	137 Lbs.	137 Lbs.	140 Lbs.	142 Lbs.	144 Lbs.
Product Dimensions (Overall Unit including Front Cover) – A – Height x B – Width x C – Depth	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"
Inside Sleeve Depth	13-13/16"	13-13/16"	13-13/16"	13-13/16"	13-13/16"	13-13/16"	13-13/16"
<b>Wall Cutout Dimensions –</b>							
Height x Width	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"


PERFORMANCE (265V)	FFRP072LT5	FFRP072LT6	FFRP092LT5	FFRP092LT6	FFRP122LT6	FFRP152LT6	FFRP152LT7
BTU (Cool)	7,200	7,200	9,400	9,400	11,800	14,500	14,500
BTU (Electric Heater)	8,300	11,700	8,300	11,700	11,700	11,700	17,000
Dehumidification (Pints per Hour)	1.7	1.7	2.1	2.1	2.7	3.5	3.5
Cool Area (Approx. Sq.Ft.)	300	300	450	450	620	830	830
Energy Efficiency Ratio	13.0	13.0	12.1	12.1	11.6	10.4	10.4
Air Volume CFM (High/Low)	312/282	312/282	330/294	330/294	341/306	341/306	341/306
Dry Mode	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Noise Level dB (High/Low)	50/48	50/48	52/50	52/50	53/50	54/51	54/51
<b>ELECTRICAL</b>							
Volts / Hertz	265V / 60Hz	265V / 60Hz	265V / 60Hz	265V / 60Hz	265V / 60Hz	265V / 60Hz	265V / 60Hz
Amps (Cool)	2.4	2.4	3.3	3.3	4.2	5.4	5.4
Amps (Electric Heater)	9.3	13.1	9.3	13.1	13.0	13.0	18.9
Watts (Cool)	550	550	775	775	1,015	1,390	1,390
Watts (Electric Heater)	2,450	3,450	2,450	3,450	3,450	3,450	5,000
Cable Included	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Length of Power Cord	2.3'	2.3'	2.3'	2.3'	2.3'	2.3'	2.3'
Circuit Breaker	15A	20A	15A	20A	20A	20A	30A
Plug Type (NEMA)	LCDD 7-15P	LCDD 7-20P	LCDD 7-15P	LCDD 7-20P	LCDD 7-20P	LCDD 7-20P	LCDD 7-30P
<b>SPECIFICATIONS</b>							
Refrigerant / Charge	R410a / 22.9 oz.	R410a / 22.9 oz.	R410a / 23.6 oz.	R410a / 23.6 oz.	R410a / 35.27 oz.	R410a / 35.27 oz.	R410a / 35.27 oz.
Product Weight	104 Lbs.	104 Lbs.	113 Lbs.	113 Lbs.	116 Lbs.	117 Lbs.	119 Lbs.
Shipping Weight (Approx.)	128 Lbs.	128 Lbs.	137 Lbs.	137 Lbs.	140 Lbs.	141 Lbs.	143 Lbs.
Product Dimensions (Overall Unit including Front Cover) – A – Height x B – Width x C – Depth	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"	16" x 42" x 21-13/16"
Inside Sleeve Depth	13-13/16"	13-13/16"	13-13/16"	13-13/16"	13-13/16"	13-13/16"	13-13/16"
<b>Wall Cutout Dimensions –</b>							
Height x Width	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"	16-5/16" x 42-3/16"

### The Industry's Longest Standard Warranty

- **Five Years**  
Parts and Labor Coverage on the Sealed Refrigeration System
- **Five Years**  
Limited Parts Coverage on Functional Parts
- **Two Years**  
Labor Coverage on Functional Parts

### Wall Sleeve & Outdoor Grille Installation

For wall sleeves and grille accessories refer to PTAC Installation Accessories pages.



Note: For planning purposes only. Always consult local and national electric codes. Refer to Product Installation Guide on the web at [frigidaire.com](http://frigidaire.com) for detailed instructions. Accessories information available on the web at [frigidaire.com](http://frigidaire.com)

Specifications subject to change. Commercial Grade Warranty - 2 year full parts and labor / 5 year sealed system. Contact Commercial Call Center for Warranty and Service Concerns at 1-866-942-1567.



# PTAC SPECIFICATIONS

## Air Conditioner/Heat Pumps with Backup Electric Heat

All models come with Corrosion Guard.

### PERFORMANCE (230/208V)

BTU (Cool)	7,200/7,000
BTU (Electric Heat)	8,300/6,800
BTU (Heat Pump)	6,000/5,800
Dehumidification (Pints per Hour)	1.7
Cool Area (Approx. Sq.Ft.)	300
Energy Efficiency Ratio	13.0
Air Volume CFM (High/Low)	312/282
Dry Mode	Yes
Noise Level dB (High/Low)	50/48

### ELECTRICAL

Volts / Hertz	230/208V / 60Hz
Amps (Cool)	2.7/2.9
Amps (Backup Electric Heat)	10.7/9.7
Amps (Heat Pump)	2.4/2.6
Watts (Cool)	550/535
Watts (Backup Electric Heat)	2,450/2,000
Watts (Heat Pump)	485/470
Cable Included	Yes
Length of Power Cord	5.5'
Circuit Breaker	15A
Plug Type (NEMA)	LCDI 6-15P

### SPECIFICATIONS

Refrigerant / Charge	R410a / 33.9 oz.
Product Weight	108 Lbs.
Shipping Weight (Approx.)	132 Lbs.
Product Dimensions (Overall Unit including Front Cover) – A - Height x B - Width x C - Depth	16"x42"x21-13/16"
Inside Sleeve Depth	13-13/16"
Wall Cutout Dimensions – Height x Width	16-5/16"x42-3/16"

### FFRP072HT2

7,200/7,000
8,300/6,800
6,000/5,800
1.7
300
13.0
312/282
Yes
50/48

### FFRP072HT3

7,200/7,000
11,700/9,600
6,000/5,800
1.7
300
13.0
312/282
Yes
50/48

### FFRP092HT2

9,400/9,200
8,300/6,800
8,300/8,100
2.1
450
12.1
330/294
Yes
52/50

### FFRP092HT3

9,400/9,200
11,700/9,600
8,300/8,100
2.1
450
12.1
330/294
Yes
52/50

### FFRP122HT3

11,800/11,600
11,700/9,600
10,600/10,400
2.7
620
11.6
341/306
Yes
53/50

### FFRP152HT3

14,500/14,200
11,700/9,600
13,300/13,000
3.5
830
10.4
341/306
Yes
54/51

### FFRP152HT4

14,500/14,200
17,000/13,900
13,300/13,000
3.5
830
10.4
341/306
Yes
54/51

### PERFORMANCE (265V)

BTU (Cool)	7,200
BTU (Electric Heat)	8,300
BTU (Heat Pump)	6,000
Dehumidification (Pints per Hour)	1.7
Cool Area (Approx. Sq.Ft.)	300
Energy Efficiency Ratio	13.0
Air Volume CFM (High/Low)	312/282
Dry Mode	Yes
Noise Level dB (High/Low)	50/48

### ELECTRICAL

Volts / Hertz	265V / 60Hz
Amps (Cool)	2.4
Amps (Backup Electric Heat)	9.3
Amps (Heat Pump)	2.2
Watts (Cool)	550
Watts (Backup Electric Heat)	2,450
Watts (Heat Pump)	485
Cable Included	Yes
Length of Power Cord	2.3'
Circuit Breaker	15A
Plug Type (NEMA)	LCDI 7-15P

### SPECIFICATIONS

Refrigerant / Charge	R410a / 33.9 oz.
Product Weight	108 Lbs.
Shipping Weight (Approx.)	132 Lbs.
Product Dimensions (Overall Unit including Front Cover) – A - Height x B - Width x C - Depth	16"x42"x21-13/16"
Inside Sleeve Depth	13-13/16"
Wall Cutout Dimensions – Height x Width	16-5/16"x42-3/16"

### FFRP072HT5

7,200
8,300
6,000
1.7
300
13.0
312/282
Yes
50/48

### FFRP072HT6

7,200
11,700
6,000
1.7
300
13.0
312/282
Yes
50/48

### FFRP092HT5

9,400
8,300
8,300
2.1
450
12.1
330/294
Yes
52/50

### FFRP092HT6

9,400
11,700
8,300
2.1
450
12.1
330/294
Yes
52/50

### FFRP122HT6



11,800
11,700
10,600
2.7
620
11.6
341/306
Yes
53/50

### FFRP152HT6

14,500
11,700
13,300
3.5
830
10.4
341/306
Yes
54/51

### FFRP152HT7

14,500
17,000
13,300
3.5
830
10.4
341/306
Yes
54/51



Specifications subject to change.  
Commercial Grade Warranty - 2 year full parts and labor / 5 year sealed system.  
Contact Commercial Call Center for Warranty and Service Concerns at 1-866-942-1567.

Note: For planning purposes only. Always consult local and national electric codes. Refer to Product Installation Guide on the web at [frigidaire.com](http://frigidaire.com) for detailed instructions. Accessories information available on the web at [frigidaire.com](http://frigidaire.com)



# PTAC INSTALLATION ACCESSORIES



Metal Wall Sleeve




Polymer Wall Sleeve




Condensation Universal Drain Kit



Stamped Aluminum Grille



Architectural Aluminum Grille



Polymer Architectural Grille

## Wall Sleeves and Drain Kit

### Metal Wall Sleeve & Accessories

- 5304482701 Steel Sleeve – Insulated
- 5304483759 16" Extended Sleeve – Insulated
- 5308815304 18" Extended Sleeve – Insulated
- 5308815305 24" Extended Sleeve – Insulated
- 5304483760 3" Sleeve Adapter

These fully insulated sleeves are made of electro-galvanized steel that resists corrosion, and welded areas are sealed with a rust preventive. White powder coating matches PTAC units. Sliding keyhole grille attachments enable easy, one-person installation from the inside.

### Polymer Wall Sleeve

- 5308815302 Insulated

Utilizes fiberglass-reinforced polyester compound to produce a durable, noncorrosive wall case that provides superior sound absorption, reduces heat loss and prevents sleeve sweating. (Requires use of a Polymer Architectural Grille.)

### Condensation Universal Drain Kit

- 5304480570 1-Pack

Controls condensate from the PTAC unit and can be used for exterior or interior drain systems. Includes 1/2" O.D. copper drain tubes with a short right angle tube and a 6" straight tube to suit the application. (Recommended for all new sleeve installations.)

## Outdoor Grilles

### Stamped Aluminum Outdoor Grille

- 5304480557 Clear Anodized Aluminum Finish

Cost-effective, one-piece stamped grille is made from durable anodized aluminum. The grille is lightweight, has a clear finish and is easy to install from inside the room.

### Architectural Aluminum Outdoor Grilles

- 5304480558 Clear Anodized Aluminum Finish
- 5308815313 Dark Brown
- 530448055X Customized Color


Enhances the appearance of any building. Made of a durable, anodized aluminum that offers weather resistance. Sliding keyhole attachment enables easy installation onto Frigidaire® metal wall sleeve.

### Polymer Architectural Outdoor Grilles

- 5308815310 Brown
- 5308815312 Alpine Beige

Blends with most building exteriors. Its durable design offers protection, has an enhanced appearance and provides superior weather resistance. (Requires use of a Polymer Wall Sleeve.)

# PTAC INSTALLATION ACCESSORIES



Decorative Subbase

Electrical Subbase

Leveling Legs



Air Filters



FFTSTATWL

Wall Thermostats



5304483050



Lateral Duct Kit

## Subbases and Leveling Legs

### Decorative Subbase

5308815315 Black

Made of heavy-gauge steel to provide support for the wall sleeve, the subbase mounts directly to the wall sleeve and has adjustable leveling legs.

### Black Electrical Subbases

5304482886 230V/15A

5304482891 265V/30A

5304482888 230V/30A

5304482890 265V/20A

5304482887 230V/20A

5304482698

265V Subbase Disconnect Switch

5304490211

Hardwire Kit, Conduit and Plate  
(For 230V and 265V)

Offers the same features as the decorative subbase, plus a factory-installed electrical junction box containing a receptacle for corded PTAC units.

### Leveling Legs

5304480575

Attach easily to the wall sleeve and offer accurate leveling and support for units without a subbase. Adjustable from 3-1/4" to 5-1/2".

## Air Filters

### Air Filters

5304482892 10-Pack

Changing filters periodically ensures a healthy room environment, proper airflow, temperature control and energy efficiency.

## Wall Thermostats

### Wireless Digital Wall Thermostat

FFTSTATWL Non-Programmable (Includes Wireless Receiver)

Allows control without having to worry about wiring. Easy to install and use. Large intuitive LCD screen improves user interaction.

### Wired Digital Wall Thermostats

5304482700

Programmable

5304483050

Non-Programmable

Offers auto-changeover, 2-stage heating and cooling, as well as emergency heating mode for heat pump.

### Laminated Insert

FPTAC0511

Informs guests that unit is controlled by wall thermostat.

## Miscellaneous

### Lateral Duct Kit

5304490206

Allows one PTAC unit to heat or cool two rooms. Kit mounts to wall sleeve and can be installed for either right- or left-side duct applications.

### Baffle Kit

5304484585

Baffle Kit for use on non-standard grilles.



## PTAC

### 2017 Air Conditioner Collection

**FRIGIDAIRE**

**USA**

10200 David Taylor Drive • Charlotte, NC 28262  
1-800-FRIGIDAIRE • [frigidaire.com](http://frigidaire.com)

**CANADA**

5855 Terry Fox Way • Mississauga, ON L5V 3E4  
1-800-265-8352 • [frigidaire.ca](http://frigidaire.ca)