



SAFETY DATA SHEET

Revision Date 26-Feb-2015

Version 1

1. IDENTIFICATION

Product identifier

Product Name VERSACHEM PRIME LOK STUD & BEARING FORMULA TYPE 275 RED 6 ML.

Other means of identification

Product Code 27569

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Adhesive

Uses advised against No information available

Details of the supplier of the safety data sheet

Manufacturer Address

ITW Permatex
10 Columbus Blvd.
Hartford, CT 06106 USA

Distributor

ITW Permatex Canada
35 Brownridge Road, Unit 1
Halton Hills, ON Canada L7G 0C6
Telephone: (800) 924-6994

Company Phone Number 1-87-Permatex
(877) 376-2839

24 Hour Emergency Phone Number Chem-Tel: 800-255-3924
International Emergency:
00+1+ 813-248-0585
Contract Number: MIS0003453

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Category 4
Acute toxicity - Dermal	Category 4
Acute toxicity - Inhalation (Dusts/Mists)	Category 4
Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2A
Specific target organ toxicity (repeated exposure)	Category 2

Label elements

Emergency Overview

Warning

Harmful if swallowed
Harmful in contact with skin
Harmful if inhaled
Causes skin irritation
Causes serious eye irritation
May cause damage to organs through prolonged or repeated exposure
Combustible liquid



Appearance Red

Physical state Liquid

Odor Mild

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
Do not eat, drink or smoke when using this product
Wear protective gloves/protective clothing/eye protection/face protection
Use only outdoors or in a well-ventilated area
Do not breathe dust/fume/gas/mist/vapors/spray
Keep away from heat/sparks/open flames/hot surfaces. — No smoking
Keep cool

Precautionary Statements - Response

Get medical advice/attention if you feel unwell
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention
IF ON SKIN: Wash with plenty of soap and water
Call a POISON CENTER or doctor/physician if you feel unwell
If skin irritation occurs: Get medical advice/attention
Take off contaminated clothing and wash before reuse
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
Call a POISON CENTER or doctor/physician
IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell
Rinse mouth
In case of fire: Use CO2, dry chemical, or foam for extinction

Precautionary Statements - Storage

Store in a well-ventilated place. Keep container tightly closed

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other Information

Not applicable.

Unknown acute toxicity

96.491% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance

Chemical Name	CAS No	Weight-%	Trade Secret
POLYGLYCOL DIMETHACRYLATE	25852-47-5	60 - 100	*
DIMETHYLBENZYL HYDROPEROXIDE	80-15-9	1 - 5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

Description of first aid measures

General advice	Get medical advice/attention if you feel unwell.
Eye contact	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Skin contact	IF ON SKIN: Wash skin with soap and water. If skin irritation persists, call a physician. Wash contaminated clothing before reuse.
Inhalation	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. If symptoms persist, call a physician.
Ingestion	IF SWALLOWED. Do NOT induce vomiting. Never give anything by mouth to an unconscious person.
Self-protection of the first aider	Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

Most important symptoms and effects, both acute and delayed

Symptoms See section 2 for more information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Carbon dioxide (CO₂), Dry chemical, Foam

Unsuitable extinguishing media

None.

Specific hazards arising from the chemical

None in particular.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas. Avoid contact with eyes and skin. Use personal protective equipment as required.

Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Ensure adequate ventilation. Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Avoid breathing vapors or mists. Avoid contact with skin, eyes or clothing. Wash thoroughly after handling. Wash contaminated clothing before reuse.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials Strong oxidizing agents, Peroxides, Reducing agent

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Appropriate engineering controls

Engineering Controls Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing.

Respiratory protection Use NIOSH-approved air-purifying respirator with organic vapor cartridge or canister, as appropriate.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Red
Odor Mild
Odor threshold No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	Does not apply	
Melting point / freezing point	No information available	

Boiling point / boiling range	> 149 °C / 300 °F	
Flash point	> 93 °C / > 199 °F	
Evaporation rate	< 1	Butyl acetate = 1
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Relative density	1.05-1.15	
Water solubility	Insoluble	
Solubility in other solvents	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Kinematic viscosity	No information available	
Dynamic viscosity	No information available	
Explosive properties	No information available	
Oxidizing properties	No information available	

Other Information

Softening point	No information available
Molecular weight	No information available
VOC Content (%)	<2%
Density	No information available
Bulk density	No information available

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Excessive heat.

Incompatible materials

Strong oxidizing agents, Peroxides, Reducing agent

Hazardous Decomposition Products

Carbon oxides

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Inhalation	May be harmful if inhaled.
Eye contact	Contact with eyes may cause irritation. May cause redness and tearing of the eyes.
Skin contact	May cause skin irritation and/or dermatitis.
Ingestion	Ingestion may cause irritation to mucous membranes.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
---------------	-----------	-------------	-----------------

DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	= 382 mg/kg (Rat)	= 0.126 mL/kg (Rabbit)	= 220 ppm (Rat) 4 h
--	---------------------	--------------------------	-----------------------

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Germ cell mutagenicity No information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

IARC (International Agency for Research on Cancer)

Not classifiable as a human carcinogen

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral) 536 mg/kg
 ATEmix (dermal) 1544 mg/kg
 ATEmix (inhalation-dust/mist) 0.7 mg/l

12. ECOLOGICAL INFORMATION

Ecotoxicity

None known

95.5% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	-	3.9: 96 h Oncorhynchus mykiss mg/L LC50 static	7: 24 h Daphnia magna mg/L EC50

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Mobility

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

US EPA Waste Number Not applicable

Chemical Name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	-	-	-	U096

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	Toxic Ignitable

14. TRANSPORT INFORMATION

DOT
 Proper shipping name: Not regulated

IATA
 Proper shipping name: Not regulated

IMDG
 Proper shipping name: Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies
EINECS/ELINCS	Does not comply
ENCS	Complies
IECSC	Complies
KECL	Complies
PICCS	Complies
AICS	Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
 EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
 ENCS - Japan Existing and New Chemical Substances
 IECSC - China Inventory of Existing Chemical Substances
 KECL - Korean Existing and Evaluated Chemical Substances
 PICCS - Philippines Inventory of Chemicals and Chemical Substances
 AICS - Australian Inventory of Chemical Substances

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
DIMETHYLBENZYL HYDROPEROXIDE - 80-15-9	1.0
SACCHARIN - 81-07-2	1.0

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	10 lb	-	RQ 10 lb final RQ RQ 4.54 kg final RQ

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	X	X	X
SACCHARIN 81-07-2	X	X	X
1,4-NAPHTHOQUINONE 130-15-4	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

NFPA	Health hazards 2	Flammability 1	Instability 0	-
HMIS	Health hazards 2	Flammability 1	Physical hazards 0	Personal protection B

NFPA (National Fire Protection Association)
 HMIS (Hazardous Material Information System)

Revision Date 26-Feb-2015

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet