

Safety Data Sheet



1. Identification

Product Name: FLOOR 1-GL 2PK ANTS L P CLEAN & ETCH SOLN **Revision Date:** 4/23/2015

Product Identifier: 108402 **Supercedes Date:** 9/15/2014

Product Use/Class: Cleaner

Supplier: Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, IL 60061
USA **Manufacturer:** Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, IL 60061
USA

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

EMERGENCY OVERVIEW: Causes severe skin and eye burns. Do not taste or swallow. Harmful if swallowed. Causes Serious Eye Irritation. Causes skin irritation. May cause eye, skin, or respiratory tract irritation. KEEP OUT OF REACH OF CHILDREN. Harmful if inhaled. Causes eye irritation. Use ventilation necessary to keep exposures below recommended exposure limits, if any.

Classification

Symbol(s) of Product



Signal Word

Danger

GHS HAZARD STATEMENTS

Acute Toxicity, Dermal, category 5	H313	May be harmful in contact with skin.
Skin Irritation, category 2	H315	Causes skin irritation.
Aspiration Hazard, category 2	H305	May be harmful if swallowed and enters airways.
Skin Irritation, category 3	H316	Causes mild skin irritation.
Eye Irritation, category 2B	H320	Causes eye irritation.
Acute Toxicity, Inhalation, category 4	H332	Harmful if inhaled.
Skin Corrosion, category 1	H314	Causes severe skin burns and eye damage.

GHS PRECAUTIONARY STATEMENTS

P102	Keep out of reach of children.
P103	Read label before use.
P202	Do not handle until all safety precautions have been read and understood.
P234	Keep only in original container.
P260	Do not breathe dust/fume/gas/mist/vapours/spray.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P262	Do not get in eyes, on skin, or on clothing.
P264	Wash ... thoroughly after handling.

P270	Do not eat, drink or smoke when using this product.
P271	Use only outdoors or in a well-ventilated area.
P273	Avoid release to the environment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P281	Use personal protective equipment as required.
P285	In case of inadequate ventilation wear respiratory protection.
P312	Call a POISON CENTER or doctor/physician if you feel unwell.
P335	Brush off loose particles from skin.
P351	Rinse cautiously with water for several minutes.
P374	Fight fire with normal precautions from a reasonable distance.
P402	Store in a dry place.
P321	Specific treatment (see ... on this label).
P352	Wash with plenty of soap and water.
P362	Take off contaminated clothing and wash before reuse.
P332+P313	If skin irritation occurs: Get medical advice/attention.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P304+P340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P310	Immediately call a POISON CENTER or doctor/physician.
P363	Wash contaminated clothing before reuse.
P301+P330+P331	IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P303+P361+P353	IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P405	Store locked up.
P501	Dispose of contents/container to ...
P302+P350	IF ON SKIN: Gently wash with plenty of soap and water.

3. Composition/Information On Ingredients

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Phosphoric Acid	7664-38-2	25-50	GHS05-GHS07	H290-302-314-332

The text for GHS Hazard Statements shown above (if any) is given in the "16. Other Information" section.

4. First-aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Remove contaminated clothing. Wash skin with soap and water. Get medical attention. Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: If affected by inhalation of dust, vapor or spray mist, remove to fresh air. If breathing difficulty persists, get medical attention immediately. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately. Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation.

FIRST AID - INGESTION: Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but give one or two glasses of water to drink and get medical attention. If swallowed, rinse mouth with water. If feeling unwell, get medical attention.

5. Fire-fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: No unusual fire or explosion hazards noted. FLASH POINT IS TESTED TO BE GREATER THAN 200 DEGREES F. Keep containers tightly closed.

SPECIAL FIREFIGHTING PROCEDURES: Use water spray to keep fire-exposed containers cool. Containers may explode when heated. Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred.

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Neutralize liquid acid spills with sodium bicarbonate (NaHCO₃). If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Follow all MSDS/label precautions even after container is emptied because it may retain product residues. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Keep away from heat, sparks, flame and sources of ignition. Keep from freezing. Store in a dry, well ventilated place. Keep container tightly closed when not in use.

8. Exposure Controls/Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Phosphoric Acid	7664-38-2	30.0	1 mg/m ³	3 mg/m ³	1 mg/m ³	N.E.

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

SKIN PROTECTION: Where contact is likely, wear chemical resistant gloves, a chemical suit, rubber boots and chemical safety goggles plus a face shield. Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application. Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

9. Physical and Chemical Properties

Appearance:	Liquid	Physical State:	Liquid
Odor:	Solvent Like	Odor Threshold:	N.E.
Relative Density:	1.139	pH:	N.A.
Freeze Point, °C:	N.D.	Viscosity:	No Information
Solubility in Water:	Miscible	Partition Coefficient, n-octanol/ water:	No Information
Decomposition Temp., °C:	No Information	Explosive Limits, vol%:	N.A. - N.A.
Boiling Range, °C:	212 - 392	Flash Point, °C:	>93
Flammability:	Supports Combustion	Auto-ignition Temp., °C:	No Information
Evaporation Rate:	Slower than Ether	Vapor Pressure:	No Information
Vapor Density:	Heavier than Air		

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

CONDITIONS TO AVOID: Avoid contact with strong reducing or oxidizing agents. Avoid contact with strong acid and strong bases.

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalis. Avoid contact with strong oxidizing and reducing agents.

HAZARDOUS DECOMPOSITION: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Irritating, and may injure eye tissue if not removed promptly. Causes Serious Eye Irritation

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Substance is corrosive. Causes severe skin burns. Corrosive; causes skin burning. Low hazard for usual industrial handling or commercial handling by trained personnel.

EFFECTS OF OVEREXPOSURE - INHALATION: Avoid breathing fumes, spray, vapors, or mist. High gas, vapor, mist or dust concentrations may be harmful if inhaled.

EFFECTS OF OVEREXPOSURE - INGESTION: Substance may be harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: Effects of overexposure may include irritation of the nose and throat, irritation of the digestive tract and signs of nervous system depression (e.g., headache, drowsiness, loss of coordination and fatigue).

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
7664-38-2	Phosphoric Acid	1530 mg/kg Rat	2730 mg/kg Rabbit	N.I.

N.I. - No Information

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components. Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
UN Number:	N.A.	3066	3066	N.A.
Proper Shipping Name:	Paint Products in Limited Quantities	Paint and Paint Related Products	Paint and Paint Related Products	Paint Products in Limited Quantities
Hazard Class:	N.A.	8	8	N.A.
Packing Group:	N.A.	III	III	N.A.
Limited Quantity:	No	Yes	No	No

15. Regulatory Information

U.S. Federal Regulations:**CERCLA - SARA Hazard Category**

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Health Hazard, Chronic Health Hazard

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>
Phosphoric Acid	7664-38-2

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

CALIFORNIA PROPOSITION 65:

No Proposition 65 Carcinogens exist in this product.

CALIFORNIA PROPOSITION 65 REPRODUCTIVE TOXINS

No Proposition 65 Reproductive Toxins exist in this product.

International Regulations:**CANADIAN WHMIS:**

This SDS has been prepared in compliance with Controlled Product Regulations except for the use of the 16 headings.

16. Other Information**HMIS RATINGS**

Health: 2* Flammability: 1 Physical Hazard: 0 Personal Protection: X

CANADIAN WHMIS CLASS: D2A

NFPA RATINGS

Health: 2 Flammability: 1 Instability: 0

VOLATILE ORGANIC COMPOUNDS, g/L: 0

MSDS REVISION DATE: 4/23/2015

REASON FOR REVISION: No Information

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

Text for GHS Hazard Statements shown in Section 3 describing each ingredient:

H290	May be corrosive to metals.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H332	Harmful if inhaled.

Icons for GHS Pictograms shown in Section 3 describing each ingredient:

GHS05



GHS07



Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.