



# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

Date of issue: 11/15/2013

Revision date: 07/17/2014

Version: 1.0

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Product name: : Sakrete Premium Driveway Sealer  
Sakrete Premium Filled Driveway Sealer

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture : Various

#### 1.3. Details of the supplier of the safety data sheet

Sakrete of North America  
8201 Arrowridge Blvd.  
28273 Charlotte, NC - USA  
T 866-725-7383

#### 1.4. Emergency telephone number

Emergency number : CHEMTREC (800) 424-9300  
CHEMTREC International +1 (703) 527-3887 24 hr

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### GHS-US classification

Skin Sensitization 1  
Germ Cell Mutagenicity 1B  
Carcinogenicity 1A  
Reproductive Toxicity 1B  
Specific target organ toxicity - Repeated exposure, Category 1

#### 2.2. Label elements

##### GHS-US labelling

Hazard pictograms (GHS-US) :



GHS07

GHS08

Signal word (GHS-US) :

Danger

Hazard statements (GHS-US) :

May cause an allergic skin reaction. May cause genetic defects. May cause cancer. May damage fertility or the unborn child. Causes damage to lungs through prolonged or repeated exposure.

Precautionary statements (GHS-US) :

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe dust/fume/gas/mist/vapours/spray. Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves/protective clothing/eye protection/face protection. If on skin: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention. Wash contaminated clothing before reuse. If exposed or concerned: Get medical advice/attention. Store locked up. Dispose of contents/container in accordance with all local, regional, national and international regulations.

#### 2.3. Other hazards

No additional information available.

#### 2.4. Unknown acute toxicity (GHS-US)

Sakrete Premium Driveway Sealer: 23 % of the mixture consists of ingredient(s) of unknown acute toxicity.

Sakrete Premium Filled Driveway Sealer 20 % of the mixture consists of ingredient(s) of unknown acute toxicity.

### SECTION 3: Composition/information on ingredients

#### 3.1. Substance

Not applicable

#### 3.2. Mixture

# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

Name	Product identifier	%	GHS-US classification
Pitch, coal tar, high-temperature	(CAS No) 65996-93-2	10 - 30	Carc. 1A, H350
Quartz	(CAS No) 14808-60-7	4 - 18	Acute Tox. 4 (Oral), H302 Carc. 1A, H350 STOT RE 1, H372
Aluminum silicate	(CAS No) 1327-36-2	1 - 5	Skin Irrit. 2, H315 Eye Irrit. 2A, H319
Feldspar	(CAS No) 68476-25-5	1 - 5	Eye Irrit. 2A, H319 STOT SE 3, H335
Titanium dioxide	(CAS No) 13463-67-7	0.1 - 1	Acute Tox. 4 (Inhalation), H332 Carc. 2, H351
Naphthalene	(CAS No) 91-20-3	0.1 - 1	Acute Tox. 4 (Oral), H302 Carc. 2, H351
Benz[a]anthracene	(CAS No) 56-55-3	0.1 - 1	Carc. 2, H351
Indeno(1,2,3-cd)pyrene	(CAS No) 193-39-5	0.1 - 1	Carc. 2, H351
Chrysene	(CAS No) 218-01-9	0.1 - 1	Muta. 2, H341 Carc. 2, H351
Benzo(b)fluoranthene	(CAS No) 205-99-2	0.1 - 1	Carc. 2, H351
Benzo(a)pyrene	(CAS No) 50-32-8	0.1 - 1	Skin Sens. 1, H317 Muta. 1B, H340 Carc. 1A, H350 Repr. 1B, H360
9H-Carbazole	(CAS No) 86-74-8	0.1 - 1	Muta. 2, H341 Carc. 2, H351
Benzo(j)fluoranthene	(CAS No) 205-82-3	0.1 - 1	Carc. 2, H351
Dibenzo(a,h)pyrene	(CAS No) 189-64-0	0.1 - 1	Muta. 2, H341 Carc. 1B, H350
Benzo(k)fluoranthene	(CAS No) 207-08-9	0.1 - 1	Carc. 2, H351

The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

- First-aid measures after inhalation : If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.
- First-aid measures after skin contact : In case of contact, immediately flush skin with plenty of water. Call a physician if irritation develops and persists.
- First-aid measures after eye contact : In case of contact, immediately flush eyes with plenty of water. Remove contact lenses, if worn. If irritation persists, get medical attention.
- First-aid measures after ingestion : If swallowed, do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical advice/attention if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/injuries after inhalation : May cause respiratory irritation.
- Symptoms/injuries after skin contact : May cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin.
- Symptoms/injuries after eye contact : May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with marked redness and swelling of the conjunctiva.
- Symptoms/injuries after ingestion : May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

### 4.3. Indication of any immediate medical attention and special treatment needed

Symptoms may not appear immediately. In case of accident or if you feel unwell, seek medical advice immediately (show the label or SDS where possible).

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

- Suitable extinguishing media : Treat for surrounding material.
- Unsuitable extinguishing media : None known.

### 5.2. Special hazards arising from the substance or mixture

- Fire hazard : Products of combustion may include, and are not limited to: oxides of carbon.

### 5.3. Advice for firefighters

- Protection during firefighting : Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

##### 6.1.1. For non-emergency personnel

Protective equipment : Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

##### 6.1.2. For emergency responders

No additional information available.

#### 6.2. Methods and material for containment and cleaning up

For containment : Contain and/or absorb spill with inert material (e.g. sand, vermiculite), then place in a suitable container. Do not flush to sewer or allow to enter waterways. Use appropriate Personal Protective Equipment (PPE).

Methods for cleaning up : Scoop up material and place in a disposal container.

#### 6.3. Reference to other sections

See section 8 for further information on protective clothing and equipment and section 13 for advice on waste disposal.

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Precautions for safe handling : Avoid contact with skin and eyes. Do not swallow. Handle and open container with care. When using do not eat, drink or smoke. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Use personal protective equipment as required. Do not breathe dust/fume/gas/mist/vapours/spray. Wash hands before eating, drinking, or smoking.

Hygiene measures : Launder contaminated clothing before reuse. Wash hands before eating, drinking, or smoking.

#### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep out of the reach of children. Keep container tightly closed. Keep container tightly closed, dry and in a well-ventilated place.

#### 7.3. Specific end use(s)

Not available.

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

<b>Pitch, coal tar, high-temperature (65996-93-2)</b>		
USA ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	0.2 mg/m <sup>3</sup>
USA OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	0.2 mg/m <sup>3</sup> (benzene soluble fraction)
<b>Quartz (14808-60-7)</b>		
USA ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	0.025 mg/m <sup>3</sup>
USA OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	(30)/(%SiO <sub>2</sub> + 2) mg/m <sup>3</sup> TWA, total dust (250)/(%SiO <sub>2</sub> + 5) mppcf TWA, respirable fraction (10)/(%SiO <sub>2</sub> + 2) mg/m <sup>3</sup> TWA, respirable fraction
<b>Naphthalene (91-20-3)</b>		
USA ACGIH	ACGIH TWA (ppm)	10 ppm
USA ACGIH	ACGIH STEL (ppm)	15 ppm
USA OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	50 mg/m <sup>3</sup>
USA OSHA	OSHA PEL (TWA) (ppm)	10 ppm
<b>Titanium dioxide (13463-67-7)</b>		
USA ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	10 mg/m <sup>3</sup>
USA OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup>
<b>Chrysene (218-01-9)</b>		
USA OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	0.2 mg/m <sup>3</sup>
<b>Benzo(a)pyrene (50-32-8)</b>		
sUSA OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	0.2 mg/m <sup>3</sup>

# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

### 8.2. Exposure controls

Appropriate engineering controls	:	Use ventilation adequate to keep exposures (airborne levels of dust, fume, vapor, etc.) below recommended exposure limits.
Hand protection	:	Wear suitable gloves.
Eye protection	:	Safety glasses or goggles are recommended when using product.
Skin and body protection	:	Wear suitable protective clothing.
Respiratory protection	:	In case of insufficient ventilation, wear suitable respiratory equipment. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
Environmental exposure controls	:	Maintain levels below Community environmental protection thresholds.
Other information	:	Do not eat, smoke or drink where material is handled, processed or stored. Wash hands carefully before eating or smoking. Handle according to established industrial hygiene and safety practices.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	:	Liquid.
Appearance	:	Viscous.
Colour	:	No data available.
Odour	:	No data available.
Odour threshold	:	No data available.
pH	:	No data available.
Relative evaporation rate (butylacetate=1)	:	No data available.
Melting point	:	No data available.
Freezing point	:	No data available.
Boiling point	:	No data available.
Flash point	:	No data available.
Self ignition temperature	:	No data available.
Decomposition temperature	:	No data available.
Flammability (solid, gas)	:	Not flammable.
Vapour pressure	:	No data available.
Relative vapour density at 20 °C	:	No data available.
Relative density	:	No data available.
Solubility	:	No data available.
Log Pow	:	No data available.
Log Kow	:	No data available.
Viscosity, kinematic	:	No data available.
Viscosity, dynamic	:	No data available.
Explosive properties	:	No data available.
Oxidising properties	:	No data available.
Explosive limits	:	No data available.

### 9.2. Other information

No additional information available.

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No dangerous reaction known under conditions of normal use.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reaction known under conditions of normal use.

### 10.4. Conditions to avoid

Incompatible materials.

### 10.5. Incompatible materials

None known.

# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

### 10.6. Hazardous decomposition products

May include, and are not limited to: oxides of carbon.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity : Not classified

Quartz (14808-60-7)	
LD50 oral rat	500 mg/kg

Naphthalene (91-20-3)	
LD50 dermal rabbit	> 20 g/kg
LC50 inhalation rat (mg/l)	> 340 mg/m <sup>3</sup> 1h

Titanium dioxide (13463-67-7)	
LD50 oral rat	> 10000 mg/kg

9H-Carbazole (86-74-8)	
LD50 oral rat	> 5000 mg/kg

Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer	
ATE (oral)	>2000 mg/kg, rabbit
ATE (dermal)	>2000 mg/kg, rabbit
ATE (inhalation)	No data available.

Skin corrosion/irritation : Based on available data, the classification criteria are not met.  
Serious eye damage/irritation : Based on available data, the classification criteria are not met.  
Respiratory or skin sensitisation : May cause an allergic skin reaction.  
Germ cell mutagenicity : May cause genetic defects.  
Carcinogenicity : May cause cancer.

Pitch, coal tar, high-temperature (65996-93-2)	
IARC group	1
National Toxicology Program (NTP) Status	2

Quartz (14808-60-7)	
IARC group	1
National Toxicology Program (NTP) Status	2

Naphthalene (91-20-3)	
IARC group	2B
National Toxicology Program (NTP) Status	1, 3

Titanium dioxide (13463-67-7)	
IARC group	2B

Benz[a]anthracene (56-55-3)	
IARC group	2B
National Toxicology Program (NTP) Status	3

Indeno(1,2,3-cd)pyrene (193-39-5)	
IARC group	2B
National Toxicology Program (NTP) Status	3

Chrysene (218-01-9)	
IARC group	2B

Benzo(b)fluoranthene (205-99-2)	
IARC group	2B
National Toxicology Program (NTP) Status	3

Benzo(a)pyrene (50-32-8)	
IARC group	1
National Toxicology Program (NTP) Status	3

9H-Carbazole (86-74-8)	
IARC group	2B

# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

<b>Dibenzo(a,h)pyrene (189-64-0)</b>	
IARC group	2B
National Toxicology Program (NTP) Status	3

<b>Benzo(j)fluoranthene (205-82-3)</b>	
IARC group	2B
National Toxicology Program (NTP) Status	3

<b>Benzo(k)fluoranthene (207-08-9)</b>	
IARC group	2B
National Toxicology Program (NTP) Status	3

Reproductive toxicity	: May damage fertility or the unborn child.
Specific target organ toxicity (single exposure)	: Based on available data, the classification criteria are not met.
Specific target organ toxicity (repeated exposure)	: Causes damage to lungs through prolonged or repeated exposure.
Aspiration hazard	: Based on available data, the classification criteria are not met.
Symptoms/injuries after skin contact	: May cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin.
Symptoms/injuries after eye contact	: May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with marked redness and swelling of the conjunctiva.
Symptoms/injuries after ingestion	: May be harmful if swallowed. May cause stomach distress, nausea or vomiting.
Symptoms/injuries after inhalation	: May cause respiratory irritation.

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general : May cause long-term adverse effects in the aquatic environment.

### 12.2. Persistence and degradability

<b>Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer</b>	
Persistence and degradability	Not established.

### 12.3. Bioaccumulative potential

<b>Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer</b>	
Bioaccumulative potential	Not established.

### 12.4. Mobility in soil

No additional information available.

### 12.5. Other adverse effects

No additional information available.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Waste disposal recommendations : This material must be disposed of in accordance with all local, state, provincial, and federal regulations.

## SECTION 14: Transport information

In accordance with DOT

### 14.1. UN number

Not applicable.

### 14.2. UN proper shipping name

Not applicable.

### 14.3. Additional information

Other information : No supplementary information available.

Special transport precautions : Do not handle until all safety precautions have been read and understood.

## SECTION 15: Regulatory information

### 15.1. US Federal regulations

<b>Pitch, coal tar, high-temperature (65996-93-2)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	

# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

<b>Quartz (14808-60-7)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
<b>Aluminum silicate (1327-36-2)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
<b>Feldspar (68476-25-5)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
<b>Naphthalene (91-20-3)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
Listed on SARA Section 313 (Specific toxic chemical listings)	
EPA TSCA Regulatory Flag	T - T - indicates a substance that is the subject of a Section 4 test rule under TSCA.
SARA Section 313 - Emission Reporting	0.1 %
<b>Titanium dioxide (13463-67-7)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
<b>Benz[a]anthracene (56-55-3)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	0.1 %
<b>Indeno(1,2,3-cd)pyrene (193-39-5)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	0.1 %
<b>Chrysene (218-01-9)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	1.0 %
<b>Benzo(b)fluoranthene (205-99-2)</b>	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	0.1 %
<b>Benzo(a)pyrene (50-32-8)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	0.1 %
<b>9H-Carbazole (86-74-8)</b>	
Listed on the United States TSCA (Toxic Substances Control Act) inventory	
<b>Dibenzo(a,h)pyrene (189-64-0)</b>	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	0.1 %
<b>Benzo(j)fluoranthene (205-82-3)</b>	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	0.1 %
<b>Benzo(k)fluoranthene (207-08-9)</b>	
Listed on SARA Section 313 (Specific toxic chemical listings)	
SARA Section 313 - Emission Reporting	0.1 %
<b>15.3. US State regulations</b>	
<b>Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer</b>	
State or local regulations	This product contains Crystalline Silica, Quartz and may also contain trace amounts of other chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.


# Sakrete Premium Driveway Sealer/Sakrete Premium Filled Driveway Sealer

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

### SECTION 16: Other information

Data sources	:	SDS prepared pursuant to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.
NFPA health hazard	:	2
NFPA fire hazard	:	1
NFPA reactivity	:	0



*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product*