HERCULES'

SAFETY DATA SHEET

1. Identification

Product identifier Hercules Climate Smooth

Other means of identification

SDS number 7390E

Synonyms Part Numbers: 10606, 10608, 10616, 10619, 10621

Recommended use Flux for joining copper tubing and pipe

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Company Name HCC Holdings, Inc. an Oatey Affiliate

Address 4700 West 160th Street

Cleveland, OH 44135

Telephone 216-267-7100 **E-mail** info@oatey.com

Transport Emergency Chemtrec 1-800-424-9300 (Outside the US 1-703-527-3887)

Emergency First Aid 1-877-740-5015
Contact person MSDS Coordinator

2. Hazard(s) identification

Physical hazards Not classified.

Health hazardsSkin corrosion/irritationCategory 1B

Serious eye damage/eye irritation Category 1

OSHA defined hazards Not classified.

Label elements



Signal word Danger

Hazard statement Causes severe skin burns and eye damage.

Precautionary statement

Prevention Do not breathe dust or mists. Wash thoroughly after handling. Wear protective gloves/protective

clothing/eye protection/face protection.

Response Wash contaminated clothing before reuse. If swallowed: Rinse mouth. Do NOT induce vomiting. If

on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. If inhaled: Remove person to fresh air and keep comfortable for breathing. Immediately call a poison center/doctor. If in eyes: Rinse cautiously with water for several minutes. Remove contact

lenses, if present and easy to do. Continue rinsing.

Storage Store locked up.

Disposal Dispose of contents/container in accordance with local/regional/national/international regulations.

Hazard(s) not otherwise classified (HNOC)

None known.

Supplemental information

Not applicable.

3. Composition/information on ingredients

Mixtures

Chemical name	CAS number	
Slack wax (petroleum)	64742-61-6	30-60

Hercules Climate Smooth SDS US

920704 Version #: 03 Revision date: 19-February-2015 Issue date: 05-August-2014

Petroleum distillates, solvent refined heavy parrafinic	64741-88-4	15-40
Zinc chloride	7646-85-7	10-30
Ammonium chloride	12125-02-9	1-5
Other components below reportable levels		5.92

^{*}Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.

Skin contactTake off immediately all contaminated clothing. Rinse skin with water/shower. Call a physician or

poison control center immediately. Chemical burns must be treated by a physician. Wash

contaminated clothing before reuse.

Eye contact Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if

present and easy to do. Continue rinsing. Call a physician or poison control center immediately.

Ingestion Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If

vomiting occurs, keep head low so that stomach content doesn't get into the lungs.

Most important symptoms/effects, acute and delayed Burning pain and severe corrosive skin damage. Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result.

Indication of immediate medical attention and special treatment needed

Provide general supportive measures and treat symptomatically. Chemical burns: Flush with water immediately. While flushing, remove clothes which do not adhere to affected area. Call an ambulance. Continue flushing during transport to hospital. Keep victim under observation. Symptoms may be delayed.

General information

Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media

Unsuitable extinguishing

media

Specific hazards arising from

the chemical

Special protective equipment and precautions for firefighters

Fire fighting

equipment/instructions

Specific methods

General fire hazards

Water spray. Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).

Do not use water jet as an extinguisher, as this will spread the fire.

During fire, gases hazardous to health may be formed.

Use water spray to cool unopened containers.

Use standard firefighting procedures and consider the hazards of other involved materials.

Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

This product is miscible in water. Stop the flow of material, if this is without risk. Dike far ahead of spill for later disposal. Use water spray to reduce vapors or divert vapor cloud drift. Prevent entry into waterways, sewer, basements or confined areas. Following product recovery, flush area with water. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Do not get this material in contact with eyes. Do not get this material in contact with skin. Avoid prolonged exposure. Do not get this material on clothing. Provide adequate ventilation. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.

Conditions for safe storage, including any incompatibilities

Store locked up. Store in original tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

Hercules Climate Smooth SDS US

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Туре	Value	Form
Petroleum distillates, solvent refined heavy parrafinic (CAS 64741-88-4)	PEL	5 mg/m3	Mist.
parrailino (e/te e ii ii ee i)		2000 mg/m3	
		500 ppm	
Zinc chloride (CAS 7646-85-7)	PEL	1 mg/m3	Fume.
US. ACGIH Threshold Limit	Values		
Components	Туре	Value	Form
Ammonium chloride (CAS	STEL	20 mg/m3	Fume.
12125-02-9)	T14/4	40 / 0	_
Detrologies distillatos	TWA	10 mg/m3	Fume.
Petroleum distillates, solvent refined heavy parrafinic (CAS 64741-88-4)	TWA	5 mg/m3	Inhalable fraction.
Zinc chloride (CAS	STEL	2 mg/m3	Fume.
7646-85-7)	TWA	1 mg/m3	Fume.
US. NIOSH: Pocket Guide to	Chemical Hazards		
Components	Туре	Value	Form
Ammonium chloride (CAS 12125-02-9)	STEL	20 mg/m3	Fume.
	TWA	10 mg/m3	Fume.
Petroleum distillates, solvent refined heavy parrafinic (CAS 64741-88-4)	STEL	10 mg/m3	Mist.
,	TWA	5 mg/m3	Mist.
Zinc chloride (CAS 7646-85-7)	STEL	2 mg/m3	Fume.
	TWA	1 mg/m3	Fume.
logical limit values	No biological exposure limits noted fo	r the ingredient(s).	
propriate engineering trols	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.		
="	such as personal protective equipme		
Eye/face protection	Wear safety glasses with side shields	(or goggles) and a face shield	
Skin protection			
Hand protection	Wear appropriate chemical resistant gloves.		
Other	Wear appropriate chemical resistant clothing.		
Respiratory protection	In case of insufficient ventilation, wear suitable respiratory equipment.		
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.		
neral hygiene siderations	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.		
Physical and chemical _l	properties		
nearance	Paste.		

9.

Appearance Paste. Solid. **Physical state Form** Solid. Color Amber to dark brown.

Odorless. Odor

SDS US Hercules Climate Smooth 920704 Version #: 03 Revision date: 19-February-2015 Issue date: 05-August-2014

Odor threshold Not available. Not available. pН

Melting point/freezing point 120 - 140 °F (48.89 - 60 °C)

Initial boiling point and boiling

range

Not available.

Not available. Flash point Not available. **Evaporation rate** Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower

Not available.

Flammability limit - upper (%)

Not available.

Explosive limit - lower (%) Not available. Explosive limit - upper (%) Not available. Vapor pressure Not available.

< 1 Vapor density 0.95 Relative density

Solubility(ies)

Solubility (water) slightly soluble Partition coefficient Not available.

(n-octanol/water)

Not available. **Auto-ignition temperature** Not available. **Decomposition temperature Viscosity** 20000 - 50000 cP

Other information

VOC (Weight %) 14 g/l

10. Stability and reactivity

The product is stable and non-reactive under normal conditions of use, storage and transport. Reactivity

Chemical stability Material is stable under normal conditions.

Possibility of hazardous

reactions

No dangerous reaction known under conditions of normal use.

Conditions to avoid Contact with incompatible materials.

Incompatible materials Strong oxidizing agents.

Hazardous decomposition

products

No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Prolonged inhalation may be harmful. May cause irritation to the respiratory system. Inhalation

Skin contact Causes severe skin burns. Causes serious eye damage. Eye contact Causes digestive tract burns. Ingestion

Symptoms related to the physical, chemical and toxicological characteristics Burning pain and severe corrosive skin damage. Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result.

Information on toxicological effects

Not available. Acute toxicity

Skin corrosion/irritation Causes severe skin burns and eye damage.

Causes serious eye damage. Serious eye damage/eye

irritation

Hercules Climate Smooth SDS US Respiratory or skin sensitization

Respiratory sensitization Not available.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicityNo data available to indicate product or any components present at greater than 0.1% are

mutagenic or genotoxic.

Carcinogenicity This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Reproductive toxicityThis product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity -

single exposure

Not classified.

Specific target organ toxicity -

repeated exposure

Not classified.

Aspiration hazard Not available.

Chronic effects Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the

possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential No data available.

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation

potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructionsCollect and reclaim or dispose in sealed containers at licensed waste disposal site. This material

and its container must be disposed of as hazardous waste. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international

regulations.

Local disposal regulations

Hazardous waste code

Dispose in accordance with all applicable regulations.

The waste code should be assigned in discussion between the user, the producer and the waste

disposal company.

Waste from residues / unused

products

Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see:

Disposal instructions).

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal.

Since emptied containers may retain product residue, follow label warnings even after container is

emptied.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

Transport in bulk according to Annex II of MARPOL 73/78 and

Not applicable.

the IBC Code

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication

Standard, 29 CFR 1910.1200.

All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

Hercules Climate Smooth SDS US

920704 Version #: 03 Revision date: 19-February-2015 Issue date: 05-August-2014

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

CERCLA Hazardous Substance List (40 CFR 302.4)

Ammonium chloride (CAS 12125-02-9) LISTED Zinc chloride (CAS 7646-85-7) LISTED

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - Yes

Delayed Hazard - No Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous

No

chemical

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.	
Zinc chloride	7646-85-7	10-30	_
Ammonium chloride	12125-02-9	1-5	

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act

Not regulated.

(SDWA)

US state regulations

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material

is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

US. Massachusetts RTK - Substance List

Ammonium chloride (CAS 12125-02-9)

Petroleum distillates, solvent refined heavy parrafinic (CAS 64741-88-4)

Zinc chloride (CAS 7646-85-7)

US. New Jersey Worker and Community Right-to-Know Act

Ammonium chloride (CAS 12125-02-9)

Zinc chloride (CAS 7646-85-7)

US. Pennsylvania Worker and Community Right-to-Know Law

Ammonium chloride (CAS 12125-02-9)

Zinc chloride (CAS 7646-85-7)

US. Rhode Island RTK

Ammonium chloride (CAS 12125-02-9)

Zinc chloride (CAS 7646-85-7)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes

Hercules Climate Smooth SDS US

Country(s) or region Inventory name On inventory (yes/no)*

Philippines Philippine Inventory of Chemicals and Chemical Substances

(PICCS)

United States & Puerto Rico Toxic Substances Control Act (TSCA) Inventory Yes

*A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 05-August-2014 19-February-2015 **Revision date**

Version # 03

HMIS® ratings Health: 3

Flammability: 0 Physical hazard: 0

Disclaimer The information in the sheet was written based on the best knowledge and experience currently

available.

Hercules Climate Smooth

920704 Version #: 03 Revision date: 19-February-2015 Issue date: 05-August-2014