



4700 W. 160th St.  
Cleveland, Ohio 44135  
Ph: (800) 321-9532  
Fax: (800) 321-9535  
www.oatey.com



## 72000 Series PVC Adjustable General Purpose Drain PVC Barrel With 5" Round Grate With Round Ring



### SUBMITTAL SPECIFICATION

**Engineering Specification:** Oatey adjustable general purpose floor drains are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Grate Finish	Part Number
	3 or 4 in. Pipe Fit	PVC	Brass	72037
	3 or 4 in. Pipe Fit	PVC	Nickel	72067
	3 or 4 in. Pipe Fit	PVC	Chrome	72097
	4 in. Pipe Fit	PVC	Brass	72038
	4 in. Pipe Fit	PVC	Nickel	72068
	4 in. Pipe Fit	PVC	Chrome	72098
	4 in. Hub Fit	PVC	Brass	72039
	4 in. Hub Fit	PVC	Nickel	72069
	4 in. Hub Fit	PVC	Chrome	72099

Primer tap knock-out option available on 3" or 4" Pipe Fit and 4" Pipe Fit bases. 4" Hub Fit base does not include primer tap.

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.25 – 2.75 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.25 – 2.75 in.	4 in. Pipe
4 in.	2.00 in.	1.25 – 2.75 in.	4 in. Hub

Grate Properties		
Finish	Open Area	Load*
Brass	6.00 in. <sup>2</sup>	Medium
Nickel	6.00 in. <sup>2</sup>	Medium
Chrome	6.00 in. <sup>2</sup>	Medium

\*Load is defined by ASME A112.21.1M.  
Light Duty – Safe live load under 2000 lbs.  
Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.



4700 W. 160th St.  
Cleveland, Ohio 44135  
Ph: (800) 321-9532  
Fax: (800) 321-9535  
www.oatey.com



**SUBMITTAL SPECIFICATION**

**82000 Series  
ABS Adjustable General Purpose Drain  
PVC Barrel With 5" Round Grate With Round Ring**



**Engineering Specification:** Oatey adjustable general purpose floor drains are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Grate Finish	Part Number
	3 or 4 in. Pipe Fit	ABS	Brass	82037
	3 or 4 in. Pipe Fit	ABS	Nickel	82067
	3 or 4 in. Pipe Fit	ABS	Chrome	82097
	4 in. Pipe Fit	ABS	Brass	82038
	4 in. Pipe Fit	ABS	Nickel	82068
	4 in. Pipe Fit	ABS	Chrome	82098
	4 in. Hub Fit	ABS	Brass	82039
	4 in. Hub Fit	ABS	Nickel	82069
	4 in. Hub Fit	ABS	Chrome	82099

Primer tap knock-out option available on 3" or 4" Pipe Fit and 4" Pipe Fit bases. 4" Hub Fit base does not include primer tap.

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.25 – 2.75 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.25 – 2.75 in.	4 in. Pipe
4 in.	2.00 in.	1.25 – 2.75 in.	4 in. Hub

Finish	Grate Properties	
	Open Area	Load*
Brass	6.00 in. <sup>2</sup>	Medium
Nickel	6.00 in. <sup>2</sup>	Medium
Chrome	6.00 in. <sup>2</sup>	Medium

\*Load is defined by ASME A112.21.1M.  
Light Duty – Safe live load under 2000 lbs.  
Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.