



No.:

Date: 27-DEC-2012

Customer :

TECHNICAL PROPOSAL

Three-phase induction motor - Squirrel cage rotor

Product line : Close Coupled Pump : Three-Phase - "JP" Type - ODP - High Efficiency

Catalog Number : 10036OP3V365JPV

List Price : \$8,860

Notes:

Performed by:

Checked:



No.:

Date: 27-DEC-2012

## DATA SHEET

### Three-phase induction motor - Squirrel cage rotor

Customer :  
Product line : Close Coupled Pump : Three-Phase - "JP" Type - ODP - High Efficiency

Frame : 365JP  
Output : 100 HP  
Frequency : 60 Hz  
Poles : 2  
Full load speed : 3560  
Slip : 1.11 %  
Voltage : 200/400 V  
Rated current : 271/136 A  
Locked rotor current : 1710/855 A  
Locked rotor current (I<sub>L</sub>/I<sub>n</sub>) : 6.3  
No-load current : 78.2/39.1 A  
Full load torque : 146 lb.ft  
Locked rotor torque : 190 %  
Breakdown torque : 270 %  
Design : B  
Insulation class : F  
Temperature rise : 80 K  
Locked rotor time : 13 s (hot)  
Service factor : 1.15  
Duty cycle : S1  
Ambient temperature : -20°C - +40°C  
Altitude : 1000  
Degree of Protection : IP23  
Approximate weight : 825 lb  
Moment of inertia : 7.8750 sq.ft.lb  
Noise level : 83 dB(A)

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6314 C3	6314 C3	100%	0.86	93.0
Regreasing interval	7209 h	7209 h	75%	0.84	93.0
Grease amount	27 g	27 g	50%	0.82	93.0

Notes:

Performed by

Checked




No.:

Date: 27-DEC-2012

### PERFORMANCE CURVES RELATED TO RATED OUTPUT

Three-phase induction motor - Squirrel cage rotor



Customer :  
Product line : Close Coupled Pump : Three-Phase - "JP" Type - ODP - High Efficiency

Frame	: 365JP	Locked rotor current (I <sub>l</sub> /I <sub>n</sub> )	: 6.3
Output	: 100 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.15
Full load speed	: 3560	Design	: B
Voltage	: 200/400 V	Locked rotor torque	: 190 %
Rated current	: 271/136 A	Breakdown torque	: 270 %
Insulation class	: F		

Notes:

Performed by


Checked



No.:

Date: 27-DEC-2012

### CHARACTERISTIC CURVES RELATED TO SPEED Three-phase induction motor - Squirrel cage rotor




Customer :  
Product line : Close Coupled Pump : Three-Phase - "JP" Type - ODP - High Efficiency

Frame	: 365JP	Locked rotor current (I <sub>l</sub> /I <sub>n</sub> )	: 6.3
Output	: 100 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.15
Full load speed	: 3560	Design	: B
Voltage	: 200/400 V	Locked rotor torque	: 190 %
Rated current	: 271/136 A	Breakdown torque	: 270 %
Insulation class	: F		

Notes:

Performed by

Checked



Notes:

Performed by:

Checked:

Customer:

Close Coupled Pump : Three-Phase - "JP" Type - ODP - High Efficiency

Three-phase induction motor  
Frame 365JP - IP23

27-DEC-2012



P	AA	ER	EQ	ET
17.874	NPT 3"	8.130	2.382	5.886
U	EM	EL	S	EP
1.624	1.750	2.125	0.375	2.756
R	ES	d1	t1	t2
1.413	2.480	EUNC 1/2"-13	0.984	1.496
C	Flange	AJ	AK	BD
32.019	FC-279	11.000	12.500	13.189
BF	BB	BC	AH	
UNC 5/8"x11	0.250		8.130	