

Models 86HEPA-Dry and 86HEPA Wet/Dry

Compact All-Steel HEPA Vacuums

The 86ASB5D4C is a compact all-steel HEPA wet/dry vacuums that are small and lightweight enough to be easily carried or transported, yet rugged enough to handle the toughest jobsites. Designed to work in congested, tight areas. These vacuums are also excellent tools in many maintenance and shop environments for fast, convenient pick-up of hazardous materials.

Powerful Vacuum:




A 1 horsepower, 2 stage by-pass, 7.2 amp motor delivers 85" waterlift and 96" CFM. Plenty of power for fast pick-up of dry or wet/dry non-flammable, hazardous materials.

True 99.97% Type A Large Capacity HEPA Filter:

Individually tested and certified to have a minimum efficiency of 99.97% at .3 microns in accordance with IEST-RP-CC001 test requirements.



Features:

-  High efficiency 2-ply enclosed, disposable paper filter bag acts as the primary filter to trap and hold dry material for easy handling and disposal. (B700408)
-  Complete HEPA Filter Assembly consisting of air seal gasket, polyester prefilter, spacer sleeve and Dacron filter bag (B526520)
-  Wet pickup adapter with reliable float shut-off (B260089 for the 86HEPA Wet/Dry)

Pullman-Holt HEPA Filter System



Air Seal Gasket – Provides tight air seal and prevents leakage.


HEPA Media – The filter is made from a single piece of high-grade HEPA media to eliminate the possibility of leaks. The pleats in the media are held open by corrugated aluminum separators for maximum airflow.

Spacer Sleeve – The purpose of the spacer sleeve is to space the Dacron bag away from the HEPA filter body so as to utilize the full area of the "Never Clog" Dacron bag.

Polyester Prefilter – This impact filter is about one inch thick and is attached to the inlet (bottom) surface of each HEPA filter. Its function is to provide final protection to the HEPA filter from premature failure due to clogging.

"Never Clog" Filter Bag – Sheds dirt and debris like a duck sheds water. Shakes clean to maintain maximum airflow.

Each Pullman-Holt HEPA filter is tested and certified to provide a minimum efficiency of 99.97% at .3 microns based on IEST-RP-CC001 test requirements.



86ASB5D4C Specifications

86ASB5D4C Style:	Dry
86ASB54C Style:	Wet/Dry
Horsepower:	1
Waterlift:	85"
CFM:	96
Recovery:	.75 bu / 5 gallon
86ASB5D4C Shipping Weight:	42 lbs.
86ASB54C Shipping Weight:	54 lbs.
86ASB5D4C Product Code:	B160419
86ASB54C Product Code:	B160420

Accessories



86HEPA-Dry Only Accessories



86HEPA-Wet/Dry Only Accessories

