



# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

Date of issue: 01/17/2014

Revision date: 09/08/2015

Version: 1.1

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Product name : Sakrete Fast Setting Cement Patcher  
Sakrete Leak Stopper Hydraulic Cement (Gray)

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture : Various.

#### 1.3. Details of the supplier of the safety data sheet

Sakrete Of North America  
8201 Arrowridge Blvd.  
Charlotte, NC 28273 - USA  
T 866-725-7383

#### 1.4. Emergency telephone number

Emergency number : CHEMTREC (800) 424-9300  
CHEMTREC International +1 (703) 527-3887 24 hr

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### GHS-US classification

Skin Irritation 2  
Serious Eye Damage 1  
Carcinogenicity 1A  
Specific Target Organ Toxicity After Single Exposure 3  
Specific Target Organ Toxicity After Repeated Exposure 1

#### 2.2. Label elements

##### GHS-US labelling

Hazard pictograms (GHS-US) :



Signal word (GHS-US) :

Danger

Hazard statements (GHS-US) :

Causes skin irritation. Causes serious eye damage. May cause cancer. May cause respiratory irritation. Causes damage to lungs through prolonged or repeated exposure.

Precautionary statements (GHS-US) :

Do not eat, drink or smoke when using this product. Wash hands thoroughly after handling. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves/protective clothing/eye protection/face protection. Use only outdoors or in a well-ventilated area. Do not breathe dust. If exposed or concerned: Get medical advice/attention. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center/doctor. If on skin: Wash with plenty of water. Take off contaminated clothing and wash it before reuse. If skin irritation occurs: Get medical advice/attention. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Dispose of contents and container in accordance with all local, regional, national and international regulations.

#### 2.3. Other hazards

Other hazards not contributing to the classification : Not applicable.

#### 2.4. Unknown acute toxicity (GHS US)

*Sakrete Leak Stopper Hydraulic Cement (Gray)*: 18% of the mixture consists of ingredient(s) of unknown acute toxicity.  
*Sakrete Fast Setting Cement Patcher*: 10% of the mixture consists of ingredient(s) of unknown acute toxicity.

# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

### SECTION 3: Composition/information on ingredients

#### 3.1. Substance

Not applicable.

#### 3.2. Mixture

Name	Product identifier	%
Quartz	(CAS No) 14808-60-7	≤75
Cement, alumina, chemicals	(CAS No) 65997-16-2	≤30 <sup>2</sup>
Cement, portland, chemicals	(CAS No) 65997-15-1	5 - 30
Calcium oxide	(CAS No) 1305-78-8	≤7
Sodium carbonate	(CAS No) 497-19-8	≤5 <sup>2</sup>
Iron oxide	(CAS No) 1309-37-1	≤5
Aluminum sulfate	(CAS No) 10043-01-3	1.5 - 3 <sup>1</sup>
Aluminum oxide	(CAS No) 1344-28-1	1.5 - 3 <sup>1</sup>
Magnesium oxide	(CAS No) 1309-48-4	≤3
Calcium hydroxide	(CAS No) 1305-62-0	0.5 - 2 <sup>2</sup>
Calcium magnesium hydroxide oxide	(CAS No) 58398-71-3	1.5 - 3 <sup>2</sup>
Calcium magnesium hydroxide	(CAS No) 39445-23-3	1.5 - 3 <sup>2</sup>
Limestone	(CAS No) 1317-65-3	≤1.5
Gypsum	(CAS No) 13397-24-5	≤1.5
Calcium sulfate	(CAS No) 7778-18-9	≤1.5

<sup>1</sup> Sakrete Fast Setting Cement Patcher  
<sup>2</sup> Sakrete Leak Stopper Hydraulic Cement

\* The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

- First-aid measures after inhalation : If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.
- First-aid measures after skin contact : In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Call a physician if irritation develops and persists.
- First-aid measures after eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. If easy to do, remove contact lenses, if worn. Get medical attention immediately.
- First-aid measures after ingestion : If swallowed, do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Immediately call a POISON CENTER or doctor/physician.

#### 4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/injuries after inhalation : May cause respiratory tract irritation.
- Symptoms/injuries after skin contact : Causes skin irritation. May cause burns in the presence of moisture. Skin contact during hydration may slowly develop sufficient heat that may cause severe burns possibly resulting in permanent injury. Do not allow product to harden around any body part or allow continuous, prolonged contact with skin. Handling can cause dry skin.
- Symptoms/injuries after eye contact : Causes serious eye damage. May cause burns in the presence of moisture. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
- Symptoms/injuries after ingestion : May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

#### 4.3. Indication of any immediate medical attention and special treatment needed

Symptoms may not appear immediately. In case of accident or if you feel unwell, seek medical advice immediately (show the label or SDS where possible).

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

- Suitable extinguishing media : Treat for surrounding material.
- Unsuitable extinguishing media : Not available.

#### 5.2. Special hazards arising from the substance or mixture

- Fire hazard : Products of combustion may include, and are not limited to: oxides of carbon.

# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

### 5.3. Advice for firefighters

Firefighting instructions : Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

General measures : Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

### 6.2. Methods and material for containment and cleaning up

For containment : Contain spill, then place in a suitable container. Do not flush to sewer or allow to enter waterways. Use appropriate Personal Protective Equipment (PPE).

Methods for cleaning up : Vacuum or sweep material and place in a disposal container.

### 6.3. Reference to other sections

No additional information available.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Avoid contact with skin and eyes. Do not swallow. Avoid generating and breathing dust. Good housekeeping is important to prevent accumulation of dust. The use of compressed air for cleaning clothing, equipment, etc, is not recommended. Handle and open container with care. When using do not eat, drink or smoke.

Hygiene measures : Launder contaminated clothing before reuse. Wash hands before eating, drinking, or smoking.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep out of the reach of children. Store in dust-tight, dry, labelled containers. Keep container tightly closed when not in use. Avoid any dust buildup by frequent cleaning and suitable construction of the storage area. Do not store in an area equipped with emergency water sprinklers.

### 7.3. Specific end use(s)

No additional information available.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Quartz (14808-60-7)		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	0.025 mg/m <sup>3</sup> (respirable fraction)
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	(30)/(%SiO <sub>2</sub> + 2) mg/m <sup>3</sup> TWA, total dust (250)/(%SiO <sub>2</sub> + 5) mppcf TWA, respirable fraction (10)/(%SiO <sub>2</sub> + 2) mg/m <sup>3</sup> TWA, respirable fraction

Cement, alumina, chemicals (65997-16-2)		
ACGIH	Not applicable	
OSHA	Not applicable	

Cement, portland, chemicals (65997-15-1)		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	1 mg/m <sup>3</sup> (particulate matter containing no asbestos and <1% crystalline silica, respirable fraction)
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup> (total dust) 5 mg/m <sup>3</sup> (respirable fraction) 50 mppcf (<1% Crystalline silica)

Calcium oxide (1305-78-8)		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	2 mg/m <sup>3</sup>
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	5 mg/m <sup>3</sup>

Sodium carbonate (497-19-8)		
ACGIH	Not applicable	
OSHA	Not applicable	

# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

<b>Iron oxide (1309-37-1)</b>		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	5 mg/m <sup>3</sup> (respirable fraction)
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	10 mg/m <sup>3</sup> (fume) 15 mg/m <sup>3</sup> (total dust) 5 mg/m <sup>3</sup> (respirable fraction)
<b>Aluminum sulfate (10043-01-3)</b>		
ACGIH	Not applicable	
OSHA	Not applicable	
<b>Aluminum oxide (1344-28-1)</b>		
ACGIH	Not applicable	
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup> (total dust) 5 mg/m <sup>3</sup> (respirable fraction)
<b>Magnesium oxide (1309-48-4)</b>		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	10 mg/m <sup>3</sup> (inhalable fraction)
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup> (fume, total particulate)
<b>Calcium hydroxide (1305-62-0)</b>		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	5 mg/m <sup>3</sup>
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup> (total dust) 5 mg/m <sup>3</sup> (respirable fraction)
<b>Calcium magnesium hydroxide oxide (58398-71-3)</b>		
ACGIH	Not applicable	
OSHA	Not applicable	
<b>Calcium magnesium hydroxide (39445-23-3)</b>		
ACGIH	Not applicable	
OSHA	Not applicable	
<b>Limestone (1317-65-3)</b>		
ACGIH	Not applicable	
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup> (total dust) 5 mg/m <sup>3</sup> (respirable fraction)
<b>Gypsum (13397-24-5)</b>		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	10 mg/m <sup>3</sup> (inhalable fraction)
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup> (total dust) 5 mg/m <sup>3</sup> (respirable fraction)
<b>Calcium sulfate (7778-18-9)</b>		
ACGIH	ACGIH TWA (mg/m <sup>3</sup> )	10 mg/m <sup>3</sup> (inhalable fraction)
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	15 mg/m <sup>3</sup> (total dust) 5 mg/m <sup>3</sup> (respirable fraction)

### 8.2. Exposure controls

Appropriate engineering controls	: Use ventilation adequate to keep exposures (airborne levels of dust, fume, vapor, etc.) below recommended exposure limits.
Hand protection	: Wear suitable waterproof gloves.
Eye protection	: Wear approved eye protection (properly fitted dust- or splash-proof chemical safety goggles) and face protection (face shield).
Skin and body protection	: Wear suitable waterproof protective clothing.

# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

Respiratory protection	: A NIOSH approved dust mask or filtering facepiece is recommended in poorly ventilated areas or when permissible exposure limits may be exceeded. Respirators should be selected by and used under the direction of a trained health and safety professional following requirements found in OSHA's respirator standard (29 CFR 1910.134) and ANSI's standard for respiratory protection (Z88.2).
Other information	: Handle according to established industrial hygiene and safety practices. Do not eat, smoke or drink where material is handled, processed or stored. Wash hands carefully before eating or smoking.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Solid
Appearance	: Powder
Colour	: Various
Odour	: Characteristic
Odour threshold	: No data available
pH	: 10 - 13
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Flammability (solid, gas)	: Not Flammable
Explosive limits	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Vapour pressure	: No data available
Relative density	: No data available
Relative vapour density at 20 °C	: No data available
Solubility	: No data available
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available

### 9.2. Other information

VOC content	: 0%, Not applicable; 0 wt, Not applicable.
-------------	---

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No dangerous reaction known under conditions of normal use.

### 10.2. Chemical stability

Stable under normal storage conditions. Keep dry in storage.

### 10.3. Possibility of hazardous reactions

No dangerous reaction known under conditions of normal use.

### 10.4. Conditions to avoid

Incompatible materials. Moisture.

### 10.5. Incompatible materials

Wet cement is alkaline and incompatible with acid, ammonium salts and aluminum metal.

### 10.6. Hazardous decomposition products

May include, and are not limited to: oxides of carbon.

# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

Acute toxicity : Not classified.

Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)	
LD50 oral rat	> 2000 mg/kg
LD50 dermal rabbit	No data available
LC50 inhalation rat	No data available

Calcium oxide (1305-78-8)	
LD50 oral rat	> 2000 mg/kg

Sodium carbonate (497-19-8)	
LD50 oral rat	4090 mg/kg
LC50 inhalation rat	2300 mg/m <sup>3</sup> /2h

Iron oxide (1309-37-1)	
LD50 oral rat	> 10000 mg/kg

Aluminum sulfate (10043-01-3)	
LD50 oral rat	1930 mg/kg

Aluminum oxide (1344-28-1)	
LD50 oral rat	> 5000 mg/kg

Calcium hydroxide (1305-62-0)	
LD50 oral rat	7340 mg/kg

Calcium sulfate (7778-18-9)	
LD50 oral rat	> 3000 mg/kg

Skin corrosion/irritation : Causes skin irritation.  
 Serious eye damage/irritation : Causes serious eye damage.  
 Respiratory or skin sensitisation : Based on available data, the classification criteria are not met.  
 Germ cell mutagenicity : Based on available data, the classification criteria are not met.  
 Carcinogenicity : May cause cancer.

Quartz (14808-60-7)	
IARC group	1 - Carcinogenic to humans
National Toxicology Program (NTP) Status	2 - Known Human Carcinogens

Iron oxide (1309-37-1)	
IARC group	3 - Not classifiable

Reproductive toxicity : Based on available data, the classification criteria are not met.  
 Specific target organ toxicity (single exposure) : May cause respiratory irritation.  
 Specific target organ toxicity (repeated exposure) : Causes damage to lungs through prolonged or repeated exposure. (Respirable crystalline silica in the form of quartz or cristobalite from occupational sources is listed by the International Agency for Research on Cancer (IARC) and National Toxicology Program (NTP) as a lung carcinogen. Prolonged exposure to respirable crystalline silica has been known to cause silicosis, a lung disease, which may be disabling. While there may be a factor of individual susceptibility to a given exposure to respirable silica dust, the risk of contracting silicosis and the severity of the disease is clearly related to the amount of dust exposure and the length of time (usually years) of exposure.)  
 Aspiration hazard : Based on available data, the classification criteria are not met.  
 Symptoms/injuries after inhalation : May cause respiratory tract irritation.  
 Symptoms/injuries after skin contact : Causes skin irritation. May cause burns in the presence of moisture. Skin contact during hydration may slowly develop sufficient heat that may cause severe burns possibly resulting in permanent injury. Do not allow product to harden around any body part or allow continuous, prolonged contact with skin. Handling can cause dry skin.  
 Symptoms/injuries after eye contact : Causes serious eye damage. May cause burns in the presence of moisture. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.

# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

Symptoms/injuries after ingestion : May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

### SECTION 12: Ecological information

#### 12.1. Toxicity

Ecology - general : No ecological consideration when used according to directions. Normal dilution of this product to drains, sewers, septic systems and treatment plants is not considered environmentally harmful.

#### 12.2. Persistence and degradability

##### Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

Persistence and degradability	No data available.
-------------------------------	--------------------

#### 12.3. Bioaccumulative potential

##### Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

Bioaccumulative potential	No data available.
---------------------------	--------------------

#### 12.4. Mobility in soil

##### Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

Ecology - soil	No data available.
----------------	--------------------

#### 12.5. Other adverse effects

Effect on the global warming : No known ecological damage caused by this product.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Waste disposal recommendations : This material must be disposed of in accordance with all local, state, provincial, and federal regulations.

### SECTION 14: Transport information

#### Department of Transportation (DOT)

In accordance with DOT.

Not regulated for transport.

#### Additional information

Other information : No supplementary information available.

### SECTION 15: Regulatory information

#### 15.1. US Federal regulations

All components of this product are listed, or excluded from listing, on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory except for:

Gypsum	CAS No 13397-24-5
--------	-------------------

##### Aluminum oxide (1344-28-1)

Subject to reporting requirements of United States SARA Section 313

SARA Section 313 - Emission Reporting	1.0 % (fibrous forms)
---------------------------------------	-----------------------

#### 15.2. US State regulations

##### Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

State or local regulations	This product contains Crystalline Silica, Quartz and may also contain other chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.
----------------------------	---

### SECTION 16: Other information

Date of issue : 01/17/2014

Revision date : 09/08/2015

Version : 1.1

Data sources : SDS prepared pursuant to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

# Sakrete Fast Setting Cement Patcher/Sakrete Leak Stopper Hydraulic Cement (Gray)

## Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

NFPA health hazard


: 3 - Short exposure could cause serious temporary or residual injury even though prompt medical attention was given.

NFPA fire hazard

: 1 - Must be preheated before ignition can occur.

NFPA reactivity

: 0 - Normally stable, even under fire exposure conditions, and are not reactive with water.



*Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.*