



SAFETY DATA SHEET

Section 1: IDENTIFICATION

1.1 PRODUCT IDENTIFIER

Product Name: Sakrete Flo-Coat Driveway Sealer

1.2 RECOMMENDED USE OF CHEMICAL AND RESTRICTIONS ON USE

Use: Various.

1.3 DETAILS OF THE SUPPLIER OF THE SAFETY DATA SHEET

Name/Address: Sakrete of North America
8201 Arrowridge Blvd.
Charlotte, NC
28273

Telephone Number: 866-725-7383

1.4 EMERGENCY TELEPHONE NUMBER

Emergency Telephone Number: CHEMTREC 800-424-9300
INTERNATIONAL + 01-703-527-3887

Section 2: HAZARD(S) IDENTIFICATION

2.1 CLASSIFICATION OF THE CHEMICAL

Hazard class

Acute toxicity 4 (Oral)
Skin sensitization 1
Specific target organ toxicity - Repeated exposure 1
Carcinogenicity 1A
Germ cell mutagenicity 1B
Reproductive toxicity 1B

2.2 LABEL ELEMENTS

Hazard Pictogram:



Signal Word: Danger

Hazard Statement: Harmful if swallowed. May cause an allergic skin reaction. Causes damage to organs through prolonged or repeated exposure. May cause cancer. May cause genetic defects. May damage fertility or the unborn child.

Prevention : If swallowed: Immediately call a poison center/doctor. Rinse mouth. Do not breathe dust/fume/gas/mist/vapors/spray. Wear protective gloves/protective clothing/eye protection/face protection. Do not eat, drink or smoke when using this product. Wash hands thoroughly after handling. Contaminated work clothing must not be allowed out of the workplace. Do not handle until all safety precautions have been read and understood. Obtain special instructions before use.



SAFETY DATA SHEET

Response: If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Wash contaminated clothing before reuse. If exposed or concerned: Get medical advice/attention.

Storage: Store locked up.

Disposal: Dispose of contents and container in accordance with all local, regional, national and international regulations.

2.3 ADDITIONAL INFORMATION

Hazards not otherwise specified: Not applicable.

20.7 % of the mixture consists of ingredient(s) of unknown acute toxicity.

Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 MIXTURES

Ingredient	CAS No	Wt. %
Silica, crystalline, quartz	14808-60-7	10 - 30
Tar, coal	8007-45-2	10 - 30
Feldspar-group minerals	68476-25-5	1 - 5
Naphthalene	91-20-3	0.5 - 1.5
Titanium dioxide	13463-67-7	0.1 - 1
Benz[a]anthracene	56-55-3	0.1 - 1
Chrysene	218-01-9	0.1 - 1
Benzo[a]pyrene	50-32-8	0.1 - 1
Indeno[1,2,3-cd]pyrene	193-39-5	0.1 - 1
Carbazole	86-74-8	0.1 - 1
Benzo[j]fluoranthene	205-82-3	0.1 - 1
Dibenzo[a,h]pyrene	189-64-0	0.1 - 1
Dibenzo[a,i]pyrene	189-55-9	0.1 - 1

The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

Section 4: FIRST-AID MEASURES

4.1 DESCRIPTION OF THE FIRST AID MEASURE

Eye: In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. If easy to do, remove contact lenses, if worn. Call a physician if irritation develops and persists.

Skin: In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Call a physician if irritation develops and persists.

Inhalation: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.

Ingestion: If swallowed, do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical advice/attention.



SAFETY DATA SHEET

4.2 MOST IMPORTANT SYMPTOMS AND EFFECTS, BOTH ACUTE AND DELAYED

Eye:	May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
Skin:	May cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin. May cause skin sensitization.
Inhalation:	May cause respiratory tract irritation.
Ingestion:	Harmful if swallowed. May cause stomach distress, nausea or vomiting.

4.3 INDICATION OF ANY IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENTS NEEDED

Note to Physicians:	Symptoms may not appear immediately.
Specific Treatments:	In case of accident or if you feel unwell, seek medical advice immediately (show the label or SDS where possible).

Section 5: FIRE-FIGHTING MEASURES

5.1 EXTINGUISHING MEDIA

Suitable Extinguishing Media:	Treat for surrounding material.
Unsuitable Extinguishing Media:	Not available.

5.2 SPECIAL HAZARDS ARISING FROM THE CHEMICAL

Products of Combustion:	May include, and are not limited to: oxides of carbon.
--------------------------------	--

5.3 SPECIAL PROTECTIVE EQUIPMENT AND PRECAUTIONS FOR FIRE FIGHTERS

Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

Section 6: ACCIDENTAL RELEASE MEASURES

6.1 PERSONAL PRECAUTIONS, PROTECTIVE EQUIPMENT AND EMERGENCY PROCEDURES

Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

6.2 METHODS AND MATERIALS FOR CONTAINMENT AND CLEANING - UP

Methods for Containment:	Contain spill, then place in a suitable container. Do not flush to sewer or allow to enter waterways. Use appropriate Personal Protective Equipment (PPE).
Methods for Cleaning-Up:	Scoop up material and place in a disposal container.

Section 7: HANDLING AND STORAGE

7.1 PRECAUTIONS FOR SAFE HANDLING

Handling:	Avoid contact with skin and eyes. Do not swallow. Avoid breathing vapour or mist. Handle and open container with care. When using do not eat or drink. Wash hands before eating, drinking, or smoking. (See section 8)
------------------	--



SAFETY DATA SHEET

General Hygiene Advice: Launder contaminated clothing before reuse. Wash hands before eating, drinking, or smoking.

7.2 CONDITIONS FOR SAFE STORAGE, INCLUDING ANY INCOMPATIBILITIES

Storage: Keep out of the reach of children. Keep container tightly closed and in a well-ventilated place. (See section 10)

Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 CONTROL PARAMETERS

Exposure Guidelines

Occupational Exposure Limits		
Ingredient	OSHA-PEL	ACGIH-TLV
Silica, crystalline, quartz	((10 mg/m ³)/(%SiO ₂ +2) TWA (resp)); ((30 mg/m ³)/(%SiO ₂ +2) TWA (total)); ((250)/(%SiO ₂ +5) mppcf TWA (resp))	0.025 mg/m ³
Tar, coal	Not available.	Not available.
Feldspar-group minerals	Not available.	Not available.
Naphthalene	10 ppm	10 ppm
Titanium dioxide	15 mg/m ³ (total dust)	10 mg/m ³
Benz[a]anthracene	Not available.	Not available.
Chrysene	0.2 mg/m ³	Not available.
Benzo[a]pyrene	Not available.	Not available.
Indeno[1,2,3-cd]pyrene	Not available.	Not available.
Carbazole	Not available.	Not available.
Benzo[j]fluoranthene	Not available.	Not available.
Dibenzo[a,h]pyrene	Not available.	Not available.
Dibenzo[a,i]pyrene	Not available.	Not available.

8.2 EXPOSURE CONTROLS

Engineering Controls: Use ventilation adequate to keep exposures (airborne levels of dust, fume, vapor, etc.) below recommended exposure limits.

8.3 INDIVIDUAL PROTECTIVE MEASURES

Personal Protective Equipment:

Eye/Face Protection: Wear approved eye (properly fitted dust- or splash-proof chemical safety goggles) / face (face shield) protection.

Skin Protection:

Hand Protection: Wear suitable waterproof gloves.

Body Protection: Wear suitable waterproof protective clothing.

Respiratory Protection: A NIOSH approved dust mask or filtering facepiece is recommended in poorly ventilated areas or when permissible exposure limits may be exceeded. Respirators should be selected by and used under the direction of a trained health and safety professional following requirements found in OSHA's respirator standard (29 CFR 1910.134) and ANSI's standard for respiratory protection (Z88.2).

General Health and Safety Measures: Handle according to established industrial hygiene and safety practices. Do not eat, smoke or drink where material is handled, processed or stored. Wash hands carefully before eating or smoking.



SAFETY DATA SHEET

Section 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1 INFORMATION ON BASIC PHYSICAL AND CHEMICAL PROPERTIES

Appearance:	Paste.
Color:	Not available.
Odor:	Not available.
Odor Threshold:	Not available.
Physical State:	Liquid.
pH:	Not available.
Melting Point/Freezing Point:	Not available.
Initial Boiling Point and Boiling Range:	Not available.
Flash Point:	Not available.
Evaporation Rate:	Not available.
Flammability:	Not Flammable.
Lower Flammability/Explosive Limit:	Not available.
Upper Flammability/Explosive Limit:	Not available.
Vapor Pressure:	Not available.
Vapor Density:	Not available.
Relative Density/Specific Gravity:	Not available.
Solubility:	Not available.
Partition coefficient: n-octanol/water:	Not available.
Auto-ignition Temperature:	Not available.
Decomposition Temperature:	Not available.
Viscosity:	Not available.
Percent Volatile, wt. %:	Not available.
VOC content, wt. %:	Not available.

Section 10: STABILITY AND REACTIVITY

10.1 REACTIVITY

No dangerous reaction known under conditions of normal use.

10.2 CHEMICAL STABILITY

Stable under normal storage conditions.

10.3 POSSIBILITY OF HAZARDOUS REACTIONS

No dangerous reaction known under conditions of normal use.

10.4 CONDITIONS TO AVOID

Incompatible materials.

**SAFETY DATA SHEET****10.5 INCOMPATIBLE MATERIALS**

None known.

10.6 HAZARDOUS DECOMPOSITION PRODUCTS

May include, and are not limited to: oxides of carbon.

Section 11: TOXICOLOGICAL INFORMATION**11.1 INFORMATION ON TOXICOLOGICAL EFFECTS****Likely Routes of Exposure:** Skin contact, skin absorption, eye contact, inhalation, and ingestion.**Symptoms related to physical/chemical/toxicological characteristics:****Eye:** May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.**Skin:** May cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin. May cause skin sensitization.**Ingestion:** Harmful if swallowed. May cause stomach distress, nausea or vomiting.**Inhalation:** May cause respiratory tract irritation.**Acute Toxicity:**

Ingredient	LC50	LD50
Silica, crystalline, quartz	Not available.	Oral 500 mg/kg, rat
Tar, coal	Not available.	Not available.
Feldspar-group minerals	Not available.	Not available.
Naphthalene	Inhalation >340 mg/m ³ 1 h, rat	Oral 490 mg/kg, rat Dermal >2500 mg/kg, rat Dermal >20000 mg/kg, rabbit
Titanium dioxide	Not available.	Oral >10000 mg/kg, rat Dermal >10000mg/kg, rabbit
Benz[a]anthracene	Not available.	Not available.
Chrysene	Not available.	Not available.
Benzo[a]pyrene	Not available.	Not available.
Indeno[1,2,3-cd]pyrene	Not available.	Not available.
Carbazole	Not available.	Oral >5000 mg/kg, rat
Benzo[j]fluoranthene	Not available.	Not available.
Dibenzo[a,h]pyrene	Not available.	Not available.
Dibenzo[a,i]pyrene	Not available.	Not available.

Calculated overall Chemical Acute Toxicity Values

LC50 (inhalation)	LD50 (oral)	LD50 (dermal)
20.1 mg/L 4 h, rat	1793.9 mg/kg, rat	> 2000 mg/kg, rabbit

Ingredient	Chemical Listed as Carcinogen or Potential Carcinogen (NTP, IARC, OSHA, ACGIH, CP65)*
Silica, crystalline, quartz	G-A2, I-1, N-1, O, CP65
Tar, coal	I-1, N-1
Feldspar-group minerals	Not listed.
Naphthalene	G-A4, I-2B, N-2, CP65
Titanium dioxide	G-A4, I-2B, O, CP65

**SAFETY DATA SHEET**

Benz[a]anthracene	G-A2, I-2B, N-2, CP65
Chrysene	G-A3, I-2B, CP65
Benzo[a]pyrene	G-A2, I-1, N-2, CP65
Indeno[1,2,3-cd]pyrene	I-2B, N-2, O, CP65
Carbazole	I-2B, O, CP65
Benzo[j]fluoranthene	I-2B, N-2, O, CP65
Dibenzo[a,h]pyrene	I-2B, N-2, O, CP66
Dibenzo[a,i]pyrene	I-2B, N-2, O, CP65

11.2 DELAYED, IMMEDIATE, AND CHRONIC EFFECTS OF SHORT- AND LONG-TERM EXPOSURE

Skin Corrosion/Irritation:	Based on available data, the classification criteria are not met.
Serious Eye Damage/Irritation:	Based on available data, the classification criteria are not met.
Respiratory Sensitization:	Based on available data, the classification criteria are not met.
Skin Sensitization:	May cause an allergic skin reaction.
STOT-Single Exposure:	Based on available data, the classification criteria are not met.
Chronic Health Effects:	Respirable crystalline silica in the form of quartz or cristobalite from occupational sources is listed by the International Agency for Research on Cancer (IARC) and National Toxicology Program (NTP) as a lung carcinogen. Prolonged exposure to respirable crystalline silica has been known to cause silicosis, a lung disease, which may be disabling. While there may be a factor of individual susceptibility to a given exposure to respirable silica dust, the risk of contracting silicosis and the severity of the disease is clearly related to the amount of dust exposure and the length of time (usually years) of exposure.
Carcinogenicity:	May cause cancer.
Germ Cell Mutagenicity:	May cause genetic defects.
Reproductive Toxicity:	
Developmental:	May damage the unborn child.
Fertility:	May damage fertility.
STOT-Repeated Exposure:	Causes damage to organs through prolonged or repeated exposure.
Aspiration Hazard:	Based on available data, the classification criteria are not met.
Toxicologically Synergistic Materials:	Not available.
Other Information:	Not available.

Section 12: ECOLOGICAL INFORMATION**12.1 ECOTOXICITY**

Acute/Chronic Toxicity:	No ecological consideration when used according to directions. Normal dilution of this product to drains, sewers, septic systems and treatment plants is not considered environmentally harmful.
--------------------------------	--

12.2 PERSISTENCE AND DEGRADABILITY

Not available.



SAFETY DATA SHEET

12.3 BIOACCUMULATIVE POTENTIAL

Bioaccumulation: Not available.

12.4 MOBILITY IN SOIL

Not available.

12.5 OTHER ADVERSE EFFECTS

Not available.

Section 13: DISPOSAL CONSIDERATIONS

13.1 WASTE TREATMENT METHODS

Disposal Method: This material must be disposed of in accordance with all local, state, provincial, and federal regulations.

Other disposal recommendations: Not available.

Section 14: TRANSPORT INFORMATION

14.1 UN NUMBER

Not regulated.

14.2 UN PROPER SHIPPING NAME

Not applicable.

14.3 TRANSPORT HAZARD CLASS(ES)

Not applicable.

14.4 PACKING GROUP

Not applicable.

14.5 ENVIRONMENTAL HAZARDS

Not available.

14.6 TRANSPORT IN BULK ACCORDING TO ANNEX II OF MARPOL 73/78 AND THE IBC CODE

Not available.

14.7 SPECIAL PRECAUTIONS FOR USER

Do not handle until all safety precautions have been read and understood.

Section 15: REGULATORY INFORMATION

15.1 SAFETY, HEALTH AND ENVIRONMENTAL REGULATIONS/ LEGISLATIONS SPECIFIC FOR THE CHEMICAL

MSDS prepared pursuant to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

SARA Title III				
Ingredient	Section 302 (EHS) TPQ (lbs.)	Section 304 EHS RQ (lbs.)	CERCLA RQ (lbs.)	Section 313
Silica, crystalline, quartz	Not listed.	Not listed.	Not listed.	Not listed.
Tar, coal	Not listed.	Not listed.	Not listed.	Not listed.
Feldspar-group minerals	Not listed.	Not listed.	Not listed.	Not listed.



SAFETY DATA SHEET

Naphthalene	Not listed.	Not listed.	100	313
Titanium dioxide	Not listed.	Not listed.	Not listed.	Not listed.
Benz[a]anthracene	Not listed.	Not listed.	10	313+^
Chrysene	Not listed.	Not listed.	100	313
Benzo[a]pyrene	Not listed.	Not listed.	1	313+^
Indeno[1,2,3-cd]pyrene	Not listed.	Not listed.	100	313+^
Carbazole	Not listed.	Not listed.	Not listed.	Not listed.
Benzo[j]fluoranthene	Not listed.	Not listed.	Not listed.	313+^
Dibenzo[a,h]pyrene	Not listed.	Not listed.	Not listed.	313+^
Dibenzo[a,i]pyrene	Not listed.	Not listed.	10	313

State Regulations

California Proposition 65:

This product contains chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.

Global Inventories:

Ingredient	USA TSCA
Silica, crystalline, quartz	Yes.
Tar, coal	Yes.
Feldspar-group minerals	Yes.
Naphthalene	Yes.
Titanium dioxide	Yes.
Benz[a]anthracene	Yes.
Chrysene	Yes.
Benzo[a]pyrene	Yes.
Indeno[1,2,3-cd]pyrene	Yes.
Carbazole	Yes.
Benzo[j]fluoranthene	No.
Dibenzo[a,h]pyrene	No.
Dibenzo[a,i]pyrene	No.

NFPA-National Fire Protection Association:

Health:	2
Fire:	1
Reactivity:	0

Hazard Rating: 0 = minimal, 1 = slight, 2 = moderate, 3 = severe, 4 = extreme

SOURCE AGENCY CARCINOGEN CLASSIFICATIONS:

OSHA (O) Occupational Safety and Health Administration.

ACGIH (G) American Conference of Governmental Industrial Hygienists.

- A1 - Confirmed human carcinogen.
- A2 - Suspected human carcinogen.
- A3 - Animal carcinogen.
- A4 - Not classifiable as a human carcinogen.
- A5 - Not suspected as a human carcinogen.

IARC (I) International Agency for Research on Cancer.

- 1 - The agent (mixture) is carcinogenic to humans.
- 2A - The agent (mixture) is probably carcinogenic to humans; there is limited evidence of carcinogenicity in humans and sufficient evidence of carcinogenicity in experimental animals.
- 2B - The agent (mixture) is possibly carcinogenic to humans; there is limited evidence of carcinogenicity in humans in the absence of sufficient evidence of carcinogenicity in experimental animals.



SAFETY DATA SHEET

- 3 - The agent (mixture, exposure circumstance) is not classifiable as to its carcinogenicity to humans.
- 4 - The agent (mixture, exposure circumstance) is probably not carcinogenic to humans.

NTP (N)

National Toxicology Program.

- 1 - Known to be carcinogens.
- 2 - Reasonably anticipated to be carcinogens.

Section 16: OTHER INFORMATION

Date of Preparation: March 28, 2013

Version: 1.0

Revision Date: July 17, 2014

Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.

Prepared by: Nexreg Compliance Inc.
Phone: (519) 488-5126
www.nexreg.com

Prepared for: Sakrete of North America

End of Safety Data Sheet