



Sakrete US Cold Patch

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

Date of issue: 01/29/2015

Revision date: 01/29/2015

Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name : Sakrete US & Canadian Cold Patch
:

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture : Various.

1.3. Details of the supplier of the safety data sheet

Sakrete of North America
8201 Arrowridge Blvd.
Charlotte, NC 28273
T 866-725-7383

1.4. Emergency telephone number

Emergency number : CHEMTREC (800) 424-9300;CHEMTREC International +1 (703) 527-3887 24 hr

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GHS-US classification

Carcinogenicity 1A
Specific Target Organ Toxicity – Repeated Exposure 1

2.2. Label elements

GHS-US labelling

Hazard pictograms (GHS-US) :



GHS08

Signal word (GHS-US) :

Danger

Hazard statements (GHS-US) :

May cause cancer. Causes damage to lungs through prolonged or repeated exposure.

Precautionary statements (GHS-US) :

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves/protective clothing/eye protection/face protection. Do not breathe dust. Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. If exposed or concerned: Get medical advice/attention. Store locked up. Dispose of contents/container in accordance with local/regional/national/international regulations.

2.3. Other hazards

No additional information available.

2.4. Unknown acute toxicity (GHS-US)

89 percent of the mixture consists of ingredient(s) of unknown acute toxicity.

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable.

3.2. Mixture

Name	Product identifier	%	GHS-US classification
Asphalt	(CAS No) 8052-42-4	5 - 10	Carc. 2
Quartz	(CAS No) 14808-60-7	1 - 5	Carc. 1A STOT RE 1
Carbon black	(CAS No) 1333-86-4	< 0.1	Carc. 2

* The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

Sakrete US Cold Patch

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

SECTION 4: First aid measures

4.1. Description of first aid measures

- First-aid measures after inhalation : If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.
- First-aid measures after skin contact : In case of contact, immediately flush skin with plenty of water. Call a physician if irritation develops and persists.
- First-aid measures after eye contact : In case of contact, immediately flush eyes with plenty of water. Remove contact lenses, if worn. If irritation persists, get medical attention.
- First-aid measures after ingestion : If swallowed, do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/injuries after inhalation : May cause respiratory tract irritation.
- Symptoms/injuries after skin contact : Dust may cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin.
- Symptoms/injuries after eye contact : Dust may cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
- Symptoms/injuries after ingestion : May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

4.3. Indication of any immediate medical attention and special treatment needed

Symptoms may not appear immediately. In case of accident or if you feel unwell, seek medical advice immediately (show the label or SDS where possible).

SECTION 5: Firefighting measures

5.1. Extinguishing media

- Suitable extinguishing media : Treat for surrounding material.
- Unsuitable extinguishing media : None known.

5.2. Special hazards arising from the substance or mixture

- Fire hazard : Products of combustion may include, and are not limited to: oxides of carbon, hydrogen sulphide, hydrocarbons.

5.3. Advice for firefighters

- Protection during firefighting : Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

- General measures : Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

6.2. Methods and material for containment and cleaning up

- For containment : Contain spill, then place in a suitable container. Do not flush to sewer or allow to enter waterways. Use appropriate Personal Protective Equipment (PPE).
- Methods for cleaning up : Vacuum or sweep material and place in a disposal container.

6.3. Reference to other sections

See section 8 for further information on protective clothing and equipment and section 13 for advice on waste disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Avoid contact with skin and eyes. Avoid generating and breathing dust. Do not swallow. Handle and open container with care. The use of compressed air for cleaning clothing, equipment, etc, is not recommended. When using do not eat, drink or smoke.
- Hygiene measures : Launder contaminated clothing before reuse. Wash hands before eating, drinking, or smoking.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Keep out of the reach of children. Store in dust-tight, dry, labeled containers. Keep containers closed when not in use. Avoid any dust buildup by frequent cleaning and suitable construction of the storage area. Do not store in an area equipped with emergency water sprinklers.

7.3. Specific end use(s)

Not available.

Sakrete US Cold Patch

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Asphalt (8052-42-4)		
ACGIH	ACGIH TWA (mg/m ³)	0.5 mg/m ³ (fume, inhalable fraction)
OSHA	Not applicable	
Quartz (14808-60-7)		
ACGIH	ACGIH TWA (mg/m ³)	0.025 mg/m ³ (respirable fraction)
OSHA	OSHA PEL (TWA) (mg/m ³)	(30)/(%SiO ₂ + 2) mg/m ³ (total dust) (250)/(%SiO ₂ + 5) mppcf (respirable fraction) (10)/(%SiO ₂ + 2) mg/m ³ (respirable fraction)
Carbon black (1333-86-4)		
ACGIH	ACGIH TWA (mg/m ³)	3 mg/m ³ (inhalable fraction)
OSHA	OSHA PEL (TWA) (mg/m ³)	3.5 mg/m ³

8.2. Exposure controls

Appropriate engineering controls	: Use ventilation adequate to keep exposures (airborne levels of dust, fume, vapor, etc.) below recommended exposure limits.
Hand protection	: Wear suitable gloves.
Eye protection	: Safety glasses or goggles are recommended when using product.
Skin and body protection	: Wear suitable protective clothing.
Respiratory protection	: In case of insufficient ventilation, wear suitable respiratory equipment. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
Environmental exposure controls	: Maintain levels below Community environmental protection thresholds.
Other information	: Do not eat, smoke or drink where material is handled, processed or stored. Wash hands carefully before eating or smoking. Handle according to established industrial hygiene and safety practices.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid.
Appearance	: Crystals.
Colour	: Black.
Odour	: Odorless.
Odour threshold	: No data available.
pH	: No data available.
Relative evaporation rate (butylacetate=1)	: Nil.
Melting point	: No data available.
Freezing point	: No data available.
Boiling point	: No data available.
Flash point	: No data available.
Auto-ignition temperature	: No data available.
Decomposition temperature	: No data available.
Flammability (solid, gas)	: Not flammable.
Vapour pressure	: No data available.
Relative vapour density at 20 °C	: No data available.
Relative density	: No data available.
Solubility	: No data available.
Partition coefficient: n-octanol/water	: No data available.
Log Pow	: No data available.
Log Kow	: No data available.
Viscosity, kinematic	: No data available.
Viscosity, dynamic	: No data available.
Explosive properties	: No data available.

Sakrete US Cold Patch

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

Oxidising properties : No data available.

Explosive limits : No data available.

9.2. Other information

VOC content : 0%, Not applicable; 0 wt, Not applicable.

SECTION 10: Stability and reactivity

10.1. Reactivity

No dangerous reaction known under conditions of normal use.

10.2. Chemical stability

Stable under normal storage conditions.

10.3. Possibility of hazardous reactions

No dangerous reaction known under conditions of normal use.

10.4. Conditions to avoid

Heat. Incompatible materials.

10.5. Incompatible materials

Strong acids. Strong bases. Oxidizers.

10.6. Hazardous decomposition products

May include, and are not limited to: oxides of carbon, hydrogen sulfide, hydrocarbons.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified.

Sakrete US Cold Patch	
LD50 oral rat	> 2000 mg/kg
LD50 dermal rabbit	> 2000 mg/kg
LC50 inhalation rat	No data available.
Asphalt (8052-42-4)	
LD50 oral rat	> 5000 mg/kg
LD50 dermal rabbit	> 2000 mg/kg
Carbon black (1333-86-4)	
LD50 oral rat	>15400 mg/kg
LD50 dermal rabbit	>3 g/kg

Skin corrosion/irritation : Based on available data, the classification criteria are not met.

Serious eye damage/irritation : Based on available data, the classification criteria are not met.

Respiratory or skin sensitisation : Based on available data, the classification criteria are not met.

Germ cell mutagenicity : Based on available data, the classification criteria are not met.

Carcinogenicity : May cause cancer.

Asphalt (8052-42-4)	
IARC group	2B - Possibly carcinogenic to humans
National Toxicology Program (NTP) Status	5 - Twelfth Report - Items under consideration
Quartz (14808-60-7)	
IARC group	1 - Carcinogenic to humans
National Toxicology Program (NTP) Status	2 - Known Human Carcinogens
Carbon black (1333-86-4)	
IARC group	2B - Possibly carcinogenic to humans

Reproductive toxicity : Based on available data, the classification criteria are not met.

Specific target organ toxicity (single exposure) : Based on available data, the classification criteria are not met.

Sakrete US Cold Patch

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

- Specific target organ toxicity (repeated exposure) : Causes damage to lungs through prolonged or repeated exposure. Respirable crystalline silica in the form of quartz or cristobalite from occupational sources is listed by the International Agency for Research on Cancer (IARC) and National Toxicology Program (NTP) as a lung carcinogen. Prolonged exposure to respirable crystalline silica has been known to cause silicosis, a lung disease, which may be disabling. While there may be a factor of individual susceptibility to a given exposure to respirable silica dust, the risk of contracting silicosis and the severity of the disease is clearly related to the amount of dust exposure and the length of time (usually years) of exposure.
- Aspiration hazard : Based on available data, the classification criteria are not met.
- Symptoms/injuries after inhalation : May cause respiratory tract irritation.
- Symptoms/injuries after skin contact : Dust may cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin.
- Symptoms/injuries after eye contact : Dust may cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
- Symptoms/injuries after ingestion : May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

SECTION 12: Ecological information

12.1. Toxicity

- Ecology - general : No ecological consideration when used according to directions.

12.2. Persistence and degradability

Sakrete US Cold Patch

Persistence and degradability	Not established.
-------------------------------	------------------

12.3. Bioaccumulative potential

Sakrete US Cold Patch

Bioaccumulative potential	Not established.
---------------------------	------------------

12.4. Mobility in soil

No additional information available.

12.5. Other adverse effects

- Effect on the global warming : No known ecological damage caused by this product.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

- Waste disposal recommendations : This material must be disposed of in accordance with all local, state, provincial, and federal regulations. The generation of waste should be avoided or minimized wherever possible.

SECTION 14: Transport information

In accordance with DOT
Not regulated for transport

Additional information

- Other information : No supplementary information available.
- Special transport precautions : Do not handle until all safety precautions have been read and understood.

SECTION 15: Regulatory information

15.1. US Federal regulations

All components of this product are listed, or excluded from listing, on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory.

15.2. US State regulations

Sakrete US Cold Patch

State or local regulations	This product contains Crystalline Silica, Quartz and may also contain other chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.
----------------------------	---


Sakrete US Cold Patch

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

SECTION 16: Other information

Date of issue	: 01/29/2015
Other information	: None.
NFPA health hazard	: 1 - Exposure could cause irritation but only minor residual injury even if no treatment is given.
NFPA fire hazard	: 0 - Materials that will not burn.
NFPA reactivity	: 0 - Normally stable, even under fire exposure conditions, and are not reactive with water.



Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.