



No.:

Date: 24-DEC-2012

Customer :

TECHNICAL PROPOSAL

Three-phase induction motor - Squirrel cage rotor

Product line : Three-Phase: W22 IE2 IEC Tru-Metric - TEFC (IP55) Cast Iron Frame

Catalog Number : 18512EP3Y315L-W22

List Price : \$38,854

Notes:

Performed by:

Checked:



No.:

Date: 24-DEC-2012

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase: W22 IE2 IEC Tru-Metric - TEFC (IP55) Cast Iron Frame

Frame : 315L
Output : 250 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1190
Slip : 0.83 %
Voltage : 460 V
Rated current : 293 A
Locked rotor current : 2310 A
Locked rotor current (I_L/I_n) : 7.9
No-load current : 130 A
Full load torque : 1088 lb.ft
Locked rotor torque : 280 %
Breakdown torque : 270 %
Design : N
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 12 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000
Degree of Protection : IP55
Approximate weight : 2994 lb
Moment of inertia : 243.14 sq.ft.lb
Noise level : 71 dB(A)

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6319 C3	6316 C3	100%	0.83	95.4
Regreasing interval	13000 h	16000 h	75%	0.78	95.4
Grease amount	45 g	34 g	50%	0.65	94.5

Notes:

Performed by


Checked



No.:

Date: 24-DEC-2012

PERFORMANCE CURVES RELATED TO RATED OUTPUT Three-phase induction motor - Squirrel cage rotor



Customer :
Product line : Three-Phase: W22 IE2 IEC Tru-Metric - TEFC (IP55) Cast Iron Frame

Frame : 315L	Locked rotor current (I _l /I _n) : 7.9
Output : 250 HP	Duty cycle : S1
Frequency : 60 Hz	Service factor : 1.15
Full load speed : 1190	Design : N
Voltage : 460 V	Locked rotor torque : 280 %
Rated current : 293 A	Breakdown torque : 270 %
Insulation class : F	

Notes:

Performed by


Checked



No.:

Date: 24-DEC-2012

CHARACTERISTIC CURVES RELATED TO SPEED Three-phase induction motor - Squirrel cage rotor



Customer :
Product line : Three-Phase: W22 IE2 IEC Tru-Metric - TEFC (IP55) Cast Iron Frame

Frame	: 315L	Locked rotor current (I _l /I _n)	: 7.9
Output	: 250 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.15
Full load speed	: 1190	Design	: N
Voltage	: 460 V	Locked rotor torque	: 280 %
Rated current	: 293 A	Breakdown torque	: 270 %
Insulation class	: F		


Notes:

Performed by

Checked

1 2 3 4 5 6 7 8

A
B
C
D



	A	AA	AB	AC	AD
	508	120	630	657	589
	B	BA	BB	C	CA
	508	219	752	216	497
E	D	E	ES	F	G
	80m6	170	160	22	71
	GD	DA	EA	TS	FA
	14	65m6	140	125	18
	GB	GF	H	HA	HB
	58	11	315	48	336
	HC	HD	HF	HG	HH
	644	774	575	760	284
	HK	K	L	LC	LL
	215	28	1383	1535	404
F	LM	S1	d1	d2	Flange
	438	2XM63X1,5	DM20	DM20	FF-600
	LA	M	N	P	T
	22	600	550	660	6
	S	Angle	Holes		
	24	22°30'	8		

Notes:

Performed by:

Checked:

Customer:

Three-Phase: W22 IE2 IEC Tru-Metric - TEFC (IP55) Cast Iron Frame

Three-phase induction motor
Frame 315L - IP55

24-DEC-2012

