

Water Baths

Digital Series



The SHEL LAB high-performance water baths are accurate, easy to use, safe and durable. The water bath design incorporates a drip free cover holster and pocket handles so users can easily transport the water bath.

A microprocessor achieves precise temperature control regardless of how the unit is loaded. Calibration is performed with the convenient, front panel touch pad, which is essential for facilities concerned with IQ/OQ/PQ validation.

FEATURES

- Easy-to-Clean Stainless Steel Tank
- Pocket Handles for Easy Lifting
- Recessed Heating Element Prevents "Burnout"
- Unique SHEL LAB Design Eliminates "Hot Spots"
- Thermometer Clip Included

SHEL LAB was the first to introduce the non-contact recessed heating element design to the analytical research market. This curtails element burnout and eliminates tank hot spots that are chronic challenges for other water baths.

The SHEL LAB digital water baths remain an industry standard for precise control and quality of design. The SHEL LAB constant temperature digital water baths are perfect for conducting a host of applications including: bacteriological examinations, food processing/QC procedures and microbiology assays just to name a few.

SHEL LAB digital water baths are durable and dependable.


Water Bath Applications

- Sample Thawing
- Bacteriological Examinations
- Warming Reagents
- Coliform Determinations
- Microbiological Assays




Precise Temperature Control -

- Over Temperature Protection
- Temperature Uniformity +/- 0.2% at 37°C
- Temperature Range Ambient + 5°C to 80°C
- Coated tanks available for applications up to 80°C



		Model Number	
Dual Chamber Water Bath	110-120V	SWB715	
	220-230V	SWB715-2	
Exterior Dimensions (wxdxh)	Inches	24.3 x 19.3 x 8.8	
	cm	61.6 x 48.9 x 22.3	
		Chamber/Tank 1	Chamber/Tank 2
Bath Chamber Dimensions (wxdxh)	Inches	11.7 x 6.0 x 6.0	11.7 x 13.0 x 6.0
	cm	29.8 x 15.2 x 15.2	29.8 x 33.0 x 15.2
Tank Capacity	L	7	15
Stainless Steel Gable Cover(s)	Yes/No	Yes - Two (2) Included	




General Purpose Water Baths	Model Number				
	110-120V	SWB2	SWB7	SWB15	SWB23
	220-230V	SWB2-2	SWB7-2	SWB15-2	SWB23-2
	Chambers	Single (1)	Single (1)	Single (1)	Single (1)
Exterior Dimensions (wxdxh)	Inches	15.0 x 12.0 x 8.8	15.3 x 12.0 x 9.0	15.0 x 19.0 x 9.0	15.0 x 25.3 x 9.0
	cm	38.1 x 30.5 x 22.3	38.8 x 30.5 x 22.9	38.1 x 48.3 x 22.9	38.1 x 64.2 x 22.9
Bath Tank Dimensions (wxdxh)	Inches	11.7 x 5.7 x 2.5	11.7 x 6.0 x 6.0	11.7 x 13.0 x 6.0	11.5 x 19.5 x 6.2
	cm	29.8 x 14.6 x 6.3	29.8 x 15.2 x 15.2	29.8 x 33.0 x 15.2	29.2 x 49.5 x 15.8
Tank Capacity	L	2	7	15	23
Stainless Steel Gable Cover(s)	Yes/No	Yes - One Included	Yes - One Included	Yes - One Included	Yes - One Included

*Tank is excluded from the 2 year warranty. All specifications are determined by using average values on standard equipment at an ambient temperature of 25°C (77°F) and line voltages within +/-10% of unit type (115V/230V). Temperature specifications follow DIN 12880 methodology. We reserve the right to change specifications at any time.



0740514 3/14



www.shellab.com
1-800-322-4897