SPEAKMAN® SE-7001

HEAT TRACED COMBINATION SHOWER & EYE/FACE WASH

<u>DESCRIPTION</u>
SE-7001 Freeze protected combination shower and eye/face wash units are wrapped with heat trace
cable and insulation and jacketed with an easy access shell to protect them to -50°F. Eye/Face wash
features dual aerated spray outlets with automatic flow controls and flip top dust covers. The impel-
lar action shower is activated by a high visibility yellow pull rod. An integral freeze valve protects unit
from freezing in case of power outage.
SPECIFICATIONS
Showerhead: 8" Dia. CYCOLAC® yellow plastic
Flow Control: Internal 20 gpm regulator
Freeze Valve: Activates automatically below 40°F
Valve: 1" NPTF chrome plated brass stay-open ball valve
Activator: Powder coated high visibility yellow, aluminum triangular pull rod
Internal Stanchion: 1" IPS galvanized steel pipe
Inlet: 1" NPT male, top supply

Performance: 20 gpm @ 30 psi Finish: Dura-Jade green plastic

EYE/FACE WASH

Spray Head: (2) yellow plastic spray outlets with automatic flow control and flip-top dust caps

Valves: 1/2" NPT brass, 3-way chrome plated ball valve

Performance: 3.82 gpm @ 30 psi Activator: Stainless steel push handle

ELECTRIC

Heating Tape: Self-limiting parallel resistance cable with braided metal shield

Thermostat: Preset, hermetically sealed single pole contact switch. Temperature range 60° to 70° F

Insulation: Closed cell rubber foam

Junction Box: NEMA 4X water tight and dust tight, suitable for indoor or outdoor locations

Power Supply: 120 vac, 60 cycle, single phase

Electrical Classification: Class 1 Division 2 GRP. B, C, D

Ground Fault Protection: Installation will require minimum 30 mA GFPD

Compliance: ANSI Z358.1

INTEGRAL OPTIONS			
☐ 30GPM	30gpm regulator		
\square DH	Drench hose		
☐ IWT	Immersion well thermometer		
\square SPV	Scald protection valve		
☐ PL	Pilot Light	Job Name	
\square SS	Stainless Steel		
<u>ACCESSORIES</u>		Location	
\square VPL	Area light	Architect/Engineer	
☐ VPL-C1D2	Hazardous area light	Sales Representative	
☐ FLW	Flow switch	•	
☐ FLW-DPDT	Flow switch - double pull	Wholesaler	
	double throw	Date Model #	