


WORLDWIDE SHAKER SCREEN MOTORS EISA-COMPLIANT HIGH EFFICIENCY

TEFC Enclosure ▪ Rigid Base
Three-Phase ▪ 208-230/460 Volt



ALL DIMENSIONS IN INCHES

Frame	E	2F1	2F2	H	BA	A	B	C	D	G	J	P	O	AB	T	S	ES	R	N-W	U	AA	XB	XC	XD	XE
326T	6.25	10.5	12	0.66	5.25	16	15.5	31.24	8	0.984	2.76	15.75	15.91	13.4	2.44	0.5	3.91	1.845	5.25	2.125	2	2.64	10.55	8.98	10.47
365T	7	11.25	12.25	0.66	5.88	18	16.2	34.11	9	1.102	2.95	17.7	18.13	15.7	2.44	0.625	4.28	2.021	5.88	2.375	3	3.74	10.55	8.98	11.3
404T	8	---	12.25	0.81	6.62	20	16.2	36.81	10	1.18	3.15	21.42	21.02	18.31	2.83	0.75	5.65	2.45	7.25	2.875	3	4.57	11.73	9.76	11.69

DIMENSIONS

Dimensions shown in this catalog are for general use only.
For an exact drawing on a specific rating, please contact our sales office.

